

MS Membrane Filters Product List 2014

(Ctrl F)
> Cat.#s

> Current System AUD Prices



| | | | |
|---|-------------------|---|-----|
| MFPTFE047045B | | Hydrophobic PTFE Membrane Filter, Pore:0.45(μm), Diameter:47(mm) | 200 |
| MFPTFE090045B | | Hydrophobic PTFE Membrane Filter, Pore:0.45(μm), Diameter:90(mm) | 100 |
| MFPTFE142045B | | Hydrophobic PTFE Membrane Filter, Pore:0.45(μm), Diameter:142(mm) | 50 |
| MFPTFE025010B | Pore size: 0.1um | Hydrophobic PTFE Membrane Filter, Pore:0.1(μm), Diameter:25(mm) | 200 |
| MFPTFE047010B | | Hydrophobic PTFE Membrane Filter, Pore:0.1(μm), Diameter:47(mm) | 200 |
| MFPTFE090010B | | Hydrophobic PTFE Membrane Filter, Pore:0.1(μm), Diameter:90(mm) | 100 |
| MFPTFE142010B | | Hydrophobic PTFE Membrane Filter, Pore:0.1(μm), Diameter:142(mm) | 50 |
| MFPTFE025100B | Pore size: 1.2um | Hydrophobic PTFE Membrane Filter, Pore:1.2(μm), Diameter:25(mm) | 200 |
| MFPTFE047100B | | Hydrophobic PTFE Membrane Filter, Pore:1.2(μm), Diameter:47(mm) | 200 |
| MFPTFE090100B | | Hydrophobic PTFE Membrane Filter, Pore:1.2(μm), Diameter:90(mm) | 100 |
| MFPTFE142100B | | Hydrophobic PTFE Membrane Filter, Pore:1.2(μm), Diameter:142(mm) | 50 |
| MFPTFE025300B | Pore size: 3.0um | Hydrophobic PTFE Membrane Filter, Pore:3.0(μm), Diameter:25(mm) | 200 |
| MFPTFE047300B | | Hydrophobic PTFE Membrane Filter, Pore:3.0(μm), Diameter:47(mm) | 200 |
| MFPTFE090300B | | Hydrophobic PTFE Membrane Filter, Pore:3.0(μm), Diameter:90(mm) | 100 |
| MFPTFE142300B | | Hydrophobic PTFE Membrane Filter, Pore:3.0(μm), Diameter:142(mm) | 50 |
| MFPTFE025300B | Pore size: 5.0um | Hydrophobic PTFE Membrane Filter, Pore:3.0(μm), Diameter:25(mm) | 200 |
| MFPTFE047500B | | Hydrophobic PTFE Membrane Filter, Pore:5.0(μm), Diameter:47(mm) | 200 |
| MFPTFE090500B | | Hydrophobic PTFE Membrane Filter, Pore:5.0(μm), Diameter:90(mm) | 100 |
| MFPTFE142500B | | Hydrophobic PTFE Membrane Filter, Pore:5.0(μm), Diameter:142(mm) | 50 |
| Hydrophilic PTFE Membrane Filter | | | |
| MFPTFE013022L | Pore size: 0.22um | Hydrophilic PTFE Membrane Filter, Pore:0.22(μm), Diameter:13(mm) | 400 |
| MFPTFE025022L | | Hydrophilic PTFE Membrane Filter, Pore:0.22(μm), Diameter:25(mm) | 200 |
| MFPTFE047022L | | Hydrophilic PTFE Membrane Filter, Pore:0.22(μm), Diameter:47(mm) | 200 |
| MFPTFE090022L | | Hydrophilic PTFE Membrane Filter, Pore:0.22(μm), Diameter:90(mm) | 100 |
| MFPTFE013045L | Pore size: 0.45um | Hydrophilic PTFE Membrane Filter, Pore:0.45(μm), Diameter:13(mm) | 400 |
| MFPTFE025045L | | Hydrophilic PTFE Membrane Filter, Pore:0.45(μm), Diameter:25(mm) | 200 |
| MFPTFE047045L | | Hydrophilic PTFE Membrane Filter, Pore:0.45(μm), Diameter:47(mm) | 200 |
| MFPTFE090045L | | Hydrophilic PTFE Membrane Filter, Pore:0.45(μm), Diameter:90(mm) | 100 |
| CA Membrane Filter | | | |
| MFCA013022 | Pore size: 0.22um | CA Membrane Filter, Pore:0.22(μm), Diameter:13(mm) | 400 |
| MFCA025022 | | CA Membrane Filter, Pore:0.22(μm), Diameter:25(mm) | 200 |
| MFCA047022 | | CA Membrane Filter, Pore:0.22(μm), Diameter:47(mm) | 200 |
| MFCA090022 | | CA Membrane Filter, Pore:0.22(μm), Diameter:90(mm) | 100 |
| MFCA142022 | | CA Membrane Filter, Pore:0.22(μm), Diameter:142(mm) | 50 |
| MFCA013045 | Pore size: 0.45um | CA Membrane Filter, Pore:0.45(μm), Diameter:13(mm) | 400 |
| MFCA025045 | | CA Membrane Filter, Pore:0.45(μm), Diameter:25(mm) | 200 |
| MFCA047045 | | CA Membrane Filter, Pore:0.45(μm), Diameter:47(mm) | 200 |
| MFCA090045 | | CA Membrane Filter, Pore:0.45(μm), Diameter:90(mm) | 100 |
| MFCA142045 | | CA Membrane Filter, Pore:0.45(μm), Diameter:142(mm) | 50 |
| MFCA013080 | Pore size: 0.8um | CA Membrane Filter, Pore:0.8(μm), Diameter:13(mm) | 400 |
| MFCA025080 | | CA Membrane Filter, Pore:0.8(μm), Diameter:25(mm) | 200 |
| MFCA047080 | | CA Membrane Filter, Pore:0.8(μm), Diameter:47(mm) | 200 |
| MFCA090080 | | CA Membrane Filter, Pore:0.8(μm), Diameter:90(mm) | 100 |
| MFCA142080 | | CA Membrane Filter, Pore:0.8(μm), Diameter:142(mm) | 50 |
| CN Membrane Filter | | | |