



VICIValco-Cheminert PRODUCT LIST 2012

Part No.	Description 1	Specs
.2FR.5-5	Frit 1/32in 0.2 micron	.25mm thick 316SS 5/pkg
.5FR.5-5	Frit 1/32in 0.5 micron	.25mm thick 316SS 5/pkg
.5FR1-10	Frit 1/16in 0.5 micron	.75mm thick 316SS 10/pkg
.5FR1HC-10	Frit 1/16in 0.5 micron	.75mm thick HC 10/pkg
.5FR2-10	Frit 1/8in 0.5 micron	1mm thick 316SS 10/pkg
.5FR4-10	Frit 1/4in 0.5 micron	1mm thick 316SS 10/pkg
.5SR.5-10	Screen 1/32in OD 0.5 micron 316SS 10/pkg	
.5SR1-10	Screen 1/16in OD 0.5 micron 316SS 10/pkg	
.5SR2-10	Screen 1/8in OD 0.5 micron 316SS 10/pkg	
.5SR4-10	Screen 1/4in 0.5 micron 316SS 10/pkg	
10FR1-10	Frit 1/16in 10 micron	.75mm thick 316SS 10/pkg
10FR2-10	Frit 1/8in 10 micron	1mm thick 316SS 10/pkg
10FR4-10	Frit 1/4in 10 micron	1mm thick 316SS 10/pkg
10FR4HC-10	Frit 1/4in 10 micron	1mm thick HC 10/pkg
10SR.5-10	Screen 1/32in 10 micron 316SS 10/pkg	
10SR1-10	Screen 1/16in 10 micron 316SS 10/pkg	
10SR2-10	Screen 1/8in 10 micron 316SS 10/pkg	
10SR4-10	Screen 1/4in 10 micron 316SS 10/pkg	
1SR.5-10	Screen 1/32in OD 1 micron 316SS 10/pkg	
1SR1-10	Screen 1/16in OD 1 micron 316SS 10/pkg	
1SR2-10	Screen 1/8in OD 1 micron 316SS 10/pkg	
1SR4-10	Screen 1/4in 1 micron 316SS 10/pkg	
210UW	10 port 2-pos valve manual/2in so	1/8 x .75mm 75C/5000psi liq N60/H
24UW	4 port 2-pos valve manual/2in so	1/8 x .75mm 75C/5000psi liq N60/H
26UW	6 port 2-pos valve manual/2in so	1/8 x .75mm 75C/5000psi liq N60/H
28UW	8 port 2-pos valve manual/2in so	1/8 x .75mm 75C/5000psi liq N60/H
2C10UW	10 port 2-pos valve manual/2in so	1/16 x .75mm 75C/5000psi liq N60/H
2C4UW	4 port 2-pos valve manual/2in so	1/16 x .75mm 75C/5000psi liq N60/H
2C6UW	6 port 2-pos valve manual/2in so	1/16 x .75mm 75C/5000psi liq N60/H
2C8UW	8 port 2-pos valve manual/2in so	1/16 x .75mm 75C/5000psi liq N60/H
2Ci4UW.2	4 port 2-pos int vol valve manual/2in so	1/16 x .75mm 75C/5000psi liq .2ul N60/H
2Ci4UW.5	4 port 2-pos int vol valve manual/2in so	1/16 x .75mm 75C/5000psi liq .5ul N60/H
2Ci4UW1	4 port 2-pos int vol valve manual/2in so	1/16 x .75mm 75C/5000psi liq 1ul N60/H
2Ci4UW2	4 port 2-pos int vol valve manual/2in so	1/16 x .75mm 75C/5000psi liq 2ul N60/H
2Ci4UWE.2	4 port 2-pos int vol valve manual/2in so	1/16 x .75mm 175C/1000psi liq .2ul N60/E
2Ci4UWE.5	4 port 2-pos int vol valve manual/2in so	1/16 x .75mm 175C/1000psi liq .5ul N60/E
2Ci4UWE1	4 port 2-pos int vol valve manual/2in so	1/16 x .75mm 175C/1000psi liq 1ul N60/E
2Ci4UWE2	4 port 2-pos int vol valve manual/2in so	1/16 x .75mm 175C/1000psi liq 2ul N60/E
2Ci4WE.06	4 port 2-pos int vol valve manual/2in so	1/16 x .4mm 175C/1000psi liq .06ul N60/E
2Ci4WE.1	4 port 2-pos int vol valve manual/2in so	1/16 x .4mm 175C/1000psi liq .1ul N60/E
2Ci4WE.2	4 port 2-pos int vol valve manual/2in so	1/16 x .4mm 175C/1000psi liq .2ul N60/E
2Ci4WE.5	4 port 2-pos int vol valve manual/2in so	1/16 x .4mm 175C/1000psi liq .5ul N60/E
2CSC10MWE	10 mpos common outlet path MW manual/2in so	1/16 x 1mm 200C/200psi gas N60/E
2CSC12MWE	12 mpos common outlet path MW manual/2in so	1/16 x 1mm 200C/200psi gas N60/E
2CSC16MWE	16 mpos common outlet path MW manual/2in so	1/16 x 1mm 200C/200psi gas N60/E
2CSC6MWE	6 mpos common outlet path MW manual/2in so	1/16 x 1mm 200C/200psi gas N60/E
2CSD10MWE	10 mpos dead-end path MW manual/2in so	1/16 x .75mm 200C/400psi gas N60/E
2CSD12MWE	12 mpos dead-end path MW manual/2in so	1/16 x .75mm 200C/400psi gas N60/E
2CSD16MWE	16 mpos dead-end path MW manual/2in so	1/16 x .75mm 200C/400psi gas N60/E
2CSD6MWE	6 mpos dead-end path MW manual/2in so	1/16 x .75mm 200C/400psi gas N60/E
2CSF10MWE	10 mpos flow-through MW manual/2in so	1/16 x 1mm 200C/200psi gas N60/E
2CSF12MWE	12 mpos flow-through MW manual/2in so	1/16 x 1mm 200C/200psi gas N60/E
2CSF16MWE	16 mpos flow-through MW manual/2in so	1/16 x 1mm 200C/200psi gas N60/E