

VICIValco-Cheminert PRODUCT LIST 2012

(Ctrl F)
> Cat.#s

> Current System AUD Prices



2CSF6MWE	6 mpos flow-through MW manual/2in so	1/16 x 1mm 200C/200psi gas N60/E
2CST10MWE	10 mpos trapping path MW manual/2in so	1/16 x .75mm 200C/200psi gas N60/E
2CST12MWE	12 mpos trap/flow path MW manual/2in so	1/16 x .75mm 200C/200psi gas N60/E
2CST16MWE	16 mpos trap/flow path MW manual/2in so	1/16 x .75mm 200C/200psi gas N60/E
2CST6MWE	6 mpos trap/flow path MW manual/2in so	1/16 x .75mm 200C/200psi gas N60/E
2CSTF10MWE	10 mpos trap/flow path MW manual/2in so	1/16 x .75mm 200C/200psi gas N60/E
2CSTF12MWE	12 mpos trap/flow path MW manual/2in so	1/16 x .75mm 200C/200psi gas N60/E
2CSTF16MWE	16 mpos trap/flow path MW manual/2in so	1/16 x .75mm 200C/200psi gas N60/E
2CSTF6MWE	6 mpos trap/flow path MW manual/2in so	1/16 x .75mm 200C/200psi gas N60/E
2FR1-10	Frit 1/16in 2 micron	.75mm thick 316SS 10/pkg
2FR1HC-10	Frit 1/16in 2 micron	.75mm thick HC 10/pkg
2FR1K	Frit 1in 2 micron	1.5mm thick 316SS
2FR1KHC	Frit 1in 2 micron	1.5mm thick HC
2FR1KTI	Frit 1in 2 micron	1.5mm thick Titanium
2FR1TI-10	Frit 1/16in 2 micron	.75mm thick Titanium 10/pkg
2FR2-10	Frit 1/8in 2 micron	1mm thick 316SS 10/pkg
2FR2HC-10	Frit 1/8in 2 micron	1mm thick HC 10/pkg
2FR2TI-10	Frit 1/8in 2 micron	1mm thick Titanium 10/pkg
2FR4-10	Frit 1/4in 2 micron	1mm thick 316SS 10/pkg
2FR4HC-10	Frit 1/4in 2 micron	1mm thick HC 10/pkg
2FR4TI-10	Frit 1/4in 2 micron	1mm thick Titanium 10/pkg
2FR6	Frit 3/8in 2 micron	1mm thick 316SS
2FR6HC	Frit 3/8in 2 micron	1mm thick HC
2FR6TI	Frit 3/8in 2 micron	1mm thick Titanium
2FR8	Frit 1/2in 2 micron	1mm thick 316SS
2FR8HC	Frit 1/2in 2 micron	1mm thick HC
2FR8TI	Frit 1/2in 2 micron	1mm thick Titanium
2I4UWE.2	4 port 2-pos int vol valve manual/2in so	1/8 x .75mm 175C/1000psi liq .2ul N60/E
2I4UWE.5	4 port 2-pos int vol valve manual/2in so	1/8 x .75mm 175C/1000psi liq .5ul N60/E
2I4UWE1	4 port 2-pos int vol valve manual/2in so	1/8 x .75mm 175C/1000psi liq 1ul N60/E
2I4UWE2	4 port 2-pos int vol valve manual/2in so	1/8 x .75mm 175C/1000psi liq 2ul N60/E
2L10UW	10 port 2-pos valve manual/2in so	1/8 x 1.0mm 75C/5000psi liq N60/H
2L4UW	4 port 2-pos valve manual/2in so	1/8 x 1.7mm 75C/5000psi liq N60/H
2L6UW	6 port 2-pos valve manual/2in so	1/8 x 1.7mm 75C/5000psi liq N60/H
2L8UW	8 port 2-pos valve manual/2in so	1/8 x 1.3mm 75C/5000psi liq N60/H
2NI4WE.06	4 port 2-pos int vol valve manual/2in so	1/32 x .25mm 175C/1000psi liq .06ulN60/E
2NI4WE.1	4 port 2-pos int vol valve manual/2in so	1/32 x .25mm 175C/1000psi liq .1ulN60/E
2NI4WE.2	4 port 2-pos int vol valve manual/2in so	1/32 x .25mm 175C/1000psi liq .2ulN60/E
2NI4WE.5	4 port 2-pos int vol valve manual/2in so	1/32 x .25mm 175C/1000psi liq .5ulN60/E
2RAD	Right angle drive 2in standoff	
2SC10MWE	10 mpos common outlet pathMWmanual/2in so	1/8 x 1mm 200C/200psi gas N60/E
2SC12MWE	12 mpos common outlet pathMWmanual/2in so	1/8 x 1mm 200C/200psi gas N60/E
2SC16MWE	16 mpos common outlet pathMWmanual/2in so	1/8 x 1mm 200C/200psi gas N60/E
2SC6MWE	6 mpos common outlet pathMWmanual/2in so	1/8 x 1mm 200C/200psi gas N60/E
2SD10MWE	10 mpos dead-end path MW manual/2in so	1/8 x 1mm 200C/200psi gas N60/E
2SD12MWE	12 mpos dead-end path MW manual/2in so	1/8 x 1mm 200C/200psi gas N60/E
2SD16MWE	16 mpos dead-end path MW manual/2in so	1/8 x 1mm 200C/200psi gas N60/E
2SD6MWE	6 mpos dead-end path MW manual/2in so	1/8 x 1mm 200C/400psi gas N60/E
2SF10MWE	10 mpos flow-through MW manual/2in so	1/8 x 1mm 200C/200psi gas N60/E
2SF12MWE	12 mpos flow-through MW manual/2in so	1/8 x 1mm 200C/200psi gas N60/E
2SF16MWE	16 mpos flow-through MW manual/2in so	1/8 x 1mm 200C/200psi gas N60/E
2SF6MWE	6 mpos flow-through MW manual/2in so	1/8 x 1mm 200C/200psi gas N60/E
2SOA	Standoff assembly 2in	for 2 pos actuator
2SOAMMP	Standoff assembly 2in keyed	for m-electric actuator
2SOAMP	Standoff assembly 2in	for mpos actuator
2SR.5-10	Screen 1/32in 2 micron 316SS 10/pkg	
2SR1-10	Screen 1/16in 2 micron 316SS 10/pkg	
2SR2-10	Screen 1/8in 2 micron 316SS 10/pkg	
2SR4-10	Screen 1/4in 2 micron 316SS 10/pkg	
2ST10MWE	10 mpos trapping path MW manual/2in so	1/8 x 1mm 200C/200psi gas N60/E
2ST12MWE	12 mpos trapping path MW manual/2in so	1/8 x 1mm 200C/200psi gas N60/E