

VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]
> Cat.#s

> Current System AUD Prices



2ST16MWE	16 mpos trapping path MW manual/2in so	1/8 x 1mm 200C/200psi gas N60/E
2ST6MWE	6 mpos trapping path MW manual/2in so	1/8 x 1mm 200C/200psi gas N60/E
2STF10MWE	10 mpos trap/flow path MW manual/2in so	1/8 x 1mm 200C/200psi gas N60/E
2STF12MWE	12 mpos trap/flow path MW manual/2in so	1/8 x 1mm 200C/200psi gas N60/E
2STF16MWE	16 mpos trap/flow path MW manual/2in so	1/8 x 1mm 200C/200psi gas N60/E
2STF6MWE	6 mpos trap/flow path MW manual/2in so	1/8 x 1mm 200C/200psi gas N60/E
410UWE	10 port 2-pos valve manual/4in so	1/8 x .75mm 225C/400psi gas N60/E
410UWT	10 port 2-pos valve manual/4in so	1/8 x .75mm 330C/300psi gas N60/T
41E1-120VAC	4-way solenoid air valve 120Vac	Non-CE !!!
41E1-12VDC	4-way solenoid air valve 12Vdc	Non-CE !!!
41E1-220VAC	4-way solenoid air valve 220Vac	Non-CE !!!
41E1-24VAC	4-way solenoid air valve 24Vac	Non-CE !!!
41E1-24VDC	4-way solenoid air valve 24Vdc	Non-CE !!!
44UWE	4 port 2-pos valve manual/4in so	1/8 x .75mm 225C/400psi gas N60/E
44UWT	4 port 2-pos valve manual/4in so	1/8 x .75mm 330C/300psi gas N60/T
46UWE	6 port 2-pos valve manual/4in so	1/8 x .75mm 225C/400psi gas N60/E
46UWT	6 port 2-pos valve manual/4in so	1/8 x .75mm 330C/300psi gas N60/T
48UWE	8 port 2-pos valve manual/4in so	1/8 x .75mm 225C/400psi gas N60/E
48UWT	8 port 2-pos valve manual/4in so	1/8 x .75mm 330C/300psi gas N60/T
4C10UWE	10 port 2-pos valve manual/4in so	1/16 x .75mm 225C/400psi gas N60/E
4C10UWT	10 port 2-pos valve manual/4in so	1/16 x .75mm 330C/300psi gas N60/T
4C10WE	10 port 2-pos valve manual/4in so	1/16 x .4mm 225C/400psi gas N60/E
4C10WT	10 port 2-pos valve manual/4in so	1/16 x .4mm 350C/300psi gas N60/T
4C4UWE	4 port 2-pos valve manual/4in so	1/16 x .75mm 225C/400psi gas N60/E
4C4UWT	4 port 2-pos valve manual/4in so	1/16 x .75mm 330C/300psi gas N60/T
4C4WE	4 port 2-pos valve manual/4in so	1/16 x .4mm 225C/400psi gas N60/E
4C4WT	4 port 2-pos valve manual/4in so	1/16 x .4mm 350C/300psi gas N60/T
4C6UWE	6 port 2-pos valve manual/4in so	1/16 x .75mm 225C/400psi gas N60/E
4C6UWT	6 port 2-pos valve manual/4in so	1/16 x .75mm 330C/300psi gas N60/T
4C6WE	6 port 2-pos valve manual/4in so	1/16 x .4mm 225C/400psi gas N60/E
4C6WT	6 port 2-pos valve manual/4in so	1/16 x .4mm 350C/300psi gas N60/T
4C8UWE	8 port 2-pos valve manual/4in so	1/16 x .75mm 225C/400psi gas N60/E
4C8UWT	8 port 2-pos valve manual/4in so	1/16 x .75mm 330C/300psi gas N60/T
4C8WE	8 port 2-pos valve manual/4in so	1/16 x .4mm 225C/400psi gas N60/E
4C8WT	8 port 2-pos valve manual/4in so	1/16 x .4mm 350C/300psi gas N60/T
4N10WE	10 port 2-pos valve manual/4in so	1/32 x .25mm 225C/400psi gas N60/E
4N10WT	10 port 2-pos valve manual/4in so	1/32 x .25mm 350C/300psi gas N60/T
4N4WE	4 port 2-pos valve manual/4in so	1/32 x .25mm 225C/400psi gas N60/E
4N4WT	4 port 2-pos valve manual/4in so	1/32 x .25mm 350C/300psi gas N60/T
4N6WE	6 port 2-pos valve manual/4in so	1/32 x .25mm 225C/400psi gas N60/E
4N6WT	6 port 2-pos valve manual/4in so	1/32 x .25mm 350C/300psi gas N60/T
4N8WE	8 port 2-pos valve manual/4in so	1/32 x .25mm 225C/400psi gas N60/E
4N8WT	8 port 2-pos valve manual/4in so	1/32 x .25mm 350C/300psi gas N60/T
4SOA	Standoff assembly 4in	for 2 pos actuator
4SOAMP	Standoff assembly 4in	for mpos actuator
4SOUTH	Handle with 4in standoff Valco UW-type	2-pos valve with 1 or 2 mounting holes
4SOUTHMP	Handle with 4in standoff Valco UW-type	2-pos valve with no mounting holes
4SOWK	4in standoff assy for 2 pos vlv W/WK	with 1 or 2 mounting holes
4SOWKMP	4in Standoff assy for 2 pos vlv W/WK	with no mounting holesand Cheminert vlv
4UW	!!! RECOMMEND 24UW	SUPPLIED WITH LARGER HANDLE
4UWE	4 port 2-pos valve manual	1/8 x .75mm 225C/400psi gas N60/E
4VL4MWE2	4 port 2-pos valve MW manual/4in so	1/4 x 4mm 75C/100psi gas N60/E2
4VL6MWE2	6 port 2-pos valve MW manual/4in so	1/4 x 4mm 75C/100psi gas N60/E2
4VL8MWE2	8 port 2-pos valve MW manual/4in so	1/4 x 4mm 75C/100psi gas N60/E2
6UW	!!! RECOMMEND 26UW	SUPPLIED WITH LARGER HANDLE
6UWE	6 port 2-pos valve manual	1/8 x .75mm 225C/400psi gas N60/E
8UW	!!! RECOMMEND 28UW	SUPPLIED WITH LARGER HANDLE
8UWE	8 port 2-pos valve manual	1/8 x .75mm 225C/400psi gas N60/E
A10	Air actuator 10 mpos close mount	36 deg rotation
A102	Air actuator 10 mpos 2in standoff	36 deg rotation
A10S	Air actuator 10 mpos for standoff	36 deg rotation