

VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]
> Cat.#s

> Current System AUD Prices



A10UW	10 port 2-pos valve air actuated	1/8 x .75mm 75C/5000psi liq N60/H
A12	Air actuator 12 mpos close mount	30 deg rotation
A122	Air actuator 12 mpos 2in standoff	30 deg rotation
A12S	Air actuator 12 mpos for standoff	30 deg rotation
A16	Air actuator 16 mpos close mount	22.5 deg rotation
A162	Air actuator 16 mpos 2in standoff	22.5 deg rotation
A16S	Air actuator 16 mpos for standoff	22.5 deg rotation
A2CI4UWE.2	4 port 2-pos int vol valve air act/2in so	1/16 x .75mm 175C/1000psi liq .2ul N60/E
A2CI4UWE.5	4 port 2-pos int vol valve air act/2in so	1/16 x .75mm 175C/1000psi liq .5ul N60/E
A2CI4UWE1	4 port 2-pos int vol valve air act/2in so	1/16 x .75mm 175C/1000psi liq 1ul N60/E
A2CI4UWE2	4 port 2-pos int vol valve air act/2in so	1/16 x .75mm 175C/1000psi liq 2ul N60/E
A2CI4WE.06	4 port 2-pos int vol valve air act/2in so	1/16 x .4mm 175C/1000psi liq .06ul N60/E
A2CI4WE.1	4 port 2-pos int vol valve air act/2in so	1/16 x .4mm 175C/1000psi liq .1ul N60/E
A2CI4WE.2	4 port 2-pos int vol valve air act/2in so	1/16 x .4mm 175C/1000psi liq .2ul N60/E
A2CI4WE.5	4 port 2-pos int vol valve air act/2in so	1/16 x .4mm 175C/1000psi liq .5ul N60/E
A2CSC10MWE	10 mpos common outlet path MWair act/2in so	1/16 x 1mm 200C/200psi gas N60/E
A2CSC12MWE	12 mpos common outlet path MWair act/2in so	1/16 x 1mm 200C/200psi gas N60/E
A2CSC16MWE	16 mpos common outlet path MWair act/2in so	1/16 x 1mm 200C/200psi gas N60/E
A2CSC6MWE	OBSOLETE USE AH2CSC6MWE	
A2CSD10MWE	10 mpos dead-end path MW air act/2in so	1/16 x .75mm 200C/400psi gas N60/E
A2CSD12MWE	12 mpos dead-end path MW air act/2in so	1/16 x .75mm 200C/400psi gas N60/E
A2CSD16MWE	16 mpos dead-end path MW air act/2in so	1/16 x .75mm 200C/400psi gas N60/E
A2CSD6MWE	6 mpos dead-end path MW air act/2in so	1/16 x .75mm 200C/400psi gas N60/E
A2CSF10MWE	10 mpos flow-through MW air act/2in so	1/16 x 1mm 200C/200psi gas N60/E
A2CSF12MWE	12 mpos flow-through MW air act/2in so	1/16 x 1mm 200C/200psi gas N60/E
A2CSF16MWE	16 mpos flow-through MW air act/2in so	1/16 x 1mm 200C/200psi gas N60/E
A2CSF6MWE	OBSOLETE USE AH2CSF6MWE	
A2CST10MWE	10 mpos trapping path MW air act high torq./2in so	1/16 x .75mm 200C/200psi gas N60/E
A2CST12MWE	12 mpos trapping path MW air act high torq./2in so	1/16 x .75mm 200C/200psi gas N60/E
A2CST16MWE	16 mpos trapping path MW air act high torq./2in so	1/16 x .75mm 200C/200psi gas N60/E
A2CST6MWE	OBSOLETE USE AH2CST6MWE	
A2CSTF10MWE	10 mpos trap/flow path MW air act high t./2in so	1/16 x .75mm 200C/200psi gas N60/E
A2CSTF12MWE	12 mpos trap/flow path MW air act high t./2in so	1/16 x .75mm 200C/200psi gas N60/E
A2CSTF16MWE	16 mpos trap/flow path MW air act high t./2in so	1/16 x .75mm 200C/200psi gas N60/E
A2CSTF6MWE	OBSOLETE USE AH2CSTF6MWE	
A2I4UWE.2	4 port 2-pos int vol valve air act/2in so	1/8 x .75mm 175C/1000psi liq .2ul N60/E
A2I4UWE.5	4 port 2-pos int vol valve air act/2in so	1/8 x .75mm 175C/1000psi liq .5ul N60/E
A2I4UWE1	4 port 2-pos int vol valve air act/2in so	1/8 x .75mm 175C/1000psi liq 1ul N60/E
A2I4UWE2	4 port 2-pos int vol valve air act/2in so	1/8 x .75mm 175C/1000psi liq 2ul N60/E
A2NI4WE.06	4 port 2-pos int vol valve air act/2in so	1/32 x .25mm 175C/1000psi liq .06ulN60/E
A2NI4WE.1	4 port 2-pos int vol valve air act/2in so	1/32 x .25mm 175C/1000psi liq .1ulN60/E
A2NI4WE.2	4 port 2-pos int vol valve air act/2in so	1/32 x .25mm 175C/1000psi liq .2ulN60/E
A2NI4WE.5	4 port 2-pos int vol valve air act/2in so	1/32 x .25mm 175C/1000psi liq .5ulN60/E
A2SC10MWE	10 mpos common outlet path MW air act/2in so	1/8 x 1mm 200C/200psi gas N60/E
A2SC12MWE	12 mpos common outlet path MW air act/2in so	1/8 x 1mm 200C/200psi gas N60/E
A2SC16MWE	16 mpos common outlet path MW air act/2in so	1/8 x 1mm 200C/200psi gas N60/E
A2SC6MWE	OBSOLETE USE AH2SC6MWE	
A2SD10MWE	10 mpos dead-end path MW air act/2in so	1/8 x 1mm 200C/200psi gas N60/E
A2SD12MWE	12 mpos dead-end path MW air act/2in so	1/8 x 1mm 200C/200psi gas N60/E
A2SD16MWE	16 mpos dead-end path MW air act/2in so	1/8 x 1mm 200C/200psi gas N60/E
A2SD6MWE	6 mpos dead-end path MW air act/2in so	1/8 x 1mm 200C/400psi gas N60/E
A2SF10MWE	10 mpos flow-through MW air act/2in so	1/8 x 1mm 200C/200psi gas N60/E
A2SF12MWE	12 mpos flow-through MW air act/2in so	1/8 x 1mm 200C/200psi gas N60/E
A2SF16MWE	16 mpos flow-through MW air act/2in so	1/8 x 1mm 200C/200psi gas N60/E
A2SF6MWE	OBSOLETE USE AH2SF6MWE	
A2ST10MWE	10 mpos trapping path MW air act high torq./2in so	1/8 x 1mm 200C/200psi gas N60/E
A2ST12MWE	12 mpos trapping path MW air act high torq./2in so	1/8 x 1mm 200C/200psi gas N60/E
A2ST16MWE	16 mpos trapping path MW air act high torq./2in so	1/8 x 1mm 200C/200psi gas N60/E
A2ST6MWE	OBSOLETE USE AH2ST6MWE	
A2STF10MWE	10 mpos trap/flow path MW air act high t./2in so	1/8 x 1mm 200C/200psi gas N60/E
A2STF12MWE	12 mpos trap/flow path MW air act high t./2in so	1/8 x 1mm 200C/200psi gas N60/E