

VICIValco-Cheminert PRODUCT LIST 2012

(Ctrl F)
> Cat.#s

> Current System AUD Prices



A2STF16MWE	16 mpos trap/flow path MW air act high t./2in so	1/8 x 1mm 200C/200psi gas N60/E
A2STF6MWE	OBSOLETE USE AH2STF6MWE	
A2VLSC8MWE2	OBSOLETE USE AH2VLSC8MWE2	
A30	Air actuator 2-pos close mount	30 deg rotation
A304	Air actuator 2-pos 4in standoff	30 deg rotation
A30S	Air actuator 2-pos for standoff	30 deg rotation
A36	Air actuator 2-pos close mount	36 deg rotation
A364	Air actuator 2-pos 4in standoff	36 deg rotation
A36S	Air actuator 2-pos for standoff	36 deg rotation
A4	Air actuator 4 mpos close mount	90 deg rotation
A410UWE	10 port 2-pos valve air actuated/4in so	1/8 x .75mm 225C/400psi gas N60/E
A410UWT	10 port 2-pos valve air actuated/4in so	1/8 x .75mm 330C/300psi gas N60/T
A42	Air actuator 4 mpos 2in standoff	90 deg rotation
A44UWE	4 port 2-pos valve air actuated/4in so	1/8 x .75mm 225C/400psi gas N60/E
A44UWT	4 port 2-pos valve air actuated/4in so	1/8 x .75mm 330C/300psi gas N60/T
A45	Air actuator 2-pos close mount	45 deg rotation
A454	Air actuator 2-pos 4in standoff	45 deg rotation
A45S	Air actuator 2-pos for standoff	45 deg rotation
A46UWE	6 port 2-pos valve air actuated/4in so	1/8 x .75mm 225C/400psi gas N60/E
A46UWT	6 port 2-pos valve air actuated/4in so	1/8 x .75mm 330C/300psi gas N60/T
A48UWE	8 port 2-pos valve air actuated/4in so	1/8 x .75mm 225C/400psi gas N60/E
A48UWT	8 port 2-pos valve air actuated/4in so	1/8 x .75mm 330C/300psi gas N60/T
A4C10UWE	10 port 2-pos valve air actuated/4in so	1/16 x .75mm 225C/400psi gas N60/E
A4C10UWT	10 port 2-pos valve air actuated/4in so	1/16 x .75mm 330C/300psi gas N60/T
A4C10WE	10 port 2-pos valve air actuated/4in so	1/16 x .4mm 225C/400psi gas N60/E
A4C10WT	10 port 2-pos valve air actuated/4in so	1/16 x .4mm 350C/300psi gas N60/T
A4C4UWE	4 port 2-pos valve air actuated/4in so	1/16 x .75mm 225C/400psi gas N60/E
A4C4UWT	4 port 2-pos valve air actuated/4in so	1/16 x .75mm 330C/300psi gas N60/T
A4C4WE	4 port 2-pos valve air actuated/4in so	1/16 x .4mm 225C/400psi gas N60/E
A4C4WT	4 port 2-pos valve air actuated/4in so	1/16 x .4mm 350C/300psi gas N60/T
A4C6UWE	6 port 2-pos valve air actuated/4in so	1/16 x .75mm 225C/400psi gas N60/E
A4C6UWT	6 port 2-pos valve air actuated/4in so	1/16 x .75mm 330C/300psi gas N60/T
A4C6WE	6 port 2-pos valve air actuated/4in so	1/16 x .4mm 225C/400psi gas N60/E
A4C6WT	6 port 2-pos valve air actuated/4in so	1/16 x .4mm 350C/300psi gas N60/T
A4C8UWE	8 port 2-pos valve air actuated/4in so	1/16 x .75mm 225C/400psi gas N60/E
A4C8UWT	8 port 2-pos valve air actuated/4in so	1/16 x .75mm 330C/300psi gas N60/T
A4C8WE	8 port 2-pos valve air actuated/4in so	1/16 x .4mm 225C/400psi gas N60/E
A4C8WT	8 port 2-pos valve air actuated/4in so	1/16 x .4mm 350C/300psi gas N60/T
A4N10WE	10 port 2-pos valve air actuated/4in so	1/32 x .25mm 225C/400psi gas N60/E
A4N10WT	10 port 2-pos valve air actuated/4in so	1/32 x .25mm 350C/300psi gas N60/T
A4N4WE	4 port 2-pos valve air actuated/4in so	1/32 x .25mm 225C/400psi gas N60/E
A4N4WT	4 port 2-pos valve air actuated/4in so	1/32 x .25mm 350C/300psi gas N60/T
A4N6WE	6 port 2-pos valve air actuated/4in so	1/32 x .25mm 225C/400psi gas N60/E
A4N6WT	6 port 2-pos valve air actuated/4in so	1/32 x .25mm 350C/300psi gas N60/T
A4N8WE	8 port 2-pos valve air actuated/4in so	1/32 x .25mm 225C/400psi gas N60/E
A4N8WT	8 port 2-pos valve air actuated/4in so	1/32 x .25mm 350C/300psi gas N60/T
A4S	Air actuator 4 mpos for standoff	90 deg rotation
A4UW	4 port 2-pos valve air actuated	1/8 x .75mm 75C/5000psi liq N60/H
A4VL4MWE2	4 port 2-pos valve MW air act/4in so	1/4 x 4mm 75C/100psi gas N60/E2
A4VL6MWE2	6 port 2-pos valve MW air act/4in so	1/4 x 4mm 75C/100psi gas N60/E2
A4VL8MWE2	8 port 2-pos valve MW air act/4in so	1/4 x 4mm 75C/100psi gas N60/E2
A6	Air actuator 6 mpos close mount	60 deg rotation
A60	Air actuator 2-pos close mount	60 deg rotation
A604	Air actuator 2-pos 4in standoff	60 deg rotation
A60S	Air actuator 2-pos for standoff	60 deg rotation
A62	Air actuator 6 mpos 2in standoff	60 deg rotation
A6S	Air actuator 6 mpos for standoff	60 deg rotation
A6UW	6 port 2-pos valve air actuated	1/8 x .75mm 75C/5000psi liq N60/H
A8	Air actuator 8 mpos close mount	45 deg rotation
A82	Air actuator 8 mpos 2in standoff	45 deg rotation
A8S	Air actuator 8 mpos for standoff	45 deg rotation