

VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]
> CatL#s

> Current System AUD Prices



A8UW	8 port 2-pos valve air actuated	1/8 x .75mm 75C/5000psi liq N60/H
A90	Air actuator 2-pos close mount	90 deg rotation
A904	Air actuator 2-pos 4in standoff	90 deg rotation
A90S	Air actuator 2-pos for standoff	90 deg rotation
AC10UW	10 port 2-pos valve air actuated	1/16 x .75mm 75C/5000psi liq N60/H
AC10W	10 port 2-pos valve air actuated	1/16 x .4mm 75C/5000psi liq N60/H
AC4UW	4 port 2-pos valve air actuated	1/16 x .75mm 75C/5000psi liq N60/H
AC4W	4 port 2-pos valve air actuated	1/16 x .4mm 75C/5000psi liq N60/H
AC6UW	6 port 2-pos valve air actuated	1/16 x .75mm 75C/5000psi liq N60/H
AC6W	6 port 2-pos valve air actuated	1/16 x .4mm 75C/5000psi liq N60/H
AC8UW	8 port 2-pos valve air actuated	1/16 x .75mm 75C/5000psi liq N60/H
AC8W	8 port 2-pos valve air actuated	1/16 x .4mm 75C/5000psi liq N60/H
ACI4UW.2	4 port 2-pos int vol valve air actuated	1/16 x .75mm 75C/5000psi liq .2ul N60/H
ACI4UW.5	4 port 2-pos int vol valve air actuated	1/16 x .75mm 75C/5000psi liq .5ul N60/H
ACI4UW1	4 port 2-pos int vol valve air actuated	1/16 x .75mm 75C/5000psi liq 1ul N60/H
ACI4UW2	4 port 2-pos int vol valve air actuated	1/16 x .75mm 75C/5000psi liq 2ul N60/H
ACI4W.06	4 port 2-pos int vol valve air actuated	1/16 x .4mm 75C/5000psi liq .06ul N60/H
ACI4W.1	4 port 2-pos int vol valve air actuated	1/16 x .4mm 75C/5000psi liq .1ul N60/H
ACI4W.2	4 port 2-pos int vol valve air actuated	1/16 x .4mm 75C/5000psi liq .2ul N60/H
ACI4W.5	4 port 2-pos int vol valve air actuated	1/16 x .4mm 75C/5000psi liq .5ul N60/H
ACSD10UW	10 mpos dead-end path air actuated	1/16 x .4mm 75C/5000psi liq N60/E
ACSD4UW	OBSOLETE USE AHCS4UW	1/16 x .4mm 75C/5000psi liq N60/E
ACSD6UW	OBSOLETE USE AHCS6UW	1/16 x 1mm 200C/200psi gas N60/E
ACST4UW	4 mpos trapping path air actuated	1/16 x 1mm 200C/200psi gas N60/E
ACST6UW	6 mpos trapping path air actuated	1/16 x .75mm 200C/200psi gas N60/E
AH2CSC6MWE	6 mpos common outlet pathMW/air act.high tor/2in so	1/16 x .75mm 200C/200psi gas N60/E
AH2CSF6MWE	6 mpos flow-through MW air act high torq./2in so	1/8 x 1mm 200C/200psi gas N60/E
AH2CST6MWE	6 mpos trapping path MW air act high torq./2in so	1/8 x 1mm 200C/200psi gas N60/E
AH2CSTF6MWE	6 mpos trap/flow path MW air act high t./2in so	1/8 x 1mm 200C/200psi gas N60/E
AH2SC6MWE	6 mpos common outlet pathMWair act high tor/2in so	1/4 x 4mm 75C/100psi gas N60/E2
AH2SF6MWE	6 mpos flow-through MW air act high torq./2in so	1/4 x 4mm 75C/100psi gas N60/E2
AH2ST6MWE	6 mpos trapping path MW air act high torq./2in so	1/4 x 4mm 75C/100psi gas N60/E2
AH2STF6MWE	6 mpos trap/flow path MW air act high t./2in so	1/4 x 4mm 75C/100psi gas N60/E2
AH2VLS4MWE2	4 mpos common outlet path MW air act/2in so	1/4 x 4mm 75C/100psi gas N60/E2
AH2VLS6MWE2	6 mpos common outlet path MW air act/2in so	1/4 x 4mm 75C/100psi gas N60/E2
AH2VLS8MWE2	8 mpos common outlet path MW air act/2in so	1/4 x 4mm 75C/100psi gas N60/E2
AH2VLS10MWE2	10 mpos dead-end path MW air act/2in so	1/4 x 4mm 75C/100psi gas N60/E2
AH2VLS4MWE2	4 mpos dead-end path MW air act/2in so	1/4 x 4mm 75C/100psi gas N60/E2
AH2VLS6MWE2	6 mpos dead-end path MW air act/2in so	1/4 x 4mm 75C/100psi gas N60/E2
AH2VLS8MWE2	8 mpos dead-end path MW air act/2in so	1/4 x 4mm 75C/100psi gas N60/E2
AH2VLSF4MWE2	4 mpos flow-through MW air act/2in so	1/4 x 4mm 75C/100psi gas N60/E2
AH2VLSF6MWE2	6 mpos flow-through MW air act/2in so	1/4 x 4mm 75C/100psi gas N60/E2
AH2VLSF8MWE2	8 mpos flow-through MW air act/2in so	1/4 x 4mm 75C/100psi gas N60/E2
AHCS4UW	4 mpos dead-end path air actuated high torque	1/16 x .4mm 75C/5000psi liq N60/E
AHCS6UW	6 mpos dead-end path air actuated hi torque	1/16 x .4mm 75C/5000psi liq N60/E
AHSD4UW	4 mpos dead-end path air actuated high torque	1/8 x .75mm 75C/5000psi liq N60/E
AHSD6UW	6 mpos dead-end path air actuated high torque	1/8 x .75mm 75C/5000psi liq N60/E
AL10UW	10 port 2-pos valve air actuated	1/8 x 1.0mm 75C/5000psi liq N60/H
AL4UW	4 port 2-pos valve air actuated	1/8 x 1.7mm 75C/5000psi liq N60/H
AL6UW	6 port 2-pos valve air actuated	1/8 x 1.7mm 75C/5000psi liq N60/H
AL8UW	8 port 2-pos valve air actuated	1/8 x 1.3mm 75C/5000psi liq N60/H
ASD4UW	OBSOLETE USE AHSD4UW	
ASD6UW	OBSOLETE USE AHSD6UW	
ASD8UW	8 mpos dead-end path air actuated	1/8 x .75mm 75C/5000psi liq N60/E
ASFV	Prime/Purge valve air actuated/1in so	3 x 1/16in .50 mm 100C/10'000psi SS
ASFV2HT	Prime/Purge valve air actuated/1in so	3 x 1/8in 1.50 mm 300C/2'000psi SS
ASFV2HT4	Prime/Purge valve air actuated/4in so	3 x 1/8in 1.50 mm 300C/2'000psi SS
ASFV40K.5	Prime/purge valve air actuated/1.625in so	3 x 1/32in .15 mm bore 50C/40'000 psi SS
ASFV40K1	Prime/purge valve air actuated/1.625in so	3 x 1/16" .15 mm bore 50C/40'000 psi SS
ASFV40K360	Prime/purge valve air actuated/1.625in so	3 x 360um .15 mm bore 50C/40'000 psi SS
ASFVHT	Prime/Purge valve air actuated/1in so	3 x 1/16in .50 mm 300C/6'000psi SS