

VICIValco-Cheminert PRODUCT LIST 2012

(Ctrl F)
> Cat.#s

> Current System AUD Prices



ASFVHT4	Prime/Purge valve air actuated/4in so	3 x 1/16in .50 mm 300C/6'000psi SS
ASFVL	Prime/Purge valve air actuated/1in so	3 x 1/16in .75 mm 100C/10'000psi SS
ASFVLHT	Prime/Purge valve air actuated/1in so	3 x 1/16in .75 mm 300C/6'000psi SS
ASFVLHT4	Prime/Purge valve air actuated/4in so	3 x 1/16in .75 mm 300C/6'000psi SS
ASFVO	On/Off valve air actuated/1in so	2 x 1/16in .50 mm bore 100C/10'000 psi SS
ASFVO2HT	On/Off valve air actuated/1in so	2 x 1/8in 1.50 mm bore 300C/2'000 psi SS
ASFVO2HT4	On/Off valve air actuated 4in so	2 x 1/8in 1.50 mm bore 300C/2'000 psi SS
ASFVO40K.5	On/Off valve air actuated/1.625in so	2 x 1/32in .15 mm bore 50C/40'000 psi SS
ASFVO40K1	On/Off valve air actuated/1.625in so	2 x 1/16" .15 mm bore 50C/40'000 psi SS
ASFVO40K360	On/Off valve air actuated/1.625in so	2 x 360um .15 mm bore 50C/40'000 psi SS
ASFVOD40K.5	Dual On/Off valve air actuated/1.625in so	3 x 1/32in .15 mm bore 50C/40'000 psi SS
ASFVOD40K1	Dual On/Off valve air actuated/1.625in so	3 x 1/16in .15 mm bore 50C/40'000 psi SS
ASFVOD40K360	Dual On/Off valve air actuated/1.625in so	3 x 360um .15 mm bore 50C/40'000 psi SS
ASFVOHT	On/Off valve air actuated/1in so	2 x 1/16in .50 mm bore 300C/6'000 psi SS
ASFVOHT4	On/Off valve air actuated 4in so	2 x 1/16in .50 mm bore 300C/6'000psi SS
ASFVOL	On/Off valve air actuated/1in so	2 x 1/16in .75 mm bore 100C/10'000 psi SS
ASFVOLHT	On/Off valve air actuated/1in so	2 x 1/16in .75 mm bore 300C/6'000 psi SS
ASFVOLHT4	On/Off valve air actuated 4in so	2 x 1/16in .75 mm bore 300C/6'000 psi SS
AT10	Air actuator 10 mpos high T close mount	36 deg rotation
AT104	Air actuator 10 mpos high T 4in standoff	36 deg rotation
AT10S	Air actuator 10 mpos high T for standoff	36 deg rotation
AT12	Air actuator 12 mpos high T close mount	30 deg rotation
AT124	Air actuator 12 mpos high T 4in standoff	30 deg rotation
AT12S	Air actuator 12 mpos high T for standoff	30 deg rotation
AT16	Air actuator 16 mpos high T close mount	22.5 deg rotation
AT164	Air actuator 16 mpos high T 4in standoff	22.5 deg rotation
AT16S	Air actuator 16 mpos high T for standoff	22.5 deg rotation
AT30	Air actuator 2-pos high T close mount	30 deg rotation
AT302	Air actuator 2-pos high T 2in standoff	30 deg rotation
AT30S	Air actuator 2-pos high T for standoff	30 deg rotation
AT36	Air actuator 2-pos high T close mount	36 deg rotation
AT362	Air actuator 2-pos high T 2in standoff	36 deg rotation
AT36S	Air actuator 2-pos high T for standoff	36 deg rotation
AT4	Air actuator 4 mpos high T close mount	90 deg rotation
AT44	Air actuator 4 mpos high T 4in standoff	90 deg rotation
AT45	Air actuator 2-pos high T close mount	45 deg rotation
AT452	Air actuator 2-pos high T 2in standoff	45 deg rotation
AT45S	Air actuator 2-pos high T for standoff	45 deg rotation
AT4S	Air actuator 4 mpos high T for standoff	90 deg rotation
AT6	Air actuator 6 mpos high T close mount	60 deg rotation
AT60	Air actuator 2-pos high T close mount	60 deg rotation
AT602	Air actuator 2-pos high T 2in standoff	60 deg rotation
AT60S	Air actuator 2-pos high T for standoff	60 deg rotation
AT64	Air actuator 6 mpos high T 4in standoff	60 deg rotation
AT6S	Air actuator 6 mpos high T for standoff	60 deg rotation
AT8	Air actuator 8 mpos high T close mount	45 deg rotation
AT84	Air actuator 8 mpos high T 4in standoff	45 deg rotation
AT8S	Air actuator 8 mpos high T for standoff	45 deg rotation
AT90	Air actuator 2-pos high T close mount	90 deg rotation
AT902	Air actuator 2-pos high T 2in standoff	90 deg rotation
AT90S	Air actuator 2-pos high T for standoff	90 deg rotation
BNV1	Micrometering needle valve bulkhead 2-225 ml/min	1/16in tube18in /45cm2um frit 225Clubr. SS/Viton
BNV1-D	Micrometering needle valve bulkhead 2-225 ml/min	1/16in tube18in /45cmnon-lubricated225C SS/Viton
BNV1-KZ	Micrometering needle valve bulkhead 2-225 ml/min	1/16in tube 18in /45cmnon-lubricated315CSS/Kalrez
BNV1LF	Micrometering needle valve bulkhead 2-90 ml/min	1/16in tube18in /45cm2um frit225Clubr. SS/Viton
BNV1LF-D	Micrometering needle valve bulkhead 2-90 ml/min	1/16in tube18in /45cm2um frit225Cnon-lubr.SS/Viton
BNV1LF-KZ	Micrometering needle valve bulkhead 2-90 ml/min	1/16in tube18in /45cm2um frit315Cnon-lub.SS/Kalrez
C10UW	!!! RECOMMEND 2C10UW	SUPPLIED WITH LARGER HANDLE
C10UWE	10 port 2-pos valve manual	1/16 x .75mm 225C/400psi gas N60/E
C10W	10 port 2-pos valve manual	1/16 x .4mm 75C/5000psi liq N60/H
C10WE	10 port 2-pos valve manual	1/16 x .4mm 225C/400psi gas N60/E