

VICIValco-Cheminert PRODUCT LIST 2012

(Ctrl F)
> Cat.#s

> Current System AUD Prices



C1-1006	6 port 2-pos vlv man/front loading+PFC	1/16 x .25mm 75C/5000psi liq N60/H
C1-10R6	Rotor seal 6 port 2-pos valve	1/16 x .25mm 75C/5000psi liq H
C1-1346	6 port 2-pos vlv man/front loading+PFC	1/16 x .25mm 50C/5000psi liq PAEK/E
C1-13R6	Rotor seal 6 port 2-pos valve	1/16 x .25mm 75C/5000psi liq E
C1-2006	6 port 2-pos vlv man/front loading+PFC	1/16 x .4mm 75C/5000psi liq N60/H
C12-310	Rotor seal 10 port 2-pos C22/C22Z-valve	1/16 x .75mm tube 75C/250psi liq E2
C12-314	Rotor seal 4 port 2-pos C22/C22Z-valve	1/16 x .75mm tube 75C/250psi liq E2
C12-316	Rotor seal 6 port 2-pos C22/C22Z-valve	1/16 x .75mm tube 75C/250psi liq E2
C12-318	Rotor seal 8 port 2-pos C22/C22Z-valve	1/16 x .75mm tube 75C/250psi liq E2
C1-2346	6 port 2-pos vlv man/front loading+PFC	1/16 x .4mm 50C/5000psi liq PAEK/E
C1-23R6	Rotor seal 6 port 2-pos valve PAEK	1/16 x .4mm 50C/5000psi liq E
C15-310	Rotor seal mpos dead-end path C15/C25Z-v	1/16 x .75mm 75C/250psi liq E2
C-1C00H	Stator 10 port 2-pos (.180BC) C2-valve	1/16 x .25mm N60
C-1C04	Stator 4 port 2-pos C2-valve	1/16 x .25mm N60
C-1C06	Stator 6 port 2-pos C2-valve	1/16 x .25mm N60
C-1C08H	Stator 8 port 2-pos (.180BC) C2-valve	1/16 x .25mm N60
C-1C30H	Stator 10 port 2-pos (.180BC) C2-valve	1/16 x .25mm Ti
C-1C34	Stator 4 port 2-pos C2-valve	1/16 x .25mm Ti
C-1C36	Stator 6 port 2-pos C1/C2-valve	1/16 x .25mm Ti
C-1C38H	Stator 8 port 2-pos (.180BC) C2-valve	1/16 x .25mm Ti
C-1C40H	Stator 10 port 2-pos (.180BC) C2-valve	1/16 x .25mm PAEK
C-1C44	Stator 4 port 2-pos C2-valve	1/16 x .25mm PAEK
C-1C46	Stator 6 port 2-pos C1/C2-valve	1/16 x .25mm PAEK
C-1C48H	Stator 8 port 2-pos (.180) C2-valve	1/16 x .25mm PAEK
C1CF-1006	6 port 2-pos vlv man/front loading cont flow+PFC	1/16 x .25mm 75C/5000psi liq N60/H
C1CF-1346	6 port 2-pos vlv man/front loading cont flow+PFC	1/16 x .25mm 50C/5000psi liq PAEK/E
C1CF-2006	6 port 2-pos vlv man/front loading cont flow+PFC	1/16 x .4mm 75C/5000psi liq N60/H
C1CF-2346	6 port 2-pos vlv man/front loading cont flow+PFC	1/16 x .4mm 75C/5000psi liq PAEK/E
C2-1004	4 port 2-pos valve manual	1/16 x .25mm 75C/5000psi liq N60/H
C2-1004A	4 port 2-pos valve air actuated	1/16 x .25mm 75C/5000psi liq N60/H
C2-1004D	4 port 2-pos valve replacement	1/16 x .25mm 75C/5000psi liq N60/H
C2-1004E	4 port 2-pos valve std-electric	1/16 x .25mm 75C/5000psi liq N60/H
C2-1004EH	4 port 2-pos valve m-electric	1/16 x .25mm 75C/5000psi liq N60/H
C2-1006	6 port 2-pos valve manual	1/16 x .25mm 75C/5000psi liq N60/H
C2-1006A	6 port 2-pos valve air actuated	1/16 x .25mm 75C/5000psi liq N60/H
C2-1006D	6 port 2-pos valve replacement	1/16 x .25mm 75C/5000psi liq N60/H
C2-1006E	6 port 2-pos valve std-electric	1/16 x .25mm 75C/5000psi liq N60/H
C2-1006EH	6 port 2-pos valve m-electric	1/16 x .25mm 75C/5000psi liq N60/H
C2-1034	4 port 2-pos valve manual	1/16 x .25mm 75C/5000psi liq Ti/H
C2-1034A	4 port 2-pos valve air actuated	1/16 x .25mm 75C/5000psi liq Ti/H
C2-1034D	4 port 2-pos valve replacement	1/16 x .25mm 75C/5000psi liq Ti/H
C2-1034E	4 port 2-pos valve std-electric	1/16 x .25mm 75C/5000psi liq Ti/H
C2-1034EH	4 port 2-pos valve m-electric	1/16 x .25mm 75C/5000psi liq Ti/H
C2-1036	6 port 2-pos valve manual	1/16 x .25mm 75C/5000psi liq Ti/H
C2-1036A	6 port 2-pos valve air actuated	1/16 x .25mm 75C/5000psi liq Ti/H
C2-1036D	6 port 2-pos valve replacement	1/16 x .25mm 75C/5000psi liq Ti/H
C2-1036E	6 port 2-pos valve std-electric	1/16 x .25mm 75C/5000psi liq Ti/H
C2-1036EH	6 port 2-pos valve m-electric	1/16 x .25mm 75C/5000psi liq Ti/H
C2-10R0H	Rotor seal 10 port 2-pos (.180BC) C2-valve	1/16 x .25mm 75C/5000psi liq H
C2-10R4	Rotor seal 4 port 2-pos C2-valve	1/16 x .25mm 75C/5000psi liq H
C2-10R6	Rotor seal 6 port 2-pos C2/C3-valve	1/16 x .25mm 75C/5000psi liq H
C2-10R8H	Rotor seal 8 port 2-pos (.180BC) C2-valve	1/16 x .25mm 75C/5000psi liq H
C2-1344	4 port 2-pos valve manual	1/16 x .25mm 50C/5000psi liq PAEK/E
C2-1344A	4 port 2-pos valve air actuated	1/16 x .25mm 50C/5000psi liq PAEK/E
C2-1344D	4 port 2-pos valve replacement	1/16 x .25mm 50C/5000psi liq PAEK/E
C2-1344E	4 port 2-pos valve std-electric	1/16 x .25mm 50C/5000psi liq PAEK/E
C2-1344EH	4 port 2-pos valve m-electric	1/16 x .25mm 50C/5000psi liq PAEK/E
C2-1346	6 port 2-pos valve manual	1/16 x .25mm 50C/5000psi liq PAEK/E
C2-1346A	6 port 2-pos valve air actuated	1/16 x .25mm 50C/5000psi liq PAEK/E
C2-1346D	6 port 2-pos valve replacement	1/16 x .25mm 50C/5000psi liq PAEK/E
C2-1346E	6 port 2-pos valve std-electric	1/16 x .25mm 50C/5000psi liq PAEK/E