

VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]
> Cat.#s

> Current System AUD Prices



C2-1346EH	6 port 2-pos valve m-electric	1/16 x .25mm 50C/5000psi liq PAEK/E
C2-13R0H	Rotor seal 10 port 2-pos C2-valve (B.C.180)	1/16 x .25mm 50C/5000psi liq E
C2-13R4	Rotor seal 4 port 2-pos C2-valve	1/16 x .25mm 50C/5000psi liq E
C2-13R6	Rotor seal 6 port 2-pos C2/C3-valve	1/16 x .25mm 50C/5000psi liq E
C2-13R8H	Rotor seal 8 port 2-pos (.180BC) C2-valve	1/16 x .25mm 50C/5000psi liq E
C2-2004	4 port 2-pos valve manual	1/16 x .4mm 75C/5000psi liq N60/H
C2-2004A	4 port 2-pos valve air act	1/16 x .4mm 75C/5000psi liq N60/H
C2-2004D	4 port 2-pos valve replacement	1/16 x .4mm 75C/5000psi liq N60/H
C2-2004E	4 port 2-pos valve std-elect	1/16 x .4mm 75C/5000psi liq N60/H
C2-2004EH	4 port 2-pos valve m-elect	1/16 x .4mm 75C/5000psi liq N60/H
C2-2006	6 port 2-pos valve manual	1/16 x .4mm 75C/5000psi liq N60/H
C2-2006A	6 port 2-pos valve air act	1/16 x .4mm 75C/5000psi liq N60/H
C2-2006D	6 port 2-pos valve replacement	1/16 x .4mm 75C/5000psi liq N60/H
C2-2006E	6 port 2-pos valve std-elect	1/16 x .4mm 75C/5000psi liq N60/H
C2-2006EH	6 port 2-pos valve m-elect	1/16 x .4mm 75C/5000psi liq N60/H
C2-2034	4 port 2-pos valve manual	1/16 x .4mm 75C/5000psi liq Ti/H
C2-2034A	4 port 2-pos valve air act	1/16 x .4mm 75C/5000psi liq Ti/H
C2-2034D	4 port 2-pos valve replacement	1/16 x .4mm 75C/5000psi liq Ti/H
C2-2034E	4 port 2-pos valve std-elect	1/16 x .4mm 75C/5000psi liq Ti/H
C2-2034EH	4 port 2-pos valve m-elect	1/16 x .4mm 75C/5000psi liq Ti/H
C2-2036	6 port 2-pos valve manual	1/16 x .4mm 75C/5000psi liq Ti/H
C2-2036A	6 port 2-pos valve air act	1/16 x .4mm 75C/5000psi liq Ti/H
C2-2036D	6 port 2-pos valve replacement	1/16 x .4mm 75C/5000psi liq Ti/H
C2-2036E	6 port 2-pos valve std-elect	1/16 x .4mm 75C/5000psi liq Ti/H
C2-2036EH	6 port 2-pos valve m-elect	1/16 x .4mm 75C/5000psi liq Ti/H
C2-20R0H	Rotor seal 10 port 2-pos (.180BC) C2-valve	1/16 x .4mm 75C/5000psi liq H
C2-20R4	Rotor seal 4 port 2-pos C2-valve	1/16 x .4mm 75C/5000psi liq H
C2-20R6	Rotor seal 6 port 2-pos C2/C3-valve	1/16 x .4mm 75C/5000psi liq H
C2-20R8H	Rotor seal 8 port 2-pos (.180BC) C2-valve	1/16 x .4mm (.180 BC) 75C/5000psi liq H
C22-310	Rotor seal 10 port 2-pos C12/C22Z-valve	1/4in -28 x .75mm 75C/250psi liq E2
C22-314	Rotor seal 4 port 2-pos C22-valve	1/4in -28 x .75mm 75C/250psi liq E2
C22-316	Rotor seal 6 port 2-pos C22-valve	1/4in -28 x .75mm 75C/250psi liq E2
C22-318	Rotor seal 8 port 2-pos C12/C22Z-valve	1/4in -28 x .75mm 75C/250psi liq E2
C22-3180	10 port 2-pos valve manual	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C22-3180A	10 port 2-pos valve air actuated	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C22-3180D	10 port 2-pos valve replacement	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C22-3180E	10 port 2-pos valve std-electric	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C22-3180EH	10 port 2-pos valve m-electric	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C22-3184	4 port 2-pos valve manual	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C22-3184A	4 port 2-pos valve air actuated	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C22-3184D	4 port 2-pos valve replacement	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C22-3184E	4 port 2-pos valve std-electric	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C22-3184EH	4 port 2-pos valve m-electric	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C22-3186	6 port 2-pos valve manual	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C22-3186A	6 port 2-pos valve air actuated	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C22-3186D	6 port 2-pos valve replacement	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C22-3186E	6 port 2-pos valve std-electric	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C22-3186EH	6 port 2-pos valve m-electric	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C22-3188	8 port 2-pos valve manual	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C22-3188A	8 port 2-pos valve air actuated	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C22-3188D	8 port 2-pos valve replacement	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C22-3188E	8 port 2-pos valve std-electric	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C22-3188EH	8 port 2-pos valve m-electric	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C2-2344	4 port 2-pos valve manual	1/16 x .4mm 50C/5000psi liq PAEK/E
C2-2344A	4 port 2-pos valve air act	1/16 x .4mm 50C/5000psi liq PAEK/E
C2-2344D	4 port 2-pos valve replacement	1/16 x .4mm 50C/5000psi liq PAEK/E
C2-2344E	4 port 2-pos valve std-elect	1/16 x .4mm 50C/5000psi liq PAEK/E
C2-2344EH	4 port 2-pos valve m-elect	1/16 x .4mm 50C/5000psi liq PAEK/E
C2-2346	6 port 2-pos valve manual	1/16 x .4mm 50C/5000psi liq PAEK/E
C2-2346A	6 port 2-pos valve air act	1/16 x .4mm 50C/5000psi liq PAEK/E
C2-2346D	6 port 2-pos valve replacement	1/16 x .4mm 50C/5000psi liq PAEK/E