

VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]
> CatL#s

> Current System AUD Prices



C2-2346E	6 port 2-pos valve std-elect	1/16 x .4mm 50C/5000psi liq PAEK/E
C2-2346EH	6 port 2-pos valve m-elect	1/16 x .4mm 50C/5000psi liq PAEK/E
C22-380	Stator 10 port 2-pos C22-valve	1/4in -28 x .75mm 75C/250psi liq PPS
C22-384	Stator 4 port 2-pos C22-valve	1/4in -28 x .75mm 75C/250psi liq PPS
C22-386	Stator 6 port 2-pos C22-valve	1/4in -28 x .75mm 75C/250psi liq PPS
C22-388	Stator 8 port 2-pos C22-valve	1/4in -28 x .75mm 75C/250psi liq PPS
C2-23R0H	Rotor seal 10 port 2-pos (.180BC) C2-valve	1/16 x .4mm 50C/5000psi liq E
C2-23R4	Rotor seal 4 port 2-pos C2-valve	1/16 x .4mm 50C/5000psi liq E
C2-23R6	Rotor seal 6 port 2-pos C2/C3-valve	1/16 x .4mm 50C/5000psi liq E
C2-23R8H	Rotor seal 8 port 2-pos (.180BC) C2-valve	1/16 x .4mm(.180 BC) 50C/5000psi liq E
C22-610	Rotor seal 10 port 2-pos C22-valve	1/4in -28 x 1.5mm 75C/250psi liq E2
C22-614	Rotor seal 4 port 2-pos C22-valve	1/4in -28 x 1.5mm 75C/250psi liq E2
C22-616	Rotor seal 6 port 2-pos C22-valve	1/4in -28 x 1.5mm 75C/250psi liq E2
C22-618	Rotor seal 8 port 2-pos C22-valve	1/4in -28 x 1.5mm 75C/250psi liq E2
C22-6180	10 port 2-pos valve manual	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C22-6180A	10 port 2-pos valve air actuated	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C22-6180D	10 port 2-pos valve replacement	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C22-6180E	10 port 2-pos valve std-electric	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C22-6180EH	10 port 2-pos valve m-electric	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C22-6184	4 port 2-pos valve manual	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C22-6184A	4 port 2-pos valve air actuated	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C22-6184D	4 port 2-pos valve replacement	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C22-6184E	4 port 2-pos valve std-electric	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C22-6184EH	4 port 2-pos valve m-electric	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C22-6186	6 port 2-pos valve manual	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C22-6186A	6 port 2-pos valve air actuated	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C22-6186D	6 port 2-pos valve replacement	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C22-6186E	6 port 2-pos valve std-electric	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C22-6186EH	6 port 2-pos valve m-electric	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C22-6188	8 port 2-pos valve manual	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C22-6188A	8 port 2-pos valve air actuated	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C22-6188D	8 port 2-pos valve replacement	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C22-6188E	8 port 2-pos valve std-electric	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C22-6188EH	8 port 2-pos valve m-electric	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C22-680	Stator 10 port 2-pos C22-valve	1/4in -28 x 1.5mm 75C/250psi liq PPS
C22-684	Stator 4 port 2-pos C22-valve	1/4in -28 x 1.5mm 75C/250psi liq PPS
C22-686	Stator 6 port 2-pos C22-valve	1/4in -28 x 1.5mm 75C/250psi liq PPS
C22-688	Stator 8 port 2-pos C22-valve	1/4in -28 x 1.5mm 75C/250psi liq PPS
C22Z-3180	10 port 2-pos valve manual	1/16 x .75mm 75C/250psi liq PPS/E2
C22Z-3180A	10 port 2-pos valve air actuated	1/16 x .75mm 75C/250psi liq PPS/E2
C22Z-3180D	10 port 2-pos valve replacement	1/16 x .75mm 75C/250psi liq PPS/E2
C22Z-3180E	10 port 2-pos valve std-electric	1/16 x .75mm 75C/250psi liq PPS/E2
C22Z-3180EH	10 port 2-pos valve m-electric	1/16 x .75mm 75C/250psi liq PPS/E2
C22Z-3184	4 port 2-pos valve manual	1/16 x .75mm 75C/250psi liq PPS/E2
C22Z-3184A	4 port 2-pos valve air actuated	1/16 x .75mm 75C/250psi liq PPS/E2
C22Z-3184D	4 port 2-pos valve replacement	1/16 x .75mm 75C/250psi liq PPS/E2
C22Z-3184E	4 port 2-pos valve std-electric	1/16 x .75mm 75C/250psi liq PPS/E2
C22Z-3184EH	4 port 2-pos valve m-electric	1/16 x .75mm 75C/250psi liq PPS/E2
C22Z-3186	6 port 2-pos valve manual	1/16 x .75mm 75C/250psi liq PPS/E2
C22Z-3186A	6 port 2-pos valve air actuated	1/16 x .75mm 75C/250psi liq PPS/E2
C22Z-3186D	6 port 2-pos valve replacement	1/16 x .75mm 75C/250psi liq PPS/E2
C22Z-3186E	6 port 2-pos valve std-electric	1/16 x .75mm 75C/250psi liq PPS/E2
C22Z-3186EH	6 port 2-pos valve m-electric	1/16 x .75mm 75C/250psi liq PPS/E2
C22Z-3188	8 port 2-pos valve manual	1/16 x .75mm 75C/250psi liq PPS/E2
C22Z-3188A	8 port 2-pos valve air actuated	1/16 x .75mm 75C/250psi liq PPS/E2
C22Z-3188D	8 port 2-pos valve replacement	1/16 x .75mm 75C/250psi liq PPS/E2
C22Z-3188E	8 port 2-pos valve std-electric	1/16 x .75mm 75C/250psi liq PPS/E2
C22Z-3188EH	8 port 2-pos valve m-electric	1/16 x .75mm 75C/250psi liq PPS/E2
C22Z-380	Stator 10 port 2-pos C22Z-valve	1/16 x .75mm 75C/250psi liq PPS
C22Z-384	Stator 4 port 2-pos C22Z-valve	1/16 x .75mm 75C/250psi liq PPS
C22Z-386	Stator 6 port 2-pos C22Z-valve	1/16 x .75mm 75C/250psi liq PPS