

VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]
> Cat.#s

> Current System AUD Prices



C22Z-388	Stator 8 port 2-pos C22Z-valve	1/16 x .75mm 75C/250psi liq PPS
C24-10R-.2	Rotor seal 4port 2-pos int vol C24-valve	1/4in -28 x .5mm 75C/250psi liq .2ul E2
C24-10R-.5	Rotor seal 4port 2-pos int vol C24-valve	1/4in -28 x .5mm 75C/250psi liq .5ul E2
C24-10R-1	Rotor seal 4port 2-pos int vol C24-valve	1/4in -28 x .5mm 75C/250psi liq 1ul E2
C24-10R-2	Rotor seal 4port 2-pos int vol C24-valve	1/4in -28 x .5mm 75C/250psi liq 2ul E2
C24-1C8	Stator 4 port 2-pos int vol C24-valve	1/4in -28 x .5mm 75C/250psi liq PPS
C24-2184-.5	4 port 2-pos int vol valve manual	1/4in -28 x .5mm 75C/250psi liq.5ulPPS/E2
C24-2184-.5A	4 port 2-pos int vol valve air act	1/4in -28 x .5mm 75C/250psi liq.5ulPPS/E2
C24-2184-.5D	4 port 2-pos int vol valve replacement	1/4in -28 x .5mm 75C/250psi liq.5ulPPS/E2
C24-2184-.5E	4 port 2-pos int vol valve std-elect	1/4in -28 x .5mm 75C/250psi liq.5ulPPS/E2
C24-2184-.5EH	4 port 2-pos int vol valve m-elect	1/4in -28 x .5mm 75C/250psi liq.5ulPPS/E2
C24-2184-1	4 port 2-pos int vol valve manual	1/4in -28 x .5mm 75C/250psi liq 1ulPPS/E2
C24-2184-1A	4 port 2-pos int vol valve air act	1/4in -28 x .5mm 75C/250psi liq 1ulPPS/E2
C24-2184-1D	4 port 2-pos int vol valve replacement	1/4in -28 x .5mm 75C/250psi liq 1ulPPS/E2
C24-2184-1E	4 port 2-pos int vol valve std-elect	1/4in -28 x .5mm 75C/250psi liq 1ulPPS/E2
C24-2184-1EH	4 port 2-pos int vol valve m-elect	1/4in -28 x .5mm 75C/250psi liq 1ulPPS/E2
C24-2184-2	4 port 2-pos int vol valve manual	1/4in -28 x .5mm 75C/250psi liq 2ulPPS/E2
C24-2184-2A	4 port 2-pos int vol valve air act	1/4in -28 x .5mm 75C/250psi liq 2ulPPS/E2
C24-2184-2D	4 port 2-pos int vol valve replacement	1/4in -28 x .5mm 75C/250psi liq 2ulPPS/E2
C24-2184-2E	4 port 2-pos int vol valve std-elect	1/4in -28 x .5mm 75C/250psi liq 2ulPPS/E2
C24-2184-2EH	4 port 2-pos int vol valve m-elect	1/4in -28 x .5mm 75C/250psi liq 2ulPPS/E2
C24Z-1C8	Stator 4 port 2-pos int vol C24Z-valve	1/16 x .4mm 75C/250psi liq PPS
C24Z-2184-.2	4 port 2-pos int vol valve manual	1/16 x .4mm 75C/250psi liq .2ul PPS/E2
C24Z-2184-.2A	4 port 2-pos int vol valve air act	1/16 x .4mm 75C/250psi liq .2ul PPS/E2
C24Z-2184-.2D	4 port 2-pos int vol valve replacement	1/16 x .4mm 75C/250psi liq .2ul PPS/E2
C24Z-2184-.2E	4 port 2-pos int vol valve std-elect	1/16 x .4mm 75C/250psi liq .2ul PPS/E2
C24Z-2184-.2EH	4 port 2-pos int vol valve m-elect	1/16 x .4mm 75C/250psi liq .2ul PPS/E2
C24Z-2184-.5	4 port 2-pos int vol valve manual	1/16 x .4mm 75C/250psi liq .5ul PPS/E2
C24Z-2184-.5A	4 port 2-pos int vol valve air act	1/16 x .4mm 75C/250psi liq .5ul PPS/E2
C24Z-2184-.5D	4 port 2-pos int vol valve replacement	1/16 x .4mm 75C/250psi liq .5ul PPS/E2
C24Z-2184-.5E	4 port 2-pos int vol valve std-elect	1/16 x .4mm 75C/250psi liq .5ul PPS/E2
C24Z-2184-.5EH	4 port 2-pos int vol valve m-elect	1/16 x .4mm 75C/250psi liq .5ul PPS/E2
C24Z-2184-1	4 port 2-pos int vol valve manual	1/16 x .4mm 75C/250psi liq 1ul PPS/E2
C24Z-2184-1A	4 port 2-pos int vol valve air act	1/16 x .4mm 75C/250psi liq 1ul PPS/E2
C24Z-2184-1D	4 port 2-pos int vol valve replacement	1/16 x .4mm 75C/250psi liq 1ul PPS/E2
C24Z-2184-1E	4 port 2-pos int vol valve std-elect	1/16 x .4mm 75C/250psi liq 1ul PPS/E2
C24Z-2184-1EH	4 port 2-pos int vol valve m-elect	1/16 x .4mm 75C/250psi liq 1ul PPS/E2
C25-310	Rotor seal 8/10 mpos dead-end path C25-valve	1/4in -28 x .75mm 75C/250psi liq E2
C25-314	Rotor seal 4 mpos dead-end path C25-valve	1/4in -28 x .75mm 75C/250psi liq E2
C25-316	Rotor seal 6 mpos dead-end path C25-valve	1/4in -28 x .75mm 75C/250psi liq E2
C25-318	OBSOLETE USE PART-NO. C25-310	
C25-3180	10 mpos dead-end path manual	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C25-3180A	10 mpos dead-end path air actuated	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C25-3180D	10 mpos dead-end path replacement	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C25-3180EMH	10 mpos dead-end path m-electric	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C25-3184	4 mpos dead-end path manual	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C25-3184A	4 mpos dead-end path air actuated	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C25-3184D	4 mpos dead-end path replacement	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C25-3184E	OBSOLETE USE C25-3184EMH	
C25-3184EMH	4 mpos dead-end path m-electric	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C25-3186	6 mpos dead-end path manual	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C25-3186A	6 mpos dead-end path air actuated	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C25-3186D	6 mpos dead-end path replacement	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C25-3186E	OBSOLETE USE C25-3186EMH	
C25-3186EMH	6 mpos dead-end path m-electric	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C25-3188	8 mpos dead-end path manual	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C25-3188A	8 mpos dead-end path air actuated	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C25-3188D	8 mpos dead-end path replacement	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C25-3188E	OBSOLETE USE C25-3188EMH	
C25-3188EMH	8 mpos dead-end path m-electric	1/4in -28 x .75mm 75C/250psi liq PPS/E2
C25-380	Stator 10 mpos dead-end path C25-valve	1/4in -28 x .75mm 75C/250psi liq PPS