



VICIValco-Cheminert PRODUCT LIST 2012

C25-384	Stator 4 mpos dead-end path C25-valve	1/4in -28 x .75mm 75C/250psi liq PPS
C25-386	Stator 6 mpos dead-end path C25-valve	1/4in -28 x .75mm 75C/250psi liq PPS
C25-388	Stator 8 mpos dead-end path C25-valve	1/4in -28 x .75mm 75C/250psi liq PPS
C25-610	Rotor seal 10 mpos dead-end path C25-valve	1/4in -28 x 1.5mm 75C/250psi liq E2
C25-614	Rotor seal 4 mpos dead-end path C25-valve	1/4in -28 x 1.5mm 75C/250psi liq E2
C25-616	Rotor seal 6 mpos dead-end path C25-valve	1/4in -28 x 1.5mm 75C/250psi liq E2
C25-618	Rotor seal 8 mpos dead-end path C25-valve	1/4in -28 x 1.5mm 75C/250psi liq E2
C25-6180	10 mpos dead-end path manual	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C25-6180A	10 mpos dead-end path air actuated	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C25-6180D	10 mpos dead-end path replacement	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C25-6180E	OBSOLETE USE C25-6180EMH	
C25-6180EMH	10 mpos dead-end path m-electric	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C25-6184	4 mpos dead-end path manual	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C25-6184A	4 mpos dead-end path air actuated	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C25-6184D	4 mpos dead-end path replacement	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C25-6184E	OBSOLETE USE C25-6184EMH	
C25-6184EMH	4 mpos dead-end path m-electric	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C25-6186	6 mpos dead-end path manual	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C25-6186A	6 mpos dead-end path air actuated	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C25-6186D	6 mpos dead-end path replacement	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C25-6186E	OBSOLETE USE C25-6186EMH	
C25-6186EMH	6 mpos dead-end path m-electric	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C25-6188	8 mpos dead-end path manual	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C25-6188A	8 mpos dead-end path air actuated	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C25-6188D	8 mpos dead-end path replacement	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C25-6188E	OBSOLETE USE C25-6188EMH	
C25-6188EMH	8 mpos dead-end path m-electric	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C25-680	Stator 10 mpos dead-end path C25-valve	1/4in -28 x 1.5mm 75C/250psi liq PPS
C25-684	Stator 4 mpos dead-end path C25-valve	1/4in -28 x 1.5mm 75C/250psi liq PPS
C25-686	Stator 6 mpos dead-end path C25-valve	1/4in -28 x 1.5mm 75C/250psi liq PPS
C25-688	Stator 8 mpos dead-end path C25-valve	1/4in -28 x 1.5mm 75C/250psi liq PPS
C25Z-3180	10 mpos dead-end path manual	1/16 x .75mm 75C/250psi liq PPS/E2
C25Z-3180A	10 mpos dead-end path air actuated	1/16 x .75mm 75C/250psi liq PPS/E2
C25Z-3180D	10 mpos dead-end path replacement	1/16 x .75mm 75C/250psi liq PPS/E2
C25Z-3180E	OBSOLETE USE C25Z-3180EMH	
C25Z-3180EMH	10 mpos dead-end path m-electric	1/16 x .75mm 75C/250psi liq PPS/E2
C25Z-31814	14 mpos dead-end path manual	1/16 x .75mm 75C/250psi liq PPS/E2
C25Z-31814A	OBSOLETE	
C25Z-31814D	14 mpos dead-end path replacement	1/16 x .75mm 75C/250psi liq PPS/E2
C25Z-31814E	OBSOLETE USE C25Z-31814EMH	
C25Z-31814EMH	14 mpos dead-end path m-electric	1/16 x .75mm 75C/250psi liq PPS/E2
C25Z-3186	6 mpos dead-end path manual	1/16 x .75mm 75C/250psi liq PPS/E2
C25Z-3186A	6 mpos dead-end path air actuated	1/16 x .75mm 75C/250psi liq PPS/E2
C25Z-3186D	6 mpos dead-end path replacement	1/16 x .75mm 75C/250psi liq PPS/E2
C25Z-3186E	OBSOLETE USE C25Z-3186EMH	
C25Z-3186EMH	6 mpos dead-end path m-electric	1/16 x .75mm 75C/250psi liq PPS/E2
C25Z-3188	8 mpos dead-end path manual	1/16 x .75mm 75C/250psi liq PPS/E2
C25Z-3188A	8 mpos dead-end path air actuated	1/16 x .75mm 75C/250psi liq PPS/E2
C25Z-3188D	8 mpos dead-end path replacement	1/16 x .75mm 75C/250psi liq PPS/E2
C25Z-3188E	OBSOLETE USE C25Z-3188EMH	
C25Z-3188EMH	8 mpos dead-end path m-electric	1/16 x .75mm 75C/250psi liq PPS/E2
C25Z-380	Stator 10 mpos dead-end path valve	1/16 x .75mm 75C/250psi liq PPS
C25Z-3814	Stator 14 mpos dead-end path valve	1/16 x .75mm 75C/250psi liq PPS
C25Z-38-14	Stator 14 mpos dead-end path valve	1/16 x .75mm 75C/250psi liq PPS
C25Z-386	Stator 6 mpos dead-end path valve	1/16 x .75mm 75C/250psi liq PPS
C25Z-388	Stator 8 mpos dead-end path valve	1/16 x .75mm 75C/250psi liq PPS
C-261	Syringe fitting assy. head knurled	C1 PEEK/TFE
C-2C00H	Stator 10 port 2-pos (.180BC) C2-valve	1/16 x .4mm N60
C-2C04	Stator 4 port 2-pos C2-valve	1/16 x .4mm N60
C-2C06	Stator 6 port 2-pos C2-valve	1/16 x .4mm N60
C-2C08H	Stator 8 port 2-pos (.180BC) C2-valve	1/16 x .4mm N60