



VICIValco-Cheminert PRODUCT LIST 2012

C-2C30H	Stator 10 port 2-pos (.180BC) C2-valve	1/16 x .4mm Titanium
C-2C34	Stator 4 port 2-pos C2-valve	1/16 x .4mm Titanium
C-2C36	Stator 6 port 2-pos C1/C2-valve	1/16 x .4mm Titanium
C-2C38H	Stator 8 port 2-pos (.180BC) C2-valve	1/16 x .4mm (.180 BC) Titanium
C-2C40H	Stator 10 port 2-pos (.180BC) C2-valve	1/16 x .4mm PAEK
C-2C44	Stator 4 port 2-pos C2-valve	1/16 x .4mm PAEK
C-2C46	Stator 6 port 2-pos C1/C2-valve	1/16 x .4mm PAEK
C-2C48H	Stator 8 port 2-pos (.180BC) C2-valve	1/16 x .4mm (.180 BC) PAEK
C2H-1000	10 port 2-pos valve (.180BC) manual	1/16 x .25mm 75C/5000psi liq N60/H
C2H-1000A	10 port 2-pos valve (.180BC) air actuated	1/16 x .25mm 75C/5000psi liq N60/H
C2H-1000D	10 port 2-pos valve (.180BC) replacement	1/16 x .25mm 75C/5000psi liq N60/H
C2H-1000E	10 port 2-pos valve (.180BC) std-electric	1/16 x .25mm 75C/5000psi liq N60/H
C2H-1000EH	10 port 2-pos valve (.180BC) m-electric	1/16 x .25mm 75C/5000psi liq N60/H
C2H-1008	8 port 2-pos valve (.180BC) manual	1/16 x .25mm 75C/5000psi liq N60/H
C2H-1008A	8 port 2-pos valve (.180BC) air actuated	1/16 x .25mm 75C/5000psi liq N60/H
C2H-1008D	8 port 2-pos valve (.180BC) replacement	1/16 x .25mm 75C/5000psi liq N60/H
C2H-1008E	8 port 2-pos valve (.180BC) std-electric	1/16 x .25mm 75C/5000psi liq N60/H
C2H-1008EH	8 port 2-pos valve (.180BC) m-electric	1/16 x .25mm 75C/5000psi liq N60/H
C2H-1030	10 port 2-pos valve (.180BC) manual	1/16 x .25mm 75C/5000psi liq Ti/H
C2H-1030A	10 port 2-pos valve (.180BC) air actuated	1/16 x .25mm 75C/5000psi liq Ti/H
C2H-1030D	10 port 2-pos valve (.180BC) replacement	1/16 x .25mm 75C/5000psi liq Ti/H
C2H-1030E	10 port 2-pos valve (.180BC) std-electric	1/16 x .25mm 75C/5000psi liq Ti/H
C2H-1030EH	10 port 2-pos valve (.180BC) m-electric	1/16 x .25mm 75C/5000psi liq Ti/H
C2H-1038	8 port 2-pos valve (.180BC) manual	1/16 x .25mm 75C/5000psi liq Ti/H
C2H-1038A	8 port 2-pos valve (.180BC) air actuated	1/16 x .25mm 75C/5000psi liq Ti/H
C2H-1038D	8 port 2-pos valve (.180BC) replacement	1/16 x .25mm 75C/5000psi liq Ti/H
C2H-1038E	8 port 2-pos valve (.180BC) std-electric	1/16 x .25mm 75C/5000psi liq Ti/H
C2H-1038EH	8 port 2-pos valve (.180BC) m-electric	1/16 x .25mm 75C/5000psi liq Ti/H
C2H-1340	10 port 2-pos valve (.180BC) manual	1/16 x .25mm 50C/5000psi liq PAEK/E
C2H-1340A	10 port 2-pos valve (.180BC) air actuator	1/16 x .25mm 50C/5000psi liq PAEK/E
C2H-1340D	10 port 2-pos valve (.180BC) replacement	1/16 x .25mm 50C/5000psi liq PAEK/E
C2H-1340E	10 port 2-pos valve (.180BC) std-electric	1/16 x .25mm 50C/5000psi liq PAEK/E
C2H-1340EH	10 port 2-pos valve (.180BC) m-electric	1/16 x .25mm 50C/5000psi liq PAEK/E
C2H-1348	8 port 2-pos valve (.180BC) manual	1/16 x .25mm 50C/5000psi liq PAEK/E
C2H-1348A	8 port 2-pos valve (.180BC) air actuated	1/16 x .25mm 50C/5000psi liq PAEK/E
C2H-1348D	8 port 2-pos valve (.180BC) replacement	1/16 x .25mm 50C/5000psi liq PAEK/E
C2H-1348E	8 port 2-pos valve (.180BC) std-electric	1/16 x .25mm 50C/5000psi liq PAEK/E
C2H-1348EH	8 port 2-pos valve (.180BC) m-electric	1/16 x .25mm 50C/5000psi liq PAEK/E
C2H-2000	10 port 2-pos valve (.180BC) manual	1/16 x .4mm 75C/5000psi liq N60/H
C2H-2000A	10 port 2-pos valve (.180BC) air act	1/16 x .4mm 75C/5000psi liq N60/H
C2H-2000D	10 port 2-pos valve (.180BC) replacement	1/16 x .4mm 75C/5000psi liq N60/H
C2H-2000E	10 port 2-pos valve (.180BC) std-electric	1/16 x .4mm 75C/5000psi liq N60/H
C2H-2000EH	10 port 2-pos valve (.180BC) m-electric	1/16 x .4mm 75C/5000psi liq N60/H
C2H-2008	8 port 2-pos valve (.180BC) manual	1/16 x .4mm 75C/5000psi liq N60/H
C2H-2008A	8 port 2-pos valve (.180BC) air act	1/16 x .4mm 75C/5000psi liq N60/H
C2H-2008D	8 port 2-pos valve (.180BC) replacement	1/16 x .4mm 75C/5000psi liq N60/H
C2H-2008E	8 port 2-pos valve (.180BC) std-elect	1/16 x .4mm 75C/5000psi liq N60/H
C2H-2008EH	8 port 2-pos valve (.180BC) m-elect	1/16 x .4mm 75C/5000psi liq N60/H
C2H-2030	10 port 2-pos valve (.180BC) manual	1/16 x .4mm 75C/5000psi liq Ti/H
C2H-2030A	10 port 2-pos valve (.180BC) air act	1/16 x .4mm 75C/5000psi liq Ti/H
C2H-2030D	10 port 2-pos valve (.180BC) replacement	1/16 x .4mm 75C/5000psi liq Ti/H
C2H-2030E	10 port 2-pos valve (.180BC) std-electric	1/16 x .4mm 75C/5000psi liq Ti/H
C2H-2030EH	10 port 2-pos valve (.180BC) m-electric	1/16 x .4mm 75C/5000psi liq Ti/H
C2H-2038	8 port 2-pos valve (.180BC) manual	1/16 x .4mm 75C/5000psi liq Ti/H
C2H-2038A	8 port 2-pos valve (.180BC) air act	1/16 x .4mm 75C/5000psi liq Ti/H
C2H-2038D	8 port 2-pos valve (.180BC) replacement	1/16 x .4mm 75C/5000psi liq Ti/H
C2H-2038E	8 port 2-pos valve (.180BC) std-elect	1/16 x .4mm 75C/5000psi liq Ti/H
C2H-2038EH	8 port 2-pos valve (.180BC) m-electric	1/16 x .4mm 75C/5000psi liq Ti/H
C2H-2340	10 port 2-pos valve (.180BC) manual	1/16 x .4mm 50C/5000psi liq PAEK/E
C2H-2340A	10 port 2-pos valve (.180BC) air act	1/16 x .4mm 50C/5000psi liq PAEK/E
C2H-2340D	10 port 2-pos valve (.180BC) replacement	1/16 x .4mm 50C/5000psi liq PAEK/E