

VICI Valco-Cheminert PRODUCT LIST 2012

[Ctrl F]
> Cat.#s

> Current System AUD Prices



C35Z-31826D	26 mpos dead-end path replacement	1/16 x .75mm 50C/100psi liq PPS/E2
C35Z-31826EMH	!!! RECOMMEND C35Z-31826EMT	
C35Z-31826EMT	26 mpos dead-end path m-electric	1/16 x .75mm 50C/100psi liq PPS/E2
C35Z-31R20	Rotor seal 20mpos dead-end path C35-vlv	1/16 x .75mm 50C/100psi liq E2
C360C	Cap 360um for metal tubing	SS nut included
C360CFS	Cap 360um for fused silica tubing	SS nut included
C360CPK	Cap 360um	PEEK
C360CPKG	OBSOLETE replaced by C360CPK	
C360ET	Make up extender tool	for 360um nuts
C360IZR.5S6	Internal reducer 1/32in x 360um	.38mm bore SS w/o frit
C360IZR.5S6PKG	Internal reducer 1/32in x 360um	.38mm bore SS with PEEK nut w/o frit
C360NFFS	Nut 360um No Twist	for FS tubing (for > 10 kpsi)
C360NFPKG	Nut 360um No Twist PEEK	with glass-filled PEEK ferrule
C360NFS6	Nut 360um No Twist SS	with 316 ferrule
C360PPK	Plug 360um	
C360QTPK2	Tee 360um quick mount 50um bore	for PEEK and FS Tubing (for < 10 kpsi)
C360QTPK4	Tee 360um quick mount 100um bore	for PEEK and FS Tubing (for < 10 kpsi)
C360QTPK6	Tee 360um quick mount 150um bore	for PEEK and FS Tubing (for < 10 kpsi)
C360QTPKG2	OBSOLETE replaced by C360QTPK2	
C360QTPKG4	OBSOLETE replaced by C360QTPK4	
C360QTPKG6	OBSOLETE replaced by C360QTPK6	
C360QUPK2	Union 360um quick mount 50um bore	for PEEK and FS Tubing (for < 10 kpsi)
C360QUPK4	Union 360um quick mount 100um bore	for PEEK and FS Tubing (for < 10 kpsi)
C360QUPK6	Union 360um quick mount 150um bore	for PEEK and FS Tubing (for < 10 kpsi)
C360QUPKG2	OBSOLETE replaced by C360QUPK2	
C360QUPKG4	OBSOLETE replaced by C360QUPK4	
C360QUPKG6	OBSOLETE replaced by C360QUPK6	
C360QXPK2	Cross 360um quick mount 50um bore	for PEEK and FS Tubing (for < 10 kpsi)
C360QXPK4	Cross 360um quick mount 100um bore	for PEEK and FS Tubing (for < 10 kpsi)
C360QXPK6	Cross 360um quick mount 150um bore	for PEEK and FS Tubing (for < 10 kpsi)
C360QXPKG2	OBSOLETE replaced by C360QXPK2	
C360QXPKG4	OBSOLETE replaced by C360QXPK4	
C360QXPKG6	OBSOLETE replaced by C360QXPK6	
C360RU.5FS2	Reducing union 1/32in to 360um	50um bore for FS tubing (for > 10 kpsi)
C360RU.5FS4	Reducing union 1/32in to 360um	100um bore for FS tubing (for > 10 kpsi)
C360RU.5FS6	Reducing union 1/32in to 360um	150um bore for FS tubing (for > 10 kpsi)
C360RU.5S62	Reducing union 1/32in to 360um	50um bore for metal tubing (up to 20 kpsi)
C360RU.5S64	Reducing union 1/32in to 360um	100um bore for metal tubing (up to 20 kpsi)
C360RU.5S66	Reducing union 1/32in to 360um	150um bore for metal tubing (up to 20 kpsi)
C360RU1FS6	Reducing union 1/16in to 360um	150um bore for FS tubing (for > 10 kpsi)
C360RU1S66	Reducing union 1/16in to 360um	150um bore for metal tubing (up to 20 kpsi)
C360UFS2	Union 360um 50um bore	for FS tubing (for > 10 kpsi)
C360UFS4	Union 360um 100um bore	for FS tubing (for > 10 kpsi)
C360UFS6	Union 360um 150um bore	for FS tubing (for > 10 kpsi)
C360UPK2	Union 360um 50um bore	for PEEK and FS tubing (for < 10 kpsi)
C360UPK4	Union 360um 100um bore	for PEEK and FS tubing (for < 10 kpsi)
C360UPK6	Union 360um 150um bore	for PEEK and FS tubing (for < 10 kpsi)
C360UPKG2	OBSOLETE replaced by C360UPK2	
C360UPKG4	OBSOLETE replaced by C360UPK4	
C360UPKG6	OBSOLETE replaced by C360UPK6	
C360US62	Union 360um 50um bore	for metal tubing (up to 20 kpsi)
C360US64	Union 360um 100um bore	for metal tubing (up to 20 kpsi)
C360US66	Union 360um 150um bore	for metal tubing (up to 20 kpsi)
C4-0004-.01	4 port 2-pos int vol valve manual	1/16 x .15mm 75C/5000psi liq .01ul N60/H
C4-0004-.01A	4 port 2-pos int vol valve air actuated	1/16 x .15mm 75C/5000psi liq .01ul N60/H
C4-0004-.01D	4 port 2-pos int vol valve replacement	1/16 x .15mm 75C/5000psi liq .01ul N60/H
C4-0004-.01E	4 port 2-pos int vol valve std-electric	1/16 x .15mm 75C/5000psi liq .01ul N60/H
C4-0004-.01EH	4 port 2-pos int vol valve m-electric	1/16 x .15mm 75C/5000psi liq .01ul N60/H
C4-0004-.02	4 port 2-pos int vol valve manual	1/16 x .15mm 75C/5000psi liq .02ul N60/H
C4-0004-.02A	4 port 2-pos int vol valve air actuated	1/16 x .15mm 75C/5000psi liq .02ul N60/H
C4-0004-.02D	4 port 2-pos int vol valve replacement	1/16 x .15mm 75C/5000psi liq .02ul N60/H