

VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]
> Cat.#s

> Current System AUD Prices



C4-0004-.02E	4 port 2-pos int vol valve std-electric	1/16 x .15mm 75C/5000psi liq .02ul N60/H
C4-0004-.02EH	4 port 2-pos int vol valve m-electric	1/16 x .15mm 75C/5000psi liq .02ul N60/H
C4-0004-.05	4 port 2-pos int vol valve manual	1/16 x .15mm 75C/5000psi liq .05ul N60/H
C4-0004-.05A	4 port 2-pos int vol valve air actuated	1/16 x .15mm 75C/5000psi liq .05ul N60/H
C4-0004-.05D	4 port 2-pos int vol valve replacement	1/16 x .15mm 75C/5000psi liq .05ul N60/H
C4-0004-.05E	4 port 2-pos int vol valve std-electric	1/16 x .15mm 75C/5000psi liq .05ul N60/H
C4-0004-.05EH	4 port 2-pos int vol valve m-electric	1/16 x .15mm 75C/5000psi liq .05ul N60/H
C4-00R-.01	Rotor seal 4 port 2-pos int vol valve	1/16 x .15mm 75C/5000psi liq .01ul H
C4-00R-.02	Rotor seal 4 port 2-pos int vol valve	1/16 x .15mm 75C/5000psi liq .02ul H
C4-00R-.05	Rotor seal 4 port 2-pos int vol valve	1/16 x .15mm 75C/5000psi liq .05ul H
C4-0344-.01	4 port 2-pos int vol valve manual	1/16 x .15mm 50C/5000psi liq .01ul PAEK/E
C4-0344-.01A	4 port 2-pos int vol valve air actuated	1/16 x .15mm 50C/5000psi liq .01ul PAEK/E
C4-0344-.01D	4 port 2-pos int vol valve replacement	1/16 x .15mm 50C/5000psi liq .01ul PAEK/E
C4-0344-.01E	4 port 2-pos int vol valve std-electric	1/16 x .15mm 50C/5000psi liq .01ul PAEK/E
C4-0344-.01EH	4 port 2-pos int vol valve m-electric	1/16 x .15mm 50C/5000psi liq .01ul PAEK/E
C4-0344-.02	4 port 2-pos int vol valve manual	1/16 x .15mm 50C/5000psi liq .02ul PAEK/E
C4-0344-.02A	4 port 2-pos int vol valve air actuated	1/16 x .15mm 50C/5000psi liq .02ul PAEK/E
C4-0344-.02D	4 port 2-pos int vol valve replacement	1/16 x .15mm 50C/5000psi liq .02ul PAEK/E
C4-0344-.02E	4 port 2-pos int vol valve std-electric	1/16 x .15mm 50C/5000psi liq .02ul PAEK/E
C4-0344-.02EH	4 port 2-pos int vol valve m-electric	1/16 x .15mm 50C/5000psi liq .02ul PAEK/E
C4-0344-.05	4 port 2-pos int vol valve manual	1/16 x .15mm 50C/5000psi liq .05ul PAEK/E
C4-0344-.05A	4 port 2-pos int vol valve air actuated	1/16 x .15mm 50C/5000psi liq .05ul PAEK/E
C4-0344-.05D	4 port 2-pos int vol valve replacement	1/16 x .15mm 50C/5000psi liq .05ul PAEK/E
C4-0344-.05E	4 port 2-pos int vol valve std-electric	1/16 x .15mm 50C/5000psi liq .05ul PAEK/E
C4-0344-.05EH	4 port 2-pos int vol valve m-electric	1/16 x .15mm 50C/5000psi liq .05ul PAEK/E
C4-03R-.01	Rotor seal 4 port 2-pos int vol valve	1/16 x .15mm 50C/5000psi liq .01ul E
C4-03R-.02	Rotor seal 4 port 2-pos int vol valve	1/16 x .15mm 50C/5000psi liq .02ul E
C4-03R-.05	Rotor seal 4 port 2-pos int vol valve	1/16 x .15mm 50C/5000psi liq .05ul E
C4-0C0	Stator 4 port 2-pos int vol C4-valve	1/16 x .15mm N60
C4-0C4	Stator 4 port 2-pos int vol C4-valve	1/16 x .15mm PAEK
C4-1004-.1	4 port 2-pos int vol valve manual	1/16 x .25mm 75C/5000psi liq .1ul N60/H
C4-1004-.1A	4 port 2-pos int vol valve air act	1/16 x .25mm 75C/5000psi liq .1ul N60/H
C4-1004-.1D	4 port 2-pos int vol valve replacement	1/16 x .25mm 75C/5000psi liq .1ul N60/H
C4-1004-.1E	4 port 2-pos int vol valve std-elect	1/16 x .25mm 75C/5000psi liq .1ul N60/H
C4-1004-.1EH	4 port 2-pos int vol valve m-elect	1/16 x .25mm 75C/5000psi liq .1ul N60/H
C4-1004-.2	4 port 2-pos int vol valve manual	1/16 x .25mm 75C/5000psi liq .2ul N60/H
C4-1004-.2A	4 port 2-pos int vol valve air act	1/16 x .25mm 75C/5000psi liq .2ul N60/H
C4-1004-.2D	4 port 2-pos int vol valve replacement	1/16 x .25mm 75C/5000psi liq .2ul N60/H
C4-1004-.2E	4 port 2-pos int vol valve std-elect	1/16 x .25mm 75C/5000psi liq .2ul N60/H
C4-1004-.2EH	4 port 2-pos int vol valve m-elect	1/16 x .25mm 75C/5000psi liq .2ul N60/H
C4-1004-.5	4 port 2-pos int vol valve manual	1/16 x .25mm 75C/5000psi liq .5ul N60/H
C4-1004-.5A	4 port 2-pos int vol valve air act	1/16 x .25mm 75C/5000psi liq .5ul N60/H
C4-1004-.5D	4 port 2-pos int vol valve replacement	1/16 x .25mm 75C/5000psi liq .5ul N60/H
C4-1004-.5E	4 port 2-pos int vol valve std-elect	1/16 x .25mm 75C/5000psi liq .5ul N60/H
C4-1004-.5EH	4 port 2-pos int vol valve m-elect	1/16 x .25mm 75C/5000psi liq .5ul N60/H
C4-1034-.1	4 port 2-pos int vol valve manual	1/16 x .25mm 75C/5000psi liq .1ul Ti/H
C4-1034-.1A	4 port 2-pos int vol valve air act	1/16 x .25mm 75C/5000psi liq .1ul Ti/H
C4-1034-.1D	4 port 2-pos int vol valve replacement	1/16 x .25mm 75C/5000psi liq .1ul Ti/H
C4-1034-.1E	4 port 2-pos int vol valve std-elect	1/16 x .25mm 75C/5000psi liq .1ul Ti/H
C4-1034-.1EH	4 port 2-pos int vol valve m-elect	1/16 x .25mm 75C/5000psi liq .1ul Ti/H
C4-1034-.2	4 port 2-pos int vol valve manual	1/16 x .25mm 75C/5000psi liq .2ul Ti/H
C4-1034-.2A	4 port 2-pos int vol valve air act	1/16 x .25mm 75C/5000psi liq .2ul Ti/H
C4-1034-.2D	4 port 2-pos int vol valve replacement	1/16 x .25mm 75C/5000psi liq .2ul Ti/H
C4-1034-.2E	4 port 2-pos int vol valve std-elect	1/16 x .25mm 75C/5000psi liq .2ul Ti/H
C4-1034-.2EH	4 port 2-pos int vol valve m-elect	1/16 x .25mm 75C/5000psi liq .2ul Ti/H
C4-1034-.5	4 port 2-pos int vol valve manual	1/16 x .25mm 75C/5000psi liq .5ul Ti/H
C4-1034-.5A	4 port 2-pos int vol valve air act	1/16 x .25mm 75C/5000psi liq .5ul Ti/H
C4-1034-.5D	4 port 2-pos int vol valve replacement	1/16 x .25mm 75C/5000psi liq .5ul Ti/H
C4-1034-.5E	4 port 2-pos int vol valve std-elect	1/16 x .25mm 75C/5000psi liq .5ul Ti/H
C4-1034-.5EH	4 port 2-pos int vol valve m-elect	1/16 x .25mm 75C/5000psi liq .5ul Ti/H
C4-10R-.1	Rotor seal 4 port 2-pos int vol valve	1/16 x .25mm 75C/5000psi liq .1ul H