

VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]
> Cat.#s

> Current System AUD Prices



C4-10R-.2	Rotor seal 4 port 2-pos int vol valve	1/16 x .25mm 75C/5000psi liq .2ul H
C4-10R-.5	Rotor seal 4 port 2-pos int vol valve	1/16 x .25mm 75C/5000psi liq .5ul H
C4-1344-.1	4 port 2-pos int vol valve manual	1/16 x .25mm 50C/5000psi liq.1ul PAEK/E
C4-1344-.1A	4 port 2-pos int vol valve air act	1/16 x .25mm 50C/5000psi liq.1ul PAEK/E
C4-1344-.1D	4 port 2-pos int vol valve replacement	1/16 x .25mm 50C/5000psi liq.1ul PAEK/E
C4-1344-.1E	4 port 2-pos int vol valve std-elect	1/16 x .25mm 50C/5000psi liq.1ul PAEK/E
C4-1344-.1EH	4 port 2-pos int vol valve m-elect	1/16 x .25mm 50C/5000psi liq.1ul PAEK/E
C4-1344-.2	4 port 2-pos int vol valve manual	1/16 x .25mm 50C/5000psi liq.2ul PAEK/E
C4-1344-.2A	4 port 2-pos int vol valve air act	1/16 x .25mm 50C/5000psi liq.2ul PAEK/E
C4-1344-.2D	4 port 2-pos int vol valve replacement	1/16 x .25mm 50C/5000psi liq.2ul PAEK/E
C4-1344-.2E	4 port 2-pos int vol valve std-elect	1/16 x .25mm 50C/5000psi liq.2ul PAEK/E
C4-1344-.2EH	4 port 2-pos int vol valve m-elect	1/16 x .25mm 50C/5000psi liq.2ul PAEK/E
C4-1344-.5	4 port 2-pos int vol valve manual	1/16 x .25mm 50C/5000psi liq.5ul PAEK/E
C4-1344-.5A	4 port 2-pos int vol valve air act	1/16 x .25mm 50C/5000psi liq.5ul PAEK/E
C4-1344-.5D	4 port 2-pos int vol valve replacement	1/16 x .25mm 50C/5000psi liq.5ul PAEK/E
C4-1344-.5E	4 port 2-pos int vol valve std-elect	1/16 x .25mm 50C/5000psi liq.5ul PAEK/E
C4-1344-.5EH	4 port 2-pos int vol valve m-elect	1/16 x .25mm 50C/5000psi liq.5ul PAEK/E
C4-13R-.1	Rotor seal 4 port 2-pos int vol valve	1/16 x .25mm 50C/5000psi liq .1ul E
C4-13R-.2	Rotor seal 4 port 2-pos int vol valve	1/16 x .25mm 50C/5000psi liq .2ul E
C4-13R-.5	Rotor seal 4 port 2-pos int vol valve	1/16 x .25mm 50C/5000psi liq .5ul E
C4-1C0	Stator 4 port 2-pos int vol C4-valve	1/16 x .25mm N60
C4-1C3	Stator 4 port 2-pos int vol C4-valve	1/16 x .25mm Titanium
C4-1C4	Stator 4 port 2-pos int vol C4-valve	1/16 x .25mm PAEK
C45-9784A	4 mpos dead-end path air act	1/2in -20 x 4.6mm 50C/100psi liq PPS/PTFE
C45-9784D	4 mpos dead-end path replacement	1/2in -20 x 4.6mm 50C/100psi liq PPS/PTFE
C45-9784E	4 mpos dead-end path m-elect	1/2in -20 x 4.6mm 50C/100psi liq PPS/PTFE
C45-9784EMT	4 mpos dead-end path m-elect	1/2in -20 x 4.6mm 50C/100psi liq PPS/PTFE
C45-9786A	OBSOLETE USE C45-9786AH	
C45-9786D	6 mpos dead-end path replacement	1/2in -20 x 4.6mm 50C/100psi liq PPS/PTFE
C45-9786E	6 mpos dead-end path m-elect	1/2in -20 x 4.6mm 50C/100psi liq PPS/PTFE
C45-9786EMT	6 mpos dead-end path m-elect	1/2in -20 x 4.6mm 50C/100psi liq PPS/PTFE
C45-97R4	Rotor 4 mpos C45-valve	1/2in -20 x 4.6mm 50C/100psi liq E2
C45-97R6	OBSOLETE USE C-316	
C4UW	!!! RECOMMEND 2C4UW	SUPPLIED WITH LARGER HANDLE
C4UWE	4 port 2-pos valve manual	1/16 x .75mm 225C/400psi gas N60/E
C4W	4 port 2-pos valve manual	1/16 x .4mm 75C/5000psi liq N60/H
C4WE	4 port 2-pos valve manual	1/16 x .4mm 225C/400psi gas N60/E
C5-2004	4 mpos dead-end path manual	1/16 x .4mm 75C/5000psi liq N60/H
C5-2004A	4 mpos dead-end path air act	1/16 x .4mm 75C/5000psi liq N60/H
C5-2004D	4 mpos dead-end path replacement	1/16 x .4mm 75C/5000psi liq N60/H
C5-2004E	OBSOLETE USE C5-2004EMH	
C5-2004EMH	4 mpos dead-end path m-elect	1/16 x .4mm 75C/5000psi liq N60/H
C5-2006	6 mpos dead-end path manual	1/16 x .4mm 75C/5000psi liq N60/H
C5-2006A	6 mpos dead-end path air act	1/16 x .4mm 75C/5000psi liq N60/H
C5-2006D	6 mpos dead-end path replacement	1/16 x .4mm 75C/5000psi liq N60/H
C5-2006E	OBSOLETE USE C5-2006EMH	
C5-2006EMH	6 mpos dead-end path m-elect	1/16 x .4mm 75C/5000psi liq N60/H
C5-2006EMTD	6 mpos dead-end path m-elect dual drive	1/16 x .4mm 75C/5000psi liq N60/H
C5-2034	4 mpos dead-end path manual	1/16 x .4mm 75C/5000psi liq Ti/H
C5-2034A	4 mpos dead-end path air act	1/16 x .4mm 75C/5000psi liq Ti/H
C5-2034D	4 mpos dead-end path replacement	1/16 x .4mm 75C/5000psi liq Ti/H
C5-2034E	OBSOLETE USE C5-2034EMH	
C5-2034EMH	4 mpos dead-end path m-elect	1/16 x .4mm 75C/5000psi liq Ti/H
C5-2036	6 mpos dead-end path manual	1/16 x .4mm 75C/5000psi liq Ti/H
C5-2036A	6 mpos dead-end path air act	1/16 x .4mm 75C/5000psi liq Ti/H
C5-2036D	6 mpos dead-end path replacement	1/16 x .4mm 75C/5000psi liq Ti/H
C5-2036E	OBSOLETE USE C5-2036EMH	
C5-2036EMH	6 mpos dead-end path m-elect	1/16 x .4mm 75C/5000psi liq Ti/H
C5-20R0H	Rotor seal 10 mpos (.180BC) dead-end path valve	1/16 x .4mm 75C/5000psi liq H
C5-20R4	Rotor seal 4 mpos dead-end path valve	1/16 x .4mm 75C/5000psi liq H
C5-20R6	Rotor seal 6 mpos dead-end path valve	1/16 x .4mm 75C/5000psi liq H