



VICIValco-Cheminert PRODUCT LIST 2012

C5-20R8H	Rotor seal 8 mpos (.180BC) dead-end path valve	1/16 x .4mm 75C/5000psi liq H
C52-1000I	10 port 2-pos valve motor sensor controller	1/16 x .25mm 40C/5000psi liq N60/H
C52-1000I-S	10 port 2-pos valve motor sensor	1/16 x .25mm 40C/5000psi liq N60/H
C52-1000IX	10 port 2-pos valve motor only	1/16 x .25mm 40C/5000psi liq N60/H
C52-1004I	4 port 2-pos valve motor sensor controller	1/16 x .25mm 40C/5000psi liq N60/H
C52-1004I-S	4 port 2-pos valve motor sensor	1/16 x .25mm 40C/5000psi liq N60/H
C52-1004IX	4 port 2-pos valve motor only	1/16 x .25mm 40C/5000psi liq N60/H
C52-1006I	6 port 2-pos valve motor sensor controller	1/16 x .25mm 40C/5000psi liq N60/H
C52-1006I-S	6 port 2-pos valve motor sensor	1/16 x .25mm 40C/5000psi liq N60/H
C52-1006IX	6 port 2-pos valve motor only	1/16 x .25mm 40C/5000psi liq N60/H
C52-1008I	8 port 2-pos valve motor sensor controller	1/16 x .25mm 40C/5000psi liq N60/H
C52-1008I-S	8 port 2-pos valve motor sensor	1/16 x .25mm 40C/5000psi liq N60/H
C52-1008IX	8 port 2-pos valve motor only	1/16 x .25mm 40C/5000psi liq N60/H
C52-1340I	10 port 2-pos valve motor sensor controller	1/16 x .25mm 40C/5000psi liq PAEK/E
C52-1340I-S	10 port 2-pos valve motor sensor	1/16 x .25mm 40C/5000psi liq PAEK/E
C52-1340IX	10 port 2-pos valve motor only	1/16 x .25mm 40C/5000psi liq PAEK/E
C52-1344I	4 port 2-pos valve motor sensor controller	1/16 x .25mm 40C/5000psi liq PAEK/E
C52-1344I-S	4 port 2-pos valve motor sensor	1/16 x .25mm 40C/5000psi liq PAEK/E
C52-1344IX	4 port 2-pos valve motor only	1/16 x .25mm 40C/5000psi liq PAEK/E
C52-1346I	6 port 2-pos valve motor sensor controller	1/16 x .25mm 40C/5000psi liq PAEK/E
C52-1346I-S	6 port 2-pos valve motor sensor	1/16 x .25mm 40C/5000psi liq PAEK/E
C52-1346IX	6 port 2-pos valve motor only	1/16 x .25mm 40C/5000psi liq PAEK/E
C52-1348I	8 port 2-pos valve motor sensor controller	1/16 x .25mm 40C/5000psi liq PAEK/E
C52-1348I-S	8 port 2-pos valve motor sensor	1/16 x .25mm 40C/5000psi liq PAEK/E
C52-1348IX	8 port 2-pos valve motor only	1/16 x .25mm 40C/5000psi liq PAEK/E
C52-1C00	Stator 10 port 2-pos C52-valve	1/16 x .25mm (.180) N60
C52-1C04	Stator 4 port 2-pos C52-valve	1/16 x .25mm (.180) N60
C52-1C06	Stator 6 port 2-pos C52-valve	1/16 x .25mm N60
C52-1C08	Stator 8 port 2-pos C52-valve	1/16 x .25mm (.180) N60
C52-1C40	Stator 10 port 2-pos C52-valve	1/16 x .25mm (.100) E3
C52-1C44	Stator 4 port 2-pos C52-valve	1/16 x .25mm (.100) E3
C52-1C46	Stator 6 port 2-pos C52-valve	1/16 x .25mm (.100) E3
C52-1C48	Stator 8 port 2-pos C52-valve	1/16 x .25mm (.100) E3
C52-2000I	10 port 2-pos valve motor sensor controller	1/16 x .4mm 40C/5000psi liq N60/H
C52-2000I-S	10 port 2-pos valve motor sensor	1/16 x .4mm 40C/5000psi liq N60/H
C52-2000IX	10 port 2-pos valve motor only	1/16 x .4mm 40C/5000psi liq N60/H
C52-2004I	4 port 2-pos valve motor sensor controller	1/16 x .4mm 40C/5000psi liq N60/H
C52-2004I-S	4port 2-pos valve motor sensor	1/16 x .4mm 40C/5000psi liq N60/H
C52-2004IX	4port 2-pos valve motor only	1/16 x .4mm 40C/5000psi liq N60/H
C52-2006I	6 port 2-pos valve motor sensor controller	1/16 x .4mm 40C/5000psi liq N60/H
C52-2006I-S	6 port 2-pos valve motor sensor	1/16 x .4mm 40C/5000psi liq N60/H
C52-2006IX	6port 2-pos valve motor only	1/16 x .4mm 40C/5000psi liq N60/H
C52-2008I	8 port 2-pos valve motor sensor controller	1/16 x .4mm 40C/5000psi liq N60/H
C52-2008I-S	8 port 2-pos valve motor sensor	1/16 x .4mm 40C/5000psi liq N60/H
C52-2008IX	8port 2-pos valve motor only	1/16 x .4mm 40C/5000psi liq N60/H
C52-2340I	10 port 2-pos valve motor sensor controller	1/16 x .4mm 40C/5000psi liq PAEK/E
C52-2340I-S	10 port 2-pos valve motor sensor	1/16 x .4mm 40C/5000psi liq PAEK/E
C52-2340IX	10 port 2-pos valve motor only	1/16 x .4mm 40C/5000psi liq PAEK/E
C52-2344I	4 port 2-pos valve motor sensor controller	1/16 x .4mm 40C/5000psi liq PAEK/E
C52-2344I-S	4 port 2-pos valve motor sensor	1/16 x .4mm 40C/5000psi liq PAEK/E
C52-2344IX	4 port 2-pos valve motor only	1/16 x .4mm 40C/5000psi liq PAEK/E
C52-2346I	6 port 2-pos valve motor sensor controller	1/16 x .4mm 40C/5000psi liq PAEK/E
C52-2346I-S	6 port 2-pos valve motor sensor	1/16 x .4mm 40C/5000psi liq PAEK/E
C52-2346IX	6 port 2-pos valve motor only	1/16 x .4mm 40C/5000psi liq PAEK/E
C52-2348I	8 port 2-pos valve motor sensor controller	1/16 x .4mm 40C/5000psi liq PAEK/E
C52-2348I-S	6 port 2-pos valve motor sensor	1/16 x .4mm 40C/5000psi liq PAEK/E
C52-2348IX	8 port 2-pos valve motor only	1/16 x .4mm 40C/5000psi liq PAEK/E
C52-2C00	Stator 10 port 2-pos C52-valve	1/16 x .4mm N60
C52-2C04	Stator 4 port 2-pos C52-valve	1/16 x .4mm N60
C52-2C06	Stator 6 port 2-pos C52-valve	1/16 x .4mm N60
C52-2C08	Stator 8 port 2-pos C52-valve	1/16 x .4mm N60