

# VICIValco-Cheminert PRODUCT LIST 2012

(Ctrl F)  
> Cat.#s

> Current System AUD Prices



C52-2C40	Stator 10 port 2-pos C52-valve	1/16 x .4mm PAEK
C52-2C44	Stator 4 port 2-pos C52-valve	1/16 x .4mm PAEK
C52-2C46	Stator 6 port 2-pos C52-valve	1/16 x .4mm PAEK
C52-2C48	Stator 8 port 2-pos C52-valve	1/16 x .4mm PAEK
C5-2344	4 mpos dead-end path manual	1/16 x .4mm 50C/5000psi liq PAEK/E
C5-2344A	4 mpos dead-end path air act	1/16 x .4mm 50C/5000psi liq PAEK/E
C5-2344D	4 mpos dead-end path replacement	1/16 x .4mm 50C/5000psi liq PAEK/E
C5-2344E	OBSOLETE USE C5-2344EMH	
C5-2344EMH	4 mpos dead-end path m-elect	1/16 x .4mm 50C/5000psi liq PAEK/E
C5-2346	6 mpos dead-end path manual	1/16 x .4mm 50C/5000psi liq PAEK/E
C5-2346A	6 mpos dead-end path air act	1/16 x .4mm 50C/5000psi liq PAEK/E
C5-2346D	6 mpos dead-end path replacement	1/16 x .4mm 50C/5000psi liq PAEK/E
C5-2346E	OBSOLETE USE C5-2346EMH	
C5-2346EMH	6 mpos dead-end path m-elect	1/16 x .4mm 50C/5000psi liq PAEK/E
C5-2346EMHD	!!! RECOMMEND C5-2346EMTD	
C5-2346EMTD	6 mpos dead-end path m-elect dual drive	1/16 x .4mm 50C/5000psi liq PAEK/E
C5-23R0H	Rotor seal 10 mpos (.180BC) dead-end path valve	1/16 x .4mm 50C/5000psi liq E
C5-23R4	Rotor seal 4 mpos dead-end path valve	1/16 x .4mm 50C/5000psi liq E
C5-23R6	Rotor seal 6 mpos dead-end path valve	1/16 x .4mm 50C/5000psi liq E
C5-23R8H	Rotor seal 8 mpos (.180BC) dead-end path valve	1/16 x .4mm 50C/5000psi liq E
C5-2C00H	Stator 10 mpos (.180BC) dead-end path C5-valve	1/16 x .4mm N60
C5-2C04	Stator 4 mpos dead-end path C5-valve	1/16 x .4mm N60
C5-2C06	Stator 6 mpos dead-end path C5-valve	1/16 x .4mm N60
C5-2C08H	Stator 8 mpos (.180BC) dead-end path C5-valve	1/16 x .4mm N60
C5-2C30H	Stator 10 mpos (.180BC) dead-end path C5-valve	1/16 x .4mm Titanium
C5-2C34	Stator 4 mpos dead-end path C5-valve	1/16 x .4mm Titanium
C5-2C36	Stator 6 mpos dead-end path C5-valve	1/16 x .4mm Titanium
C5-2C38H	Stator 8 mpos (.180BC) dead-end path C5-valve	1/16 x .4mm Titanium
C5-2C40H	Stator 10 mpos (.180BC) dead-end path C5-valve	1/16 x .4mm PEAKE
C5-2C44	Stator 4 mpos dead-end path C5-valve	1/16 x .4mm PAEK
C5-2C46	Stator 6 mpos dead-end path C5-valve	1/16 x .4mm PAEK
C5-2C48H	Stator 8 mpos (.180BC) dead-end path C5-valve	1/16 x .4mm PAEK
C55-2000I	10 mpos valve motor sensor controller	1/16 x .4mm 50C/5000psi liq N60/H
C55-2000I-S	10 mpos valve motor sensor	1/16 x .4mm 50C/5000psi liq N60/H
C55-2000IX	10 mpos valve motor only	1/16 x .4mm 50C/5000psi liq N60/H
C55-2004I	4 mpos valve motor sensor controller	1/16 x .4mm 50C/5000psi liq N60/H
C55-2004I-S	4 mpos valve motor sensor	1/16 x .4mm 50C/5000psi liq N60/H
C55-2004IX	4 mpos valve motor only	1/16 x .4mm 50C/5000psi liq N60/H
C55-2006I	6 mpos valve motor sensor controller	1/16 x .4mm 50C/5000psi liq N60/H
C55-2006I-S	6 mpos valve motor sensor	1/16 x .4mm 50C/5000psi liq N60/H
C55-2006IX	6 mpos valve motor only	1/16 x .4mm 50C/5000psi liq N60/H
C55-2008I	8 mpos valve motor sensor controller	1/16 x .4mm 50C/5000psi liq N60/H
C55-2008I-S	8 mpos valve motor sensor	1/16 x .4mm 50C/5000psi liq N60/H
C55-2008IX	8 mpos valve motor only	1/16 x .4mm 50C/5000psi liq N60/H
C55-2340I	10 mpos valve motor sensor controller	1/16 x .4mm 50C/5000psi liq PAEK/E
C55-2340I-S	10 mpos valve motor sensor	1/16 x .4mm 50C/5000psi liq PAEK/E
C55-2340IX	10 mpos valve motor only	1/16 x .4mm 50C/5000psi liq PAEK/E
C55-2344I	4 mpos valve motor sensor controller	1/16 x .4mm 50C/5000psi liq PAEK/E
C55-2344I-S	4 mpos valve motor sensor	1/16 x .4mm 50C/5000psi liq PAEK/E
C55-2344IX	4 mpos valve motor only	1/16 x .4mm 50C/5000psi liq PAEK/E
C55-2346I	6 mpos valve motor sensor controller	1/16 x .4mm 50C/5000psi liq PAEK/E
C55-2346I-S	6 mpos valve motor sensor	1/16 x .4mm 50C/5000psi liq PAEK/E
C55-2346IX	6 mpos valve motor only	1/16 x .4mm 50C/5000psi liq PAEK/E
C55-2348I	8 mpos valve motor sensor controller	1/16 x .4mm 50C/5000psi liq PAEK/E
C55-2348I-S	8 mpos valve motor sensor	1/16 x .4mm 50C/5000psi liq PAEK/E
C55-2348IX	8 mpos valve motor only	1/16 x .4mm 50C/5000psi liq PAEK/E
C55-2C00	Stator 10 mpos dead-end path C55-valve	1/16 x .4mm N60
C55-2C04	Stator 4 mpos dead-end path C55-valve	1/16 x .4mm N60
C55-2C06	Stator 6 mpos dead-end path C55-valve	1/16 x .4mm N60
C55-2C08	Stator 8 mpos dead-end path C55-valve	1/16 x .4mm N60
C55-2C40	Stator 10 mpos dead-end path C55-valve	1/16 x .4mm PAEK