



# VICIValco-Cheminert PRODUCT LIST 2012

C55-2C44	Stator 4 mpos dead-end path C55-valve	1/16 x .4mm PAEK
C55-2C46	Stator 6 mpos dead-end path C55-valve	1/16 x .4mm PAEK
C55-2C48	Stator 8 mpos dead-end path C55-valve	1/16 x .4mm PAEK
C5H-2000	10 mpos dead-end path (.180BC) manual	1/16 x .4mm 75C/5000psi liq N60/H
C5H-2000A	10 mpos dead-end path (.180BC) air act	1/16 x .4mm 75C/5000psi liq N60/H
C5H-2000D	10 mpos dead-end path (.180BC) replacement	1/16 x .4mm 75C/5000psi liq N60/H
C5H-2000E	OBSOLETE USE C5H-2000EMT	
C5H-2000EMT	10 mpos dead-end path (.180BC) m-elect	1/16 x .4mm 75C/5000psi liq N60/H
C5H-2000EMTD	10 mpos dead-end path(.180BC) m-elect dual drive	1/16 x .4mm 75C/5000psi liq N60/H
C5H-2008	8 mpos dead-end path (.180BC) manual	1/16 x .4mm 75C/5000psi liq N60/H
C5H-2008A	8 mpos dead-end path (.180BC) air act	1/16 x .4mm 75C/5000psi liq N60/H
C5H-2008D	8 mpos dead-end path (.180BC) replacement	1/16 x .4mm 75C/5000psi liq N60/H
C5H-2008E	OBSOLETE USE C5H-2008EMT	
C5H-2008EMT	8 mpos dead-end path (.180BC) m-elect	1/16 x .4mm 75C/5000psi liq N60/H
C5H-2008EMTD	8 mpos dead-end path (.180BC) m-elect dual drive	1/16 x .4mm 75C/5000psi liq N60/H
C5H-2030	10 mpos dead-end path (.180BC) manual	1/16 x .4mm 75C/5000psi liq Ti/H
C5H-2030A	10 mpos dead-end path (.180BC) air act	1/16 x .4mm 75C/5000psi liq Ti/H
C5H-2030D	10 mpos dead-end path (.180BC) replacement	1/16 x .4mm 75C/5000psi liq Ti/H
C5H-2030E	OBSOLETE USE C5H-2030EMT	
C5H-2030EMT	10 mpos dead-end path (.180BC) m-elect	1/16 x .4mm 75C/5000psi liq Ti/H
C5H-2038	8 mpos dead-end path (.180BC) manual	1/16 x .4mm 75C/5000psi liq Ti/H
C5H-2038A	8 mpos dead-end path (.180BC) air act	1/16 x .4mm 75C/5000psi liq Ti/H
C5H-2038D	8 mpos dead-end path (.180BC) replacement	1/16 x .4mm 75C/5000psi liq Ti/H
C5H-2038E	OBSOLETE USE C5H-2038EMT	
C5H-2038EMT	8 mpos dead-end path (.180BC) m-elect	1/16 x .4mm 75C/5000psi liq Ti/H
C5H-2340	10 mpos dead-end path (.180BC) manual	1/16 x .4mm 50C/5000psi liq PAEK/E
C5H-2340A	10 mpos dead-end path (.180BC) air act	1/16 x .4mm 50C/5000psi liq PAEK/E
C5H-2340D	10 mpos dead-end path (.180BC) replacement	1/16 x .4mm 50C/5000psi liq PAEK/E
C5H-2340E	OBSOLETE USE C5H-2340EMT	
C5H-2340EMT	10 mpos dead-end path (.180BC) m-elect	1/16 x .4mm 50C/5000psi liq PAEK/E
C5H-2340EMTD	10 mpos dead-end path(.180BC) m-elect dual drive	1/16 x .4mm 50C/5000psi liq PAEK/E
C5H-2348	8 mpos dead-end path (.180BC) manual	1/16 x .4mm 50C/5000psi liq PAEK/E
C5H-2348A	8 mpos dead-end path (.180BC) air act	1/16 x .4mm 50C/5000psi liq PAEK/E
C5H-2348D	8 mpos dead-end path (.180BC) replacement	1/16 x .4mm 50C/5000psi liq PAEK/E
C5H-2348E	OBSOLETE USE C5H-2348EMT	
C5H-2348EMT	8 mpos dead-end path (.180BC) m-elect	1/16 x .4mm 50C/5000psi liq PAEK/E
C5H-2348EMTD	8 mpos dead-end path (.180BC) m-elect dual drive	1/16 x .4mm 50C/5000psi liq PAEK/E
C5M1KF	Cheminert manifold 1/4in -28 1/16in OD tubing	4 inlets 1 outlet .75mm bore CTFE
C5M1PK	Cheminert manifold 1/4in -28 1/16in OD tubing	4 inlets 1 outlet .75mm bore PEEK
C5M2KF	Cheminert manifold 1/4in -28 1/8in OD tubing	4 inlets 1 outlet 1.5mm bore CTFE
C5M2PK	Cheminert manifold 1/4in -28 1/8in OD tubing	4 inlets 1 outlet 1.5mm bore PEEK
C6-1006	6 port 2-pos valve cont. flow manual	1/16 x .25mm 75C/5000psi liq N60/H
C6-1006A	6 port 2-pos valve cont. flow air actuator	1/16 x .25mm 75C/5000psi liq N60/H
C6-1006D	6 port 2-pos valve cont. flow replacement	1/16 x .25mm 75C/5000psi liq N60/H
C6-1006E	6 port 2-pos valve cont. flow std. electric	1/16 x .25mm 75C/5000psi liq N60/H
C6-1006EH	6 port 2-pos valve cont. flow m-electric	1/16 x .25mm 75C/5000psi liq N60/H
C6-1346	6 port 2-pos valve cont. flow manual	1/16 x .25mm 50C/5000psi liq PAEK/E
C6-1346A	6 port 2-pos valve cont. flow air actuator	1/16 x .25mm 50C/5000psi liq PAEK/E
C6-1346D	6 port 2-pos valve cont. flow replacement	1/16 x .25mm 50C/5000psi liq PAEK/E
C6-1346E	6 port 2-pos valve cont. flow std. electric	1/16 x .25mm 50C/5000psi liq PAEK/E
C6-1346EH	6 port 2-pos valve cont. flow m-electric	1/16 x .25mm 50C/5000psi liq PAEK/E
C6-1C06	Stator 6 port 2-pos C6-valve	1/16 x .25mm N60
C6-1C46	Stator 6 port 2-pos cont. flow valve	1/16 x .25mm PAEK
C6-2006	6 port 2-pos valve cont. flow manual	1/16 x .4mm 75C/5000psi liq N60/H
C6-2006A	6 port 2-pos valve cont. flow air actuator	1/16 x .4mm 75C/5000psi liq N60/H
C6-2006D	6 port 2-pos valve cont. flow replacement	1/16 x .4mm 75C/5000psi liq N60/H
C6-2006E	6 port 2-pos valve cont. flow std. electric	1/16 x .4mm 75C/5000psi liq N60/H
C6-2006EH	6 port 2-pos valve cont. flow m-electric	1/16 x .4mm 75C/5000psi liq N60/H
C62-3180I	10 port 2-pos valve motor sensor controller	1/4in -28 x 0.75mm 75C/250psi liq PPS/E2
C62-3180I-S	10 port 2-pos valve motor sensor	1/4in -28 x 0.75mm 75C/250psi liq PPS/E2
C62-3184I	4 port 2-pos valve motor sensor controller	1/4in -28 x 0.75mm 75C/250psi liq PPS/E2