

VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]
> Cat.#s

> Current System AUD Prices



C62-3184I-S	4 port 2-pos valve motor sensor	1/4in -28 x 0.75mm 75C/250psi liq PPS/E2
C62-3186I	6 port 2-pos valve motor sensor controller	1/4in -28 x 0.75mm 50C/250psi liq PPS/E2
C62-3186I-S	6 port 2-pos valve motor sensor	1/4in -28 x 0.75mm 75C/250psi liq PPS/E2
C62-3188I	8 port 2-pos valve motor sensor controller	1/4in -28 x 0.75mm 75C/250psi liq PPS/E2
C62-3188I-S	8 port 2-pos valve motor sensor	1/4in -28 x 0.75mm 75C/250psi liq PPS/E2
C6-2346	6 port 2-pos valve cont. flow manual	1/16 x .4mm 50C/5000psi liq PAEK/E
C6-2346A	6 port 2-pos valve cont. flow air actuator	1/16 x .4mm 50C/5000psi liq PAEK/E
C6-2346D	6 port 2-pos valve cont. flow replacement	1/16 x .4mm 50C/5000psi liq PAEK/E
C6-2346E	6 port 2-pos valve cont. flow std. electric	1/16 x .4mm 50C/5000psi liq PAEK/E
C6-2346EH	6 port 2-pos valve cont. flow m-electric	1/16 x .4mm 50C/5000psi liq PAEK/E
C62-6180I	10 port 2-pos valve motor sensor controller	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C62-6180I-S	10 port 2-pos valve motor sensor	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C62-6184I	4 port 2-pos valve motor sensor controller	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C62-6184I-S	4 port 2-pos valve motor sensor	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C62-6186I	6 port 2-pos valve motor sensor controller	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C62-6186I-S	6 port 2-pos valve motor sensor	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C62-6188I	8 port 2-pos valve motor sensor controller	1/4in -28 x 1.5mm 50C/250psi liq PPS/E2
C62-6188I-S	6 port 2-pos valve motor sensor	1/4in -28 x 1.5mm 75C/250psi liq PPS/E2
C6-2C06	Stator 6 port 2-pos cont. flow valve	1/16 x .4mm N60
C6-2C46	Stator 6 port 2-pos cont. flow valve	1/16 x .4mm PAEK
C62Z-3180I	10 port 2-pos valve motor sensor controller	1/16in x .75mm 50C/250psi liq PPS/E2
C62Z-3180I-S	10 port 2-pos valve motor sensor	1/16in x .75mm 50C/250psi liq PPS/E2
C62Z-3184I	4 port 2-pos valve motor sensor controller	1/16in x .75mm 50C/250psi liq PPS/E2
C62Z-3184I-S	4 port 2-pos valve motor sensor	1/16in x .75mm 50C/250psi liq PPS/E2
C62Z-3186I	6 port 2-pos valve motor sensor controller	1/16in x .75mm 50C/250psi liq PPS/E2
C62Z-3186I-S	6 port 2-pos valve motor sensor	1/16in x .75mm 50C/250psi liq PPS/E2
C62Z-3188I	8 port 2-pos valve motor sensor controller	1/16in x .75mm 50C/250psi liq PPS/E2
C62Z-3188I-S	8 port 2-pos valve motor sensor	1/16in x .75mm 50C/250psi liq PPS/E2
C65-3180I	10 mpos dead-end path motor sensor controller	1/4in -28 x 0.75mm 50C/250psi liq PPS/E2
C65-3180I-S	10 mpos dead-end path motor sensor	1/4in -28 x 0.75mm 50C/250psi liq PPS/E2
C65-3184I	4 mpos dead-end path motor sensor controller	1/4in -28 x 0.75mm 50C/250psi liq PPS/E2
C65-3184I-S	4 mpos dead-end path motor sensor	1/4in -28 x 0.75mm 50C/250psi liq PPS/E2
C65-3186I	6 mpos dead-end path motor sensor controller	1/4in -28 x 0.75mm 50C/250psi liq PPS/E2
C65-3186I-S	6 mpos dead-end path motor sensor	1/4in -28 x 0.75mm 50C/250psi liq PPS/E2
C65-3188I	8 mpos dead-end path motor sensor controller	1/4in -28 x 0.75mm 50C/250psi liq PPS/E2
C65-3188I-S	8 mpos dead-end path motor sensor	1/4in -28 x 0.75mm 50C/250psi liq PPS/E2
C65-6180I	10 mpos dead-end path motor sensor controller	1/4in -28 x 0.75mm 50C/250psi liq PPS/E2
C65-6180I-S	10 mpos dead-end path motor sensor	1/4in -28 x 0.75mm 50C/250psi liq PPS/E2
C65-6184I	4 mpos dead-end path motor sensor controller	1/4in -28 x 1.5mm 50C/250psi liq PPS/E2
C65-6184I-S	4 mpos dead-end path motor sensor	1/4in -28 x 1.5mm 50C/250psi liq PPS/E2
C65-6186I	6 mpos dead-end path motor sensor controller	1/4in -28 x 1.5mm 50C/250psi liq PPS/E2
C65-6186I-S	6 mpos dead-end path motor sensor	1/4in -28 x 1.5mm 50C/250psi liq PPS/E2
C65-6188I	8 mpos dead-end path motor sensor controller	1/4in -28 x 1.5mm 50C/250psi liq PPS/E2
C65-6188I-S	8 mpos dead-end path motor sensor	1/4in -28 x 1.5mm 50C/250psi liq PPS/E2
C65Z-3180I	10 mpos dead-end path motorsensorw/o controller	1/16in x .75mm 50C/250psi liq PPS/E2
C65Z-3180I-S	10 mpos dead-end pathmotor sensorw/o controller	1/16in x .75mm 50C/250psi liq PPS/E2
C65Z-3184I	4 mpos dead-end path integrated actuator	1/16in x .75mm 50C/250psi liq PPS/E2
C65Z-3184I-S	4 mpos dead-end path motor sensorw/o controller	1/16in x .75mm 50C/250psi liq PPS/E2
C65Z-3186I	6 mpos dead-end path integrated actuator	1/16in x .75mm 50C/250psi liq PPS/E2
C65Z-3186I-S	6 mpos dead-end path motor sensorw/o controller	1/16in x .75mm 50C/250psi liq PPS/E2
C65Z-3188I	8 mpos dead-end path integrated actuator	1/16in x .75mm 50C/250psi liq PPS/E2
C65Z-3188I-S	8 mpos dead-end path motor sensorw/o controller	1/16in x .75mm 50C/250psi liq PPS/E2
C6UW	!!! RECOMMEND 2C6UW	SUPPLIED WITH LARGER HANDLE
C6UWE	6 port 2-pos valve manual	1/16 x .75mm 225C/400psi gas N60/E
C6W	6 port 2-pos valve manual	1/16 x .4mm 75C/5000psi liq N60/H
C6WE	6 port 2-pos valve manual	1/16 x .4mm 225C/400psi gas N60/E
C72-16R0	Rotor seal 10 port 2-pos C72-valve	1/16 x .25mm 50C/all pressures liqE3
C72-16R4	Rotor seal 4 port 2-pos C72-valve	1/16 x .25mm 50C/all pressures liqE3
C72-16R6	Rotor seal 6 port 2-pos C72-valve	1/16 x .25mm 50C/all pressures liqE3
C72-16R8	Rotor seal 8 port 2-pos C72-valve	1/16 x .25mm 50C/all pressures liqE3
C72-1C90	Stator 10 port 2-pos C72-valve	1/16 x .25mm N60C