

VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]
> CatL#s

> Current System AUD Prices



C72-1C94	Stator 4 port 2-pos C72-valve	1/16 x .25mmN60C
C72-1C96	Stator 6 port 2-pos C72-valve	1/16 x .25mm N60C
C72-1C98	Stator 8 port 2-pos C72-valve	1/16 x .25mm N60C
C72H-1690	10 port 2-pos valve	1/16 x .25mm 50C/10000psi liq N60C/E3
C72H-1690A	10 port 2-pos valve air actuator	1/16 x .25mm 50C/10000psi liq N60C/E3
C72H-1690D	10 port 2-pos valve replacement	1/16 x .25mm 50C/10000psi liq N60C/E3
C72H-1690E	10 port 2-pos valve standard electric actuator	1/16 x .25mm 50C/10000psi liq N60C/E3
C72H-1690ED	10 port 2-pos valve m-electric	1/16 x .25mm 50C/10000psi liq N60C/E3
C72H-1694	4 port 2-pos valve	1/16 x .25mm 50C/10000psi liq N60C/E3
C72H-1694A	4 port 2-pos valve air actuator	1/16 x .25mm 50C/10000psi liq N60C/E3
C72H-1694D	4 port 2-pos valve replacement	1/16 x .25mm 50C/10000psi liq N60C/E3
C72H-1694E	4 port 2-pos valve standard electric actuator	1/16 x .25mm 50C/10000psi liq N60C/E3
C72H-1694EH	4 port 2-pos valve m-electric	1/16 x .25mm 50C/10000psi liq N60C/E3
C72H-1696	6 port 2-pos valve manual	1/16 x .25mm 50C/10000psi liq N60C/E3
C72H-1696A	6 port 2-pos valve air actuator	1/16 x .25mm 50C/10000psi liq N60C/E3
C72H-1696D	6 port 2-pos valve replacement	1/16 x .25mm 50C/10000psi liq N60C/E3
C72H-1696E	6 port 2-pos valve standard electric actuator	1/16 x .25mm 50C/10000psi liq N60C/E3
C72H-1696EH	6 port 2-pos valve m-electric	1/16 x .25mm 50C/10000psi liq N60C/E3
C72H-1698	8 port 2-pos valve manual	1/16 x .25mm 50C/10000psi liq N60C/E3
C72H-1698A	8 port 2-pos valve air actuator	1/16 x .25mm 50C/10000psi liq N60C/E3
C72H-1698D	8 port 2-pos valve replacement	1/16 x .25mm 50C/10000psi liq N60C/E3
C72H-1698E	8 port 2-pos valve standard electric actuator	1/16 x .25mm 50C/10000psi liq N60C/E3
C72H-1698ED	8 port 2-pos valve m-electric	1/16 x .25mm 50C/10000psi liq N60C/E3
C72M-46R6	Rotor seal 6 port 2-pos C72M-valve	360µm .10mm 50C/all pressures liqE3
C72M-4C94	Stator 4 port 2-pos C72M-valve	360um .10mm N60C
C72M-4C96	Stator 6 port 2-pos C72M-valve	360um .10mm N60C
C72M-66R0	Rotor seal 10 port 2-pos C72M-valve	360µm .15mm 50C/all pressures liqE3
C72M-66R6	Rotor seal 6 port 2-pos C72M-valve	360µm .15mm 50C/all pressures liqE3
C72M-6C90	Stator 10 port 2-pos C72M-valve	360um .15mm N60C
C72M-6C96	Stator 6 port 2-pos C72M-valve	360um .15mm N60C
C72MH-4696D	6 port 2-pos valve replacement	360um x .10mm 50C/10000psi liq N60C/E3
C72MH-4696EH	6 port 2-pos valve m-electric	360um x .10mm 50C/10000psi liq N60C/E3
C72MU-4694	4 port 2-pos valve manual	360um x .10mm 50C/20000psi liq N60C/E3
C72MU-4694A	4 port 2-pos valve air act	360um x .10mm 50C/20000psi liq N60C/E3
C72MU-4694D	4 port 2-pos valve replacement	360um x .10mm 50C/20000psi liq N60C/E3
C72MU-4694E	4 port 2-pos valve std-elect	360um x .10mm 50C/20000psi liq N60C/E3
C72MU-4694EH	4 port 2-pos valve m-elect	360um x .10mm 50C/20000psi liq N60C/E3
C72MU-4696	6 port 2-pos valve manual	360um x .10mm 50C/20000psi liq N60C/E3
C72MU-4696A	6 port 2-pos valve air act	360um x .10mm 50C/20000psi liq N60C/E3
C72MU-4696D	6 port 2-pos valve replacement	360um x .10mm 50C/20000psi liq N60C/E3
C72MU-4696E	6 port 2-pos valve std-elect	360um x .10mm 50C/20000psi liq N60C/E3
C72MU-4696EH	6 port 2-pos valve m-elect	360um x .10mm 50C/20000psi liq N60C/E3
C72MX-6690	10 port 2-pos valve manual	360um x .15mm 50C/15000psi liq N60C/E3
C72MX-6690A	10 port 2-pos valve air act.	360um x .15mm 50C/15000psi liq N60C/E3
C72MX-6690D	10 port 2-pos valve replacement	360um x .15mm 50C/15000psi liq N60C/E3
C72MX-6690E	10 port 2-pos valve std-elect.	360um x .15mm 50C/15000psi liq N60C/E3
C72MX-6690ED	10 port 2-pos valve m-elect.	360um x .15mm 50C/15000psi liq N60C/E3
C72MX-6696	6 port 2-pos valve manual	360um x .15mm 50C/15000psi liq N60C/E3
C72MX-6696A	6 port 2-pos valve air act.	360um x .15mm 50C/15000psi liq N60C/E3
C72MX-6696D	6 port 2-pos valve replacement	360um x .15mm 50C/15000psi liq N60C/E3
C72MX-6696E	6 port 2-pos valve std-elect.	360um x .15mm 50C/15000psi liq N60C/E3
C72MX-6696EH	6 port 2-pos valve m-elect.	360um x .15mm 50C/15000psi liq N60C/E3
C72N-66R0	Rotor seal 10 port 2-pos C72N-valve	1/32 x .15mm 50C/all pressures liqE3
C72N-66R6	Rotor seal 6 port 2-pos C72N-valve	1/32 x .15mm 50C/all pressures liqE3
C72N-6C90	Stator 10 port 2-pos C2N-valve	1/32 x .15mm N60C
C72N-6C96	Stator 6 port 2-pos C2N-valve	1/32 x .15mm N60C
C72NX-6690	10 port 2-pos valve manual	1/32 x .15mm 50C/15000psi liq N60C/E3
C72NX-6690A	10 port 2-pos valve air actuator	1/32 x .15mm 50C/15000psi liq N60C/E3
C72NX-6690D	10 port 2-pos valve replacement	1/32 x .15mm 50C/15000psi liq N60C/E3
C72NX-6690E	10 port 2-pos valve standard electric actuator	1/32 x .15mm 50C/15000psi liq N60C/E3
C72NX-6690ED	10 port 2-pos valve m-electric	1/32 x .15mm 50C/15000psi liq N60C/E3