

VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]
> Cat.#s

> Current System AUD Prices



C72NX-6696	6 port 2-pos valve manual	1/32 x .15mm 50C/15000psi liq N60C/E3
C72NX-6696A	6 port 2-pos valve air actuator	1/32 x .15mm 50C/15000psi liq N60C/E3
C72NX-6696D	6 port 2-pos valve replacement	1/32 x .15mm 50C/15000psi liq N60C/E3
C72NX-6696E	6 port 2-pos valve standard electric actuator	1/32 x .15mm 50C/15000psi liq N60C/E3
C72NX-6696EH	6 port 2-pos valve m-electric	1/32 x .15mm 50C/15000psi liq N60C/E3
C72X-1690	10 port 2-pos valvemanual	1/16 x .25mm 50C/15000psi liq N60C/E3
C72X-1690A	10 port 2-pos valve air actuator	1/16 x .25mm 50C/15000psi liq N60C/E3
C72X-1690D	10 port 2-pos valve replacement	1/16 x .25mm 50C/15000psi liq N60C/E3
C72X-1690E	10 port 2-pos valve standard electric actuator	1/16 x .25mm 50C/15000psi liq N60C/E3
C72X-1690ED	10 port 2-pos valve m-electric	1/16 x .25mm 50C/15000psi liq N60C/E3
C72X-1694	4 port 2-pos valvemanual	1/16 x .25mm 50C/15000psi liq N60C/E3
C72X-1694A	4 port 2-pos valve air actuator	1/16 x .25mm 50C/15000psi liq N60C/E3
C72X-1694D	4 port 2-pos valve replacement	1/16 x .25mm 50C/15000psi liq N60C/E3
C72X-1694E	4 port 2-pos valve standard electric actuator	1/16 x .25mm 50C/15000psi liq N60C/E3
C72X-1694EH	4 port 2-pos valve m-electric	1/16 x .25mm 50C/15000psi liq N60C/E3
C72X-1696	6 port 2-pos valve manual	1/16 x .25mm 50C/15000psi liq N60C/E3
C72X-1696A	6 port 2-pos valve air actuator	1/16 x .25mm 50C/15000psi liq N60C/E3
C72X-1696D	6 port 2-pos valve replacement	1/16 x .25mm 50C/15000psi liq N60C/E3
C72X-1696E	6 port 2-pos valve standard electric actuator	1/16 x .25mm 50C/15000psi liq N60C/E3
C72X-1696EH	6 port 2-pos valve m-electric	1/16 x .25mm 50C/15000psi liq N60C/E3
C72X-1698	8 port 2-pos valvemanual	1/16 x .25mm 50C/15000psi liq N60C/E3
C72X-1698A	8 port 2-pos valve air actuator	1/16 x .25mm 50C/15000psi liq N60C/E3
C72X-1698D	8 port 2-pos valve replacement	1/16 x .25mm 50C/15000psi liq N60C/E3
C72X-1698E	8 port 2-pos valve standard electric actuator	1/16 x .25mm 50C/15000psi liq N60C/E3
C72X-1698ED	8 port 2-pos valve m-electric	1/16 x .25mm 50C/15000psi liq N60C/E3
C74-16R-.01	Rotor seal 4 port 2-pos int vol valve C74-valve	1/16 x .25mm 50C/all pressures liq .01ul E3
C74-16R-.02	Rotor seal 4 port 2-pos int vol valve C74-valve	1/16 x .25mm 50C/all pressures liq .02ul E3
C74-16R-.05	Rotor seal 4 port 2-pos int vol valve C74-valve	1/16 x .25mm 50C/all pressures liq .05ul E3
C74-1C9	Stator 4 port 2-pos int vol C74-valve	1/16 x .25mm N60C
C74H-1694-.01	4 port 2-pos int vol valve manual	1/16 x .25mm 50C/10000psi liq .01ul N60C/E3
C74H-1694-.01A	4 port 2-pos int vol valve air actuator	1/16 x .25mm 50C/10000psi liq .01ul N60C/E3
C74H-1694-.01D	4 port 2-pos int vol valve replacement	1/16 x .25mm 50C/10000psi liq .01ul N60C/E3
C74H-1694-.01E	4 port 2-pos int vol valve std-electric	1/16 x .25mm 50C/10000psi liq .01ul N60C/E3
C74H-1694-.01EH	4 port 2-pos int vol valve m-electric	1/16 x .25mm 50C/10000psi liq .01ul N60C/E3
C74H-1694-.02	4 port 2-pos int vol valve manual	1/16 x .25mm 50C/10000psi liq .02ul N60C/E3
C74H-1694-.02A	4 port 2-pos int vol valve air actuator	1/16 x .25mm 50C/10000psi liq .02ul N60C/E3
C74H-1694-.02D	4 port 2-pos int vol valve replacement	1/16 x .25mm 50C/10000psi liq .02ul N60C/E3
C74H-1694-.02E	4 port 2-pos int vol valve std-electric	1/16 x .25mm 50C/10000psi liq .02ul N60C/E3
C74H-1694-.02EH	4 port 2-pos int vol valve m-electric	1/16 x .25mm 50C/10000psi liq .02ul N60C/E3
C74H-1694-.05	4 port 2-pos int vol valve manual	1/16 x .25mm 50C/10000psi liq .05ul N60C/E3
C74H-1694-.05A	4 port 2-pos int vol valve air actuator	1/16 x .25mm 50C/10000psi liq .05ul N60C/E3
C74H-1694-.05D	4 port 2-pos int vol valve replacement	1/16 x .25mm 50C/10000psi liq .05ul N60C/E3
C74H-1694-.05E	4 port 2-pos int vol valve std-electric	1/16 x .25mm 50C/10000psi liq .05ul N60C/E3
C74H-1694-.05EH	4 port 2-pos int vol valve m-electric	1/16 x .25mm 50C/10000psi liq .05ul N60C/E3
C74N-66R-.004	Rotor seal 4 port 2-pos int vol valve C74N-valve	1/32 x .15mm 50C/all pressures liq .004ul E3
C74N-66R-.01	Rotor seal 4 port 2-pos int vol valve C74N-valve	1/32 x .15mm 50C/all pressures liq .01ul E3
C74N-66R-.02	Rotor seal 4 port 2-pos int vol valve C74N-valve	1/32 x .15mm 50C/all pressures liq .02ul E3
C74N-6C9	Stator 4 port 2-pos int vol C74N-valve	1/32 x .15mm N60C
C74NX-6694-.01	4 port 2-pos int vol valve manual	1/32 x .15mm 50C/15000psi liq .01ul N60C/E3
C74NX-6694-.004	4 port 2-pos int vol valve manual	1/32 x .15mm 50C/15000psi liq .004ul N60C/E3
C74NX-6694-.004A	4 port 2-pos int vol valve air actuator	1/32 x .15mm 50C/15000psi liq .004ul N60C/E3
C74NX-6694-.004D	4 port 2-pos int vol valve replacement valve	1/32 x .15mm 50C/15000psi liq .004ul N60C/E3
C74NX-6694-.004E	4 port 2-pos int vol valve std. electric actuator	1/32 x .15mm 50C/15000psi liq .004ul N60C/E3
C74NX-6694-.004EH	4 port 2-pos int vol valve microelectric actuator	1/32 x .15mm 50C/15000psi liq .01ul N60C/E3
C74NX-6694-.01	4 port 2-pos int vol valve manual	1/32 x .15mm 50C/15000psi liq .01ul N60C/E3
C74NX-6694-.01A	4 port 2-pos int vol valve air actuator	1/32 x .15mm 50C/15000psi liq .01ul N60C/E3
C74NX-6694-.01D	4 port 2-pos int vol valve replacement valve	1/32 x .15mm 50C/15000psi liq .01ul N60C/E3
C74NX-6694-.01E	4 port 2-pos int vol valve std. electric actuator	1/32 x .15mm 50C/15000psi liq .01ul N60C/E3
C74NX-6694-.01EH	4 port 2-pos int vol valve microelectric actuator	1/32 x .15mm 50C/15000psi liq .01ul N60C/E3
C74NX-6694-.02	4 port 2-pos int vol valve manual	1/32 x .15mm 50C/15000psi liq .02ul N60C/E3
C74NX-6694-.02A	4 port 2-pos int vol valve air actuator	1/32 x .15mm 50C/15000psi liq .02ul N60C/E3