

# VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]  
> CatL#s

> Current System AUD Prices



C74NX-6694-.02D	4 port 2-pos int vol valve replacement valve	1/32 x .15mm 50C/15000psi liq .02ul N60C/E3
C74NX-6694-.02E	4 port 2-pos int vol valve std. electric actuator	1/32 x .15mm 50C/15000psi liq .02ul N60C/E3
C74NX-6694-.02EH	4 port 2-pos int vol valve microelectric actuator	1/32 x .15mm 50C/15000psi liq .02ul N60C/E3
C74X-1694-.01	4 port 2-pos int vol valve manual	1/16 x .25mm 50C/15000psi liq .01ul N60C/E3
C74X-1694-.01A	4 port 2-pos int vol valve air actuator	1/16 x .25mm 50C/15000psi liq .01ul N60C/E3
C74X-1694-.01D	4 port 2-pos int vol valve replacement	1/16 x .25mm 50C/15000psi liq .01ul N60C/E3
C74X-1694-.01E	4 port 2-pos int vol valve std-electric	1/16 x .25mm 50C/15000psi liq .01ul N60C/E3
C74X-1694-.01EH	4 port 2-pos int vol valve m-electric	1/16 x .25mm 50C/15000psi liq .01ul N60C/E3
C74X-1694-.02	4 port 2-pos int vol valve manual	1/16 x .25mm 50C/15000psi liq .02ul N60C/E3
C74X-1694-.02A	4 port 2-pos int vol valve air actuator	1/16 x .25mm 50C/15000psi liq .02ul N60C/E3
C74X-1694-.02D	4 port 2-pos int vol valve replacement	1/16 x .25mm 50C/15000psi liq .02ul N60C/E3
C74X-1694-.02E	4 port 2-pos int vol valve std-electric	1/16 x .25mm 50C/15000psi liq .02ul N60C/E3
C74X-1694-.02EH	4 port 2-pos int vol valve m-electric	1/16 x .25mm 50C/15000psi liq .02ul N60C/E3
C74X-1694-.05	4 port 2-pos int vol valve manual	1/16 x .25mm 50C/15000psi liq .05ul N60C/E3
C74X-1694-.05A	4 port 2-pos int vol valve air actuator	1/16 x .25mm 50C/15000psi liq .05ul N60C/E3
C74X-1694-.05D	4 port 2-pos int vol valve replacement	1/16 x .25mm 50C/15000psi liq .05ul N60C/E3
C74X-1694-.05E	4 port 2-pos int vol valve std-electric	1/16 x .25mm 50C/15000psi liq .05ul N60C/E3
C74X-1694-.05EH	4 port 2-pos int vol valve m-electric	1/16 x .25mm 50C/15000psi liq .05ul N60C/E3
C75-16R0	Rotor seal 11 port 10-pos C75-valve	1/16 x .25mm 50C/all pressures liqE3
C75-16R6	Rotor seal 7 port 6-pos C75-valve	1/16 x .25mm 50C/all pressures liqE3
C75-16R8	Rotor seal 9 port 8-pos C75-valve	1/16 x .25mm 50C/all pressures liqE3
C75-1C90	Stator 11 port 10-pos C75-valve	1/16 x .25mm N60C
C75-1C96	Stator 7 port 6-pos C75-valve	1/16 x .25mm N60C
C75-1C98	Stator 7 port 6-pos C75-valve	1/16 x .25mm N60C
C75H-1690A	10 mpos dead-end path air actuator	1/16 x .25mm 50C/10'000psi liq N60C/E3
C75H-1690D	10 mpos dead-end path replacement	1/16 x .25mm 50C/10'000psi liq N60C/E3
C75H-1690E	10 mpos dead-end path standard electric actuator	1/16 x .25mm 50C/10'000psi liq N60C/E3
C75H-1690EMT	10 mpos dead-end path m-electric	1/16 x .25mm 50C/10'000psi liq N60C/E3
C75H-1696A	6 mpos dead-end path air actuator	1/16 x .25mm 50C/10'000psi liq N60C/E3
C75H-1696D	6 mpos dead-end path replacement	1/16 x .25mm 50C/10'000psi liq N60C/E3
C75H-1696E	6 mpos dead-end path standard electric actuator	1/16 x .25mm 50C/10'000psi liq N60C/E3
C75H-1696EMH	6 mpos dead-end path m-electric	1/16 x .25mm 50C/10'000psi liq N60C/E3
C75H-1698A	8 mpos dead-end path air actuator	1/16 x .25mm 50C/10'000psi liq N60C/E3
C75H-1698D	8 mpos dead-end path replacement	1/16 x .25mm 50C/10'000psi liq N60C/E3
C75H-1698E	8 mpos dead-end path standard electric actuator	1/16 x .25mm 50C/10'000psi liq N60C/E3
C75H-1698EMT	8 mpos dead-end path m-electric	1/16 x .25mm 50C/10'000psi liq N60C/E3
C75N-66R0	Rotor seal 10 mpos C75N-valve dead-end path	1/32 x .15mm 50C/all pressures liqE3
C75N-66R6	Rotor seal 6 mpos C75N-valve dead-end path	1/32 x .15mm 50C/all pressures liqE3
C75N-66R8	Rotor seal 8 mpos C75N-valve dead-end path	1/32 x .15mm 50C/all pressures liqE3
C75N-6C90	Stator 10 mpos dead-end path C75N-valve	1/32 x .15mm N60C
C75N-6C96	Stator 6 mpos dead-end path C75N-valve	1/32 x .15mm N60C
C75N-6C98	Stator 8 mpos dead-end path C75N-valve	1/32 x .15mm N60C
C75NX-6690A	10 mpos dead-end path air actuator	1/32 x .15mm 50C/15000psi liq N60C/E3
C75NX-6690D	10 mpos dead-end path replacement	1/32 x .15mm 50C/15000psi liq N60C/E3
C75NX-6690E	10 mpos dead-end path standard electric actuator	1/32 x .15mm 50C/15000psi liq N60C/E3
C75NX-6690EMT	10 mpos dead-end path m-electric	1/32 x .15mm 50C/15000psi liq N60C/E3
C75NX-6696A	6 mpos dead-end path air actuator	1/32 x .15mm 50C/15000psi liq N60C/E3
C75NX-6696D	6 mpos dead-end path replacement	1/32 x .15mm 50C/15000psi liq N60C/E3
C75NX-6696E	6 mpos dead-end path standard electric actuator	1/32 x .15mm 50C/15000psi liq N60C/E3
C75NX-6696EMH	6 mpos dead-end path m-electric	1/32 x .15mm 50C/15000psi liq N60C/E3
C75NX-6698A	8 mpos dead-end path air actuator	1/32 x .15mm 50C/15000psi liq N60C/E3
C75NX-6698D	8 mpos dead-end path replacement	1/32 x .15mm 50C/15000psi liq N60C/E3
C75NX-6698E	8 mpos dead-end path standard electric actuator	1/32 x .15mm 50C/15000psi liq N60C/E3
C75NX-6698EMT	8 mpos dead-end path m-electric	1/32 x .15mm 50C/15000psi liq N60C/E3
C8UW	!!! RECOMMEND 2C8UW	SUPPLIED WITH LARGER HANDLE
C8UWE	8 port 2-pos valve manual	1/16 x .75mm 225C/400psi gas N60/E
C8W	8 port 2-pos valve manual	1/16 x .4mm 75C/5000psi liq N60/H
C8WE	8 port 2-pos valve manual	1/16 x .4mm 225C/400psi gas N60/E
C9M1KF	Cheminert manifold 1/4in -28 1/16in OD tubing	8 inlets 1 outlet .75mm bore CTFE
C9M1PK	Cheminert manifold 1/4in -28 1/16in OD tubing	8 inlets 1 outlet .75mm bore PEEK
C9M2KF	Cheminert manifold 1/4in -28 1/8in OD tubing	8 inlets 1 outlet 1.5mm bore CTFE