



# VICIValco-Cheminert PRODUCT LIST 2012

CFS-E03018-100A	GC-Column FS ValcoBond VB-624	30m length ID 0.18mm df 1.00um
CFS-E03025-140A	GC-Column FS ValcoBond VB-624	30m length ID 0.25mm df 1.40um
CFS-E03032-180A	GC-Column FS ValcoBond VB-624	30m length ID 0.32mm df 1.80um
CFS-E03053-300A	GC-Column FS ValcoBond VB-624	30m length ID 0.53mm df 3.00um
CFS-E04018-100A	GC-Column FS ValcoBond VB-624	40m length ID 0.18mm df 1.00um
CFS-E06025-140A	GC-Column FS ValcoBond VB-624	60m length ID 0.25mm df 1.40um
CFS-E06032-180A	GC-Column FS ValcoBond VB-624	60m length ID 0.32mm df 1.80um
CFS-E06053-300A	GC-Column FS ValcoBond VB-624	60m length ID 0.53mm df 3.00um
CFS-E07553-300A	GC-Column FS ValcoBond VB-624	75m length ID 0.53mm df 3.00um
CFS-F01525-025A	GC-Column FS ValcoBond VB-1701	15m length ID 0.25mm df 0.25um
CFS-F01525-050A	GC-Column FS ValcoBond VB-1701	15m length ID 0.25mm df 0.50um
CFS-F01532-025A	GC-Column FS ValcoBond VB-1701	15m length ID 0.32mm df 0.25um
CFS-F01532-050A	GC-Column FS ValcoBond VB-1701	15m length ID 0.32mm df 0.50um
CFS-F01532-100A	GC-Column FS ValcoBond VB-1701	15m length ID 0.32mm df 1.00um
CFS-F01553-050A	GC-Column FS ValcoBond VB-1701	15m length ID 0.53mm df 0.50um
CFS-F01553-100A	GC-Column FS ValcoBond VB-1701	15m length ID 0.53mm df 1.00um
CFS-F03025-025A	GC-Column FS ValcoBond VB-1701	30m length ID 0.25mm df 0.25um
CFS-F03025-050A	GC-Column FS ValcoBond VB-1701	30m length ID 0.25mm df 0.50um
CFS-F03032-025A	GC-Column FS ValcoBond VB-1701	30m length ID 0.32mm df 0.25um
CFS-F03032-050A	GC-Column FS ValcoBond VB-1701	30m length ID 0.32mm df 0.50um
CFS-F03032-100A	GC-Column FS ValcoBond VB-1701	30m length ID 0.32mm df 1.00um
CFS-F03053-050A	GC-Column FS ValcoBond VB-1701	30m length ID 0.53mm df 0.50um
CFS-F03053-100A	GC-Column FS ValcoBond VB-1701	30m length ID 0.53mm df 1.00um
CFS-F06025-025A	GC-Column FS ValcoBond VB-1701	60m length ID 0.25mm df 0.25um
CFS-F06025-050A	GC-Column FS ValcoBond VB-1701	60m length ID 0.25mm df 0.50um
CFS-F06032-025A	GC-Column FS ValcoBond VB-1701	60m length ID 0.32mm df 0.25um
CFS-F06032-050A	GC-Column FS ValcoBond VB-1701	60m length ID 0.32mm df 0.50um
CFS-F06032-100A	GC-Column FS ValcoBond VB-1701	60 length ID 0.32mm df 1.00um
CFS-F06053-050A	GC-Column FS ValcoBond VB-1701	60m length ID 0.53mm df 0.50um
CFS-F06053-100A	GC-Column FS ValcoBond VB-1701	60 length ID 0.53mm df 1.00um
CFS-G01010-010A	GC-Column FS ValcoBond VB-Wax	10m length ID 0.10mm df 0.10um
CFS-G01018-018A	GC-Column FS ValcoBond VB-WAX	10m length ID 0.18mm df 0.18um
CFS-G01525-025A	GC-Column FS ValcoBond VB-Wax	VB-Wax column 15m x 0.25mm ID x 0.25df
CFS-G01532-025A	GC-Column FS ValcoBond VB-WAX	15m length ID 0.32mm df 0.25um
CFS-G01532-050A	GC-Column FS ValcoBond VB-WAX	15m length ID 0.32mm df 0.50um
CFS-G01532-100A	GC-Column FS ValcoBond VB-WAX	15m length ID 0.32mm df 1.00um
CFS-G01553-050A	GC-Column FS ValcoBond VB-WAX	15m length ID 0.53mm df 0.50um
CFS-G01553-100A	GC-Column FS ValcoBond VB-Wax	VB-Wax column 15m x 0.53mm ID x 1.00df
CFS-G02010-010A	GC-Column FS ValcoBond VB-WAX	20m length ID 0.10mm df 0.10um
CFS-G02018-018A	GC-Column FS ValcoBond VB-WAX	20m length ID 0.18mm df 0.18um
CFS-G03025-025A	GC-Column FS ValcoBond VB-Wax	30m length ID 0.25mm df 0.25um
CFS-G03032-025A	GC-Column FS ValcoBond VB-Wax	30m length ID 0.32mm df 0.25um
CFS-G03032-050A	GC-Column FS ValcoBond VB-Wax	30m length ID 0.32mm df 0.50um
CFS-G03032-100A	GC-Column FS ValcoBond VB-Wax	30m length ID 0.32mm df 1.00um
CFS-G03053-050A	GC-Column FS ValcoBond VB-Wax	30m length ID 0.53mm df 0.50um
CFS-G03053-100A	GC-Column FS ValcoBond VB-Wax	30m length ID 0.53mm df 1.00um
CFS-G06025-025A	GC-Column FS ValcoBond VB-Wax	60m length ID 0.25mm df 0.25um
CFS-G06032-025A	GC-Column FS ValcoBond VB-Wax	60m length ID 0.32mm df 0.25um
CFS-G06032-050A	GC-Column FS ValcoBond VB-Wax	60m length ID 0.32mm df 0.50um
CFS-G06053-100A	GC-Column FS ValcoBond VB-Wax	60m length ID 0.53mm df 1um
CFSL100FEP	Cheminert sample loop 100ul	flangeless connections 1/4in -28 FEP
CFSL100PK	Cheminert sample loop 100ul	flangeless connections 1/4in -28 PEEK
CFSL100TF	Cheminert sample loop 100ul	flangeless connections 1/4in -28 PTFE
CFSL1KFEP	Cheminert sample loop 1ml	flangeless connections 1/4in -28 FEP
CFSL1KPK	Cheminert sample loop 1ml	flangeless connections 1/4in -28 PEEK
CFSL1KTF	Cheminert sample loop 1ml	flangeless connections 1/4in -28 PTFE
CFSL20FEP	Cheminert sample loop 20ul	flangeless connections 1/4in -28 FEP
CFSL20PK	Cheminert sample loop 20ul	flangeless connections 1/4in -28 PEEK
CFSL20TF	Cheminert sample loop 20ul	flangeless connections 1/4in -28 PTFE
CFSL250FEP	Cheminert sample loop 250ul	flangeless connections 1/4in -28 FEP
CFSL250PK	Cheminert sample loop 250ul	flangeless connections 1/4in -28 PEEK