



# VICIValco-Cheminert PRODUCT LIST 2012

CFSL250TF	Cheminert sample loop 250ul	flangeless connections 1/4in -28 PTFE
CFSL2KFEP	Cheminert sample loop 2ml	flangeless connections 1/4in -28 FEP
CFSL2KPK	Cheminert sample loop 2ml	flangeless connections 1/4in -28 PEEK
CFSL2KTF	Cheminert sample loop 2ml	flangeless connections 1/4in -28 PTFE
CFSL500FEP	Cheminert sample loop 500ul	flangeless connections 1/4in -28 FEP
CFSL500PK	Cheminert sample loop 500ul	flangeless connections 1/4in -28 PEEK
CFSL500TF	Cheminert sample loop 500ul	flangeless connections 1/4in -28 PTFE
CFSL50FEP	Cheminert sample loop 50ul	flangeless connections 1/4in -28 FEP
CFSL50PK	Cheminert sample loop 50ul	flangeless connections 1/4in -28 PEEK
CFSL50TF	Cheminert sample loop 50ul	flangeless connections 1/4in -28 PTFE
CFS-N03025-025	GC-Column FS ValcoBond VB-Fluoro	30m length ID 0.25mm df 0.25um
CFS-N03053-100	GC-Column FS ValcoBond VB-Fluoro	30m length ID 0.53mm ID df 1.00um
CFS-PA1532-100	GC-Column FS ValcoPLOT HayeSep A	15m length ID 0.32mm df 10um
CFS-PA1553-200	GC-Column FS ValcoPLOT HayeSep A	15m length ID 0.53mm df 20um
CFS-PA3032-100	GC-Column FS ValcoPLOT HayeSep A	30m length ID 0.32mm df 10um
CFS-PA3053-200	GC-Column FS ValcoPLOT HayeSep A	30m length ID 0.53mm df 20um
CFS-PB1532-100	VPHS-B Column FS ValcoBond HayeSep B	15m length ID 0.32mm df 0.10um
CFS-PB1553-200	VPHS-B Column FS ValcoBond HayeSep B	15m length ID 0.53mm df 0.20um
CFS-PB3032-100	VPHS-B Column FS ValcoBond HayeSep B	30m length ID 0.32mm df 0.10um
CFS-PB3053-200	GC-Column FS ValcoPLOT HayeSep B	30m length ID 0.53mm df 20um
CFS-PC1532-100	VPHS-C Column FS ValcoBond HayeSep C	15m length ID 0.32mm df 0.10um
CFS-PC1553-200	GC-Column FS ValcoPLOT HayeSep C	15m length ID 0.53mm df 20um
CFS-PC3032-100	VPHS-C Column FS ValcoBond HayeSep C	30m length ID 0.32mm df 0.10um
CFS-PC3053-200	GC-Column FS ValcoPLOT HayeSep C	30m length ID 0.53mm df 20um
CFS-PD1532-100	GC-Column FS ValcoPLOT HayeSep D	15m length ID 0.32mm df 10um
CFS-PD1553-200	GC-Column FS ValcoPLOT HayeSep D	15m length ID 0.53mm df 20um
CFS-PD3032-100	GC-Column FS ValcoPLOT HayeSep D	30m length ID 0.32mm df 10um
CFS-PD3053-200	GC-Column FS ValcoPLOT HayeSep D	30m length ID 0.53mm df 20um
CFS-PN1532-100	VPHS-N Column FS ValcoBond HayeSep N	15m length ID 0.32mm df 0.10um
CFS-PN1553-200	VPHS-N Column FS ValcoBond HayeSep N	15m length ID 0.53mm df 0.20um
CFS-PN3032-100	VPHS-N Column FS ValcoBond HayeSep N	30m length ID 0.32mm df 0.10um
CFS-PN3053-200	GC-Column FS ValcoPLOT HayeSep N	30m length ID 0.53mm df 20um
CFS-PP1532-100	VPHS-P Column FS ValcoBond HayeSep P	15m length ID 0.32mm df 0.10um
CFS-PP1553-200	VPHS-P Column FS ValcoBond HayeSep P	15m length ID 0.53mm df 0.20um
CFS-PP3032-100	VPHS-P Column FS ValcoBond HayeSep P	30m length ID 0.32mm df 0.10um
CFS-PP3053-200	GC-Column FS ValcoPLOT HayeSep P	30m length ID 0.53mm df 20um
CFS-PQ1532-100	GC-Column FS ValcoPLOT HayeSep Q	15m length ID 0.32mm df 10um
CFS-PQ1553-200	GC-Column FS ValcoPLOT HayeSep Q	15m length ID 0.53mm df 20um
CFS-PQ3032-100	VPHS-Q Column FS ValcoBond HayeSep Q	30m length ID 0.32mm df 0.10um
CFS-PQ3053-200	GC-Column FS ValcoPLOT HayeSep Q	30m length ID 0.53mm df 20um
CFS-PR1532-100	VPHS-R Column FS ValcoBond HayeSep R	15m length ID 0.32mm df 0.10um
CFS-PR1553-200	VPHS-R Column FS ValcoBond HayeSep R	15m length ID 0.53mm df 0.20um
CFS-PR3032-100	VPHS-R Column FS ValcoBond HayeSep R	30m length ID 0.32mm df 0.10um
CFS-PR3053-200	GC-Column FS ValcoPLOT HayeSep R	30m length ID 0.53mm df 20um
CFS-PS1532-100	VPHS-S Column FS ValcoBond HayeSep S	15m length ID 0.32mm df 0.10um
CFS-PS1553-200	VPHS-S Column FS ValcoBond HayeSep S	15m length ID 0.53mm df 0.20um
CFS-PS3032-100	GC-Column FS ValcoPLOT HayeSep S	30m length ID 0.32mm df 10um
CFS-PS3053-200	VPHS-S Column FS ValcoBond HayeSep S	30m length ID 0.53mm df 0.20um
CFS-X1553-200	VP-Molesieve ColumnFS ValcoBond 5A Fused Silica	15m length ID 0.53mm df 0.20um
CFS-X1553-500	VP-Molesieve ColumnFS ValcoBond 5A Fused Silica	15m length ID 0.53mm df 0.50um
CFS-X3053-200	GC-Column FS ValcoPLOT Molesieve 5A	30m length ID 0.53mm df 20um
CFS-X3053-500	GC-Column FS ValcoPLOT Molesieve 5A	30m length ID 0.53mm df 50um
CFS-Y3053-100	GC-Column FS ValcoPlot Alumina	30m length ID 0.53mm df 10um
CFS-Y5053-100	GC-Column FS ValcoPlot Alumina	50m length ID 0.53mm df 10um
CFS-Z1553-100	VP-Alumina ColumnFS ValcoBond VP-Alumina Na2SO4	15m length ID 0.53mm df 0.10um
CFS-Z3053-100	GC-Column FS ValcoPlot Alumina	30m length ID 0.53mm df 10um
CFS-Z5053-100	GC-Column FS ValcoPlot Alumina	50m length ID 0.53mm df 10um
CFT-110	Cheminert flanging tool	110Vac non CE !!!
CFT1K-110	Cheminert starter kit for 1/16in tubing	110Vac non CE !!!
CFT1K-220	Cheminert starter kit for 1/16in tubing	220Vac non CE !!!
CFT-220	Cheminert flanging tool	220Vac non CE !!!