



# VICIValco-Cheminert PRODUCT LIST 2012

CFT2K-110	Cheminert starter kit for 1/8in tubing	110Vac non CE !!!
CFT2K-220	Cheminert starter kit for 1/8in tubing	220Vac non CE !!!
CFT-H	Cheminert holder flanging tool	
CFT-R	Cheminert razor blade 10/pkg	
CFT-TC	Cheminert tip flanging tool	for tubing ID <075 mm
CFT-TL	Cheminert tip flanging tool	for tubing ID <150 mm
CFT-TM	Cheminert tip flanging tool	for tubing ID <100 mm
CFT-TXC	Cheminert tip flanging tool	for tubing ID <0.25 mm
CFT-TXL	Cheminert tip flanging tool	for tubing ID <200 mm
CF-W1	Cheminert washers for 1/16in OD tubing	10/pkg
CF-W2	Cheminert washers for 1/8in OD tubing	10/pkg
CGC41	Cheminert glass connector	1mm bore Acetal
CGC41KF	Cheminert glass connector	1mm bore CTFE
CGC42	Cheminert glass connector	2mm bore Acetal
CGC42KF	Cheminert glass connector	2mm bore CTFE
CGCB	Cheminert glass bushing	Acetal
CGCBKF	Cheminert glass bushing	CTFE
CGCG41	Cheminert glass rod 3-1/4in long	1mm bore Acetal
CGCG42	Cheminert glass rod 3-1/4in long	2mm bore Acetal
CGCN	Cheminert nut glass connector	Acetal
CGCNKF	Cheminert nut glass connector	CTFE
CGCR	Cheminert split ring	Acetal 5/pkg
CGCRKF	Cheminert split ring	CTFE 5/pkg
CI4UW.2	!!! RECOMMEND 2CI4UW.2	SUPPLIED WITH LARGER HANDLE
CI4UW.5	!!! RECOMMEND 2CI4UW.5	SUPPLIED WITH LARGER HANDLE
CI4UW1	!!! RECOMMEND 2CI4UW1	SUPPLIED WITH LARGER HANDLE
CI4UW2	!!! RECOMMEND 2CI4UW2	SUPPLIED WITH LARGER HANDLE
CI4UWE.2	4 port 2-pos int vol valve manual	1/16 x .75mm 175C/1000psi liq .2ul N60/E
CI4UWE.5	4 port 2-pos int vol valve manual	1/16 x .75mm 175C/1000psi liq .5ul N60/E
CI4UWE1	4 port 2-pos int vol valve manual	1/16 x .75mm 175C/1000psi liq 1ul N60/E
CI4UWE2	4 port 2-pos int vol valve manual	1/16 x .75mm 175C/1000psi liq 2ul N60/E
CI4W.06	4 port 2-pos int/vol valve manual	1/16 x .4mm 75C/5000psi liq .06ul N60/H
CI4W.1	4 port 2-pos int vol valve manual	1/16 x .4mm 75C/5000psi liq .1ul N60/H
CI4W.2	4 port 2-pos int vol valve manual	1/16 x .4mm 75C/5000psi liq .2ul N60/H
CI4W.5	4 port 2-pos int vol valve manual	1/16 x .4mm 75C/5000psi liq .5ul N60/H
CI4WE.06	4 port 2-pos int vol valve manual	1/16 x .4mm 175C/1000psi liq .06ulN60/E
CI4WE.1	4 port 2-pos int vol valve manual	1/16 x .4mm 175C/1000psi liq .1ul N60/E
CI4WE.2	4 port 2-pos int vol valve manual	1/16 x .4mm 175C/1000psi liq .2ulN60/E
CI4WE.5	4 port 2-pos int vol valve manual	1/16 x .4mm 175C/1000psi liq .5ul N60/E
C-LFP	Loop fill port assy.	
C-LZP1PK	Plug 1/16in long hex high pressure	Cheminert Polymeric vlv series C1-C5 PEEK
CM	Column mandrel	
CM1XKF	Cheminert mixing tee 1/4in -28	for 1/16in tubing 0.75mm bore CTFE
CM1XPK	Cheminert mixing tee 1/4in -28	for 1/16in tubing 0.75mm bore PEEK
CM2XKF	Cheminert mixing tee 1/4in -28	for 1/8in tubing 1.5mm bore CTFE
CM2XPK	Cheminert mixing tee 1/4in -28	for 1/8in tubing 1.5mm bore PEEK
CMH	Close mount hardware 2-pos valve	1 or 2 holes air or elec. act.
CMH11H	Close mount hardware	Cheminert h/p air or elec. act.
CMH11L	Close mount hardware	Cheminert l/p air or elec. act.
CMH12H	Close mount hardware 2-pos. valve	m-electric actuator
CMH12L	Close mount hardware 2-pos. valve	Cheminert l/p m-electric actuator
CMH13	OBSOLETE USE CMH13H	
CMH13H	Close mount hardware m-pos. valve	Cheminert h/p m-electric actuator
CMH13L	Close mount hardware m-pos. valve	Cheminert l/p m-electric actuator
CMHMP	Close mount hardware 2-pos/m-pos valve	no mounting holes air or elec. actuator
CMLAKF	Cheminert male luer adapter to 1/4-28	1.5mm bore CTFE
CMLAPFA	Cheminert male luer adapter to 1/4-28	1.5mm bore PFA
CMLAPK	Cheminert male luer adapter to 1/4-28	1.5mm bore PEEK
C-MPFT10	Cheminert mobile phase filter	for 1/8in OD tubing 10um Titanium frit PTFE
C-MPFT12	Cheminert mobile phase filter	for 1/8in OD tubing 2um Titanium frit PTFE
C-MPR2	Cheminert solvent reservoir 500ml	with 2-hole cap 1/4in -28 fittings PE