



VICIValco-Cheminert PRODUCT LIST 2012

C-MPR3	Cheminert solvent reservoir 500ml	with 3-hole cap 1/4in -28 fittings PE
C-MZP1PK	Plug 1/16in hex high pressure	Cheminert Polymeric vlv series C1-C5 PEEK
CN2-4340	10 port 2-pos valve manual	1/32 x .10mm 50C/5000psi liq PAEK/E
CN2-4340D	10 port 2-pos valve replacement	1/32 x .10mm 50C/5000psi liq PAEK/E
CN2-4340EH	10 port 2-pos valve m-electric	1/32 x .10mm 50C/5000psi liq PAEK/E
CN2-4346	6 port 2-pos valve manual	1/32 x .10mm 50C/5000psi liq PAEK/E
CN2-4346D	6 port 2-pos valve replacement	1/32 x .10mm 50C/5000psi liq PAEK/E
CN2-4346EH	6 port 2-pos valve m-elect	1/32 x .10mm 50C/5000psi liq PAEK/E
CN2-43R0	Rotor seal 10 port CN2-valve	1/32 x .10mm 50C/5000psi liq E
CN2-43R6	Rotor seal 6 port CN2-valve	1/32 x .10mm 50C/5000psi liq E
CN2-4C40I	Stator/Insert 10 port CN2-valve	0.10mm bore (.004in) .080in bolt circle E3
CN2-4C46I	Stator/Insert 6 port CN2-valve	0.10mm bore (.004in) .080in bolt circle E3
CN4-4344-.004	4 port 2-pos int vol valve manual	1/32 x .10mm 50C/5000psi liq .004ul PAEK/E
CN4-4344-.004D	4 port 2-pos int vol valve replacement	1/32 x .10mm 50C/5000psi liq .004ul PAEK/E
CN4-4344-.004EH	4 port 2-pos int vol valve m-elect	1/32 x .10mm 50C/5000psi liq .004ul PAEK/E
CN4-4344-.01	4 port 2-pos int vol valve manual	1/32 x .10mm 50C/5000psi liq .01ul PAEK/E
CN4-4344-.01D	4 port 2-pos int vol valve replacement	1/32 x .10mm 50C/5000psi liq .01ul PAEK/E
CN4-4344-.01EH	4 port 2-pos int vol valve m-elect	1/32 x .10mm 50C/5000psi liq .01ul PAEK/E
CN4-4344-.02	4 port 2-pos int vol valve manual	1/32 x .10mm 50C/5000psi liq .02ul PAEK/E
CN4-4344-.02D	4 port 2-pos int vol valve replacement	1/32 x .10mm 50C/5000psi liq .02ul PAEK/E
CN4-4344-.02EH	4 port 2-pos int vol valve m-elect	1/32 x .10mm 50C/5000psi liq .02ul PAEK/E
CN4-43R-.004	Rotor seal 4 port CN4-valve int .004ul	1/32 x .10mm 50C/5000psi liq E
CN4-43R-.01	Rotor seal 4 port CN4-valve int .01ul	1/32 x .10mm 50C/5000psi liq E
CN4-43R-.02	Rotor seal 4 port CN4-valve int .02ul	1/32 x .10mm 50C/5000psi liq E
CN4-4C4I	Stator/Insert 4 port CN4-valve	0.10mm bore (.004in) .080in int. E3
C-NEF.5FPK.15S1	Column end fitting Nano 1/32in Cheminert 1um scr	150um PEEK with liners for FS 125-175um
C-NEF.5FPK.20S1	Column end fitting Nano 1/32in Cheminert 1um scr	150um PEEK with liners for FS 175-225um
C-NEF.5FPK.25S1	Column end fitting Nano 1/32in Cheminert 1um scr	150um PEEK with liners for FS 225-275um
C-NEF.5FPK.30S1	Column end fitting Nano 1/32in Cheminert 1um scr	150um PEEK with liners for FS 275-325um
C-NEF.5FPK.35S1	Column end fitting Nano 1/32in Cheminert 1um scr	150um PEEK with liners for FS 325-375um
C-NEF.5XFPK.15S1	Column end fitting Nano 1/32in Cheminert 1um scr	100um PEEK with liners for FS 125-175um
C-NEF.5XFPK.20S1	Column end fitting Nano 1/32in Cheminert 1um scr	100um PEEK with liners for FS 175-225um
C-NEF.5XFPK.25S1	Column end fitting Nano 1/32in Cheminert 1um scr	100um PEEK with liners for FS 225-275um
C-NEF.5XFPK.30S1	Column end fitting Nano 1/32in Cheminert 1um scr	100um PEEK with liners for FS 275-325um
C-NEF.5XFPK.35S1	Column end fitting Nano 1/32in Cheminert 1um scr	100um PEEK with liners for FS 325-375um
C-NEU.5FPK	Union Int/Ext 1/32in Cheminert	150um PEEK without liners
C-NEU.5FPK.15	Union Int/Ext Nano 1/32in Cheminert	150um PEEK with liners for FS 125-175um
C-NEU.5FPK.20	Union Int/Ext Nano 1/32in Cheminert	150um PEEK with liners for FS 175-225um
C-NEU.5FPK.25	Union Int/Ext Nano 1/32in Cheminert	150um PEEK with liners for FS 225-275um
C-NEU.5FPK.30	Union Int/Ext Nano 1/32in Cheminert	150um PEEK with liners for FS 275-325um
C-NEU.5FPK.35	Union Int/Ext Nano 1/32in Cheminert	150um PEEK with liners for FS 325-375um
C-NEU.5XFPK	Union Int/Ext Nano 1/32in Cheminert	100um PEEK without liners
C-NEU.5XFPK.15	Union Int/Ext Nano 1/32in Cheminert	100um PEEK with liners for FS 125-175um
C-NEU.5XFPK.20	Union Int/Ext Nano 1/32in Cheminert	100um PEEK with liners for FS 175-225um
C-NEU.5XFPK.25	Union Int/Ext Nano 1/32in Cheminert	100um PEEK with liners for FS 225-275um
C-NEU.5XFPK.30	Union Int/Ext Nano 1/32in Cheminert	100um PEEK with liners for FS 275-325um
C-NEU.5XFPK.35	Union Int/Ext Nano 1/32in Cheminert	100um PEEK with liners for FS 325-375um
CNFT	Tightening Tool for PEEK hex-head	1/32 nuts green
C-NL.15L-5	Liner long Nano 1/32in Cheminert 27 mm	PEEK for FS OD 125 - 175um 5/pkg
C-NL.15S-5	Liner short Nano 1/32in Cheminert 10 mm	PEEK for FS OD 125 -175um 5/pkg
C-NL.20L-5	Liner long Nano 1/32in Cheminert 27 mm	PEEK for FS OD 175 - 225um 5/pkg
C-NL.20S-5	Liner long Nano 1/32in Cheminert 10 mm	PEEK for FS OD 175 - 225um 5/pkg
C-NL.25L-5	Liner long Nano 1/32in Cheminert 27 mm	PEEK for FS OD 225 - 275 um 5/pkg
C-NL.25S-5	Liner short Nano 1/32in Cheminert 10 mm	PEEK for FS OD 225 - 275um 5/pkg
C-NL.30L-5	Liner long Nano 1/32in Cheminert 27 mm	PEEK for FS OD 275 - 325um 5/pkg
C-NL.30S-5	Liner short Nano 1/32in Cheminert 10 mm	PEEK for FS OD 275 - 325um 5/pkg
C-NL.35L-5	Liner long Nano 1/32in Cheminert 27 mm	PEEK for FS OD 325 - 375um 5/pkg
C-NL.35S-5	Liner short Nano 1/32in Cheminert 10 mm	PEEK for FS OD 325 - 375um 5/pkg
C-NLS1.15	Liner Nano 1/32in Cheminert screen 1um 27 mm	PEEK for FS OD 125-175um
C-NLS1.20	Liner Nano 1/32in Cheminert screen 1um 27 mm	PEEK for FS OD 175 - 225 um
C-NLS1.25	Liner Nano 1/32in Cheminert screen 1um 27 mm	PEEK for FS OD 225-275um