



VICI Valco-Cheminert PRODUCT LIST 2012

C-NLS1.30	Liner Nano 1/32in Cheminert screen 1um 27 mm	PEEK for FS OD 275-325um
C-NLS1.35	Liner Nano 1/32in Cheminert screen 1um 27 mm	PEEK for FS OD 325-375um
C-NNFFPK	Nut/Ferrule One-piece 1/32in Cheminert	
C-NNFLFPK	Nut/Ferrule One-piece 1/32in Cheminert	long
C-NPFPK	Plug 1/32 Cheminert	
CNSL1KPK	Cheminert sample loop 1ul (1000nl)	1/32in ends with nuts PEEK
CNSL250PK	Cheminert sample loop 250nl	1/32in ends with nuts PEEK
CNSL2KPK	Cheminert sample loop 2ul (2000nl)	1/32in ends with nuts PEEK
CNSL500PK	Cheminert sample loop 500nl	1/32in ends with nuts PEEK
CNSL5KPK	Cheminert sample loop 5ul (5000nl)	1/32in ends with nuts PEEK
C-NTFPK	Tee Nano 1/32in Cheminert	150um PEEK
C-NTXFPK	Tee Nano 1/32in Cheminert	100um PEEK
CNV1A10S1	Combo needle valve silver colored knob	0-10ml N2 at 40psi 1/16in int Al/Viton
CNV1A150S1	Combo needle valve silver colored knob	150ml N2 at 40psi 1/16in int Al/Viton
CNV1A250S1	Combo needle valve silver colored knob	250ml N2 at 40psi 1/16in int Al/Viton
CNV1A500S1	Combo needle valve silver colored knob	500ml N2 at 40psi 1/16in int Al/Viton
CNV1A50S1	Combo needle valve silver colored knob	50ml N2 at 40psi 1/16in int Al/Viton
CNV1S10S1	Combo needle valve silver colored knob	0-10ml N2 at 40psi 1/16in int SS/Viton
CNV1S150S1	Combo needle valve silver colored knob	150ml N2 at 40psi 1/16in int SS/Viton
CNV1S250S1	Combo needle valve silver colored knob	250ml N2 at 40psi 1/16in int SS/Viton
CNV1S500S1	Combo needle valve silver colored knob	500ml N2 at 40psi 1/16in int SS/Viton
CNV1S50S1	Combo needle valve silver colored knob	50ml N2 at 40psi 1/16in int SS/Viton
CNVEKB	Combo needle valve standard knob black	length .62in /16mm long
CNVEKG	Combo needle valve standard knob green	length .62in /16mm long
CNVEKLB	Combo needle valve long knob black	length 1.25in /32mm long
CNVEKLG	Combo needle valve long knob green	length 1.25in /32mm long
CNVEKLR	Combo needle valve long long knob red	length 1.25in /32mm long
CNVEKLS	Combo needle valve long knob silver	length 1.25in /32mm long
CNVEKLU	Combo needle valve long knob blue	length 1.25in /32mm long
CNVEKR	Combo needle valve standard knob red	length .62in /16mm long
CNVEKS	Combo needle valve standard knob silver	length .62in /16mm long
CNVEKU	Combo needle valve standard knob blue	length .62in /16mm long
C-NVISF	Syringe Fill Port 1/32in Cheminert	for 0.85in /22mm long needle 26 Gauge OD
C-NXFPK	Cross Nano 1/32in Cheminert	150um PEEK
C-NXXFPK	Cross Nano 1/32in Cheminert	100um PEEK
C-NYFPK	Y-assy Nano 1/32in Cheminert	150um PEEK
C-NYXFPK	Y-assy Nano 1/32in Cheminert	100um PEEK
CP2-4841-100D	M6 Pump only replacement	vol. 100ul Sapphire/TF E3/P VICI Logo
CP2-4841-100M1	M6 Pump with controller and stepper motor	vol. 100ul Sapphire/TF E3/P Viton VICI Logo
CP2-4841-100SM	M6 Pump with stepper motor (no controller)	vol. 100ul Sapphire/TF E3/P VICI Logo
CP3-8182-625D	M50 Pump only	vol. 625ul Sapphire/TF ceramic rotor VICI Logo
CP3-8182-625M2	M50 Pump with controller and stepper motor	vol. 625ul Sapphire/TF ceramic rotor VICI Logo
CP3-8182-625SM2	M50 Pump and stepper motor	vol. 625ul Sapphire/TF ceramic rotor VICI Logo
CPA2KF	Cheminert pipe connector 1/8in NPT	1/4in -28female x M-NPT 1.5mm bore CTFE
CPA2PK	Cheminert pipe connector 1/8in NPT	1/4in -28female x M-NPT 1.5mm bore PEEK
CPA4KF	Cheminert pipe connector 1/4in NPT	1/4in -28female x M-NPT 1.5mm bore CTFE
CPA4PK	Cheminert pipe connector 1/4in NPT	1/4in -28female x M-NPT 1.5mm bore PEEK
CP-CM1-P	Controller MicroLynx-4	
CP-DSM	Driver Pump M6	
CP-DSM2	Driver Pump M50	
C-PF	Cheminert perfit 1/4in -28 kit of 6 pcs	for peristaltic tubing .5 to 2.29mm ID
C-PFL	Cheminert perfit 1/4in -28	for peristaltic tubing 1.85 to 2.29mm ID
C-PFM	Cheminert perfit 1/4in -28	for peristaltic tubing 1.12 to 1.65mm ID
C-PFS	Cheminert perfit 1/4in -28	for peristaltic tubing .5 to 1.02mm ID
CPKF	Cheminert plug 1/4in -28	CTFE 5/pkg
CPPK	Cheminert plug 1/4in -28	PEEK 5/pkg
CR10	Clamp ring for standoff assembly	x SOAMP m-pos m-electric actuator
CR11	Clamp ring closomount 2-pos/m-pos vlv.	2-pos/m-pos std. electric/air actuator
CR3	Clamp ring for standoff assembly	x SOA/ x SOAMP
CR4	Clamp ring for close mount assembly	2-pos air/electric actuator and DV valve
CR8	Clamp ring for standoff assembly	x SOA/ x SOAMP 2-pos m-electric actuator