



VICI Valco-Cheminert PRODUCT LIST 2012

CSD10UW	10 mpos dead-end path manual	1/16 x .4mm 75C/5000psi liq N60/E
CSD4UW	4 mpos dead-end path manual	1/16 x .4mm 75C/5000psi liq N60/E
CSD6UW	6 mpos dead-end path manual	1/16 x .4mm 75C/5000psi liq N60/E
CSL10	Cheminert sample loop 10ul	1/16in ends with nuts & ferrules 316SS
CSL100	Cheminert sample loop 100ul	1/16in ends with nuts & ferrules 316SS
CSL100TI	Cheminert sample loop 100ul	1/16in ends with nuts & ferrules Ti
CSL10K	Cheminert sample loop 10ml	1/16in ends with nuts & ferrules 316SS
CSL10TI	Cheminert sample loop 10ul	1/16in ends with nuts & ferrules Ti
CSL1K	Cheminert sample loop 1ml	1/16in ends with nuts & ferrules 316SS
CSL1KTl	Cheminert sample loop 1ml	1/16in ends with nuts & ferrules Ti
CSL2	Cheminert sample loop 2ul	1/16in ends with nuts & ferrules 316SS
CSL20	Cheminert sample loop 20ul	1/16in ends with nuts & ferrules 316SS
CSL20TI	Cheminert sample loop 20ul	1/16in ends with nuts & ferrules Ti
CSL250	Cheminert sample loop 250ul	1/16in ends with nuts & ferrules 316SS
CSL250TI	Cheminert sample loop 250ul	1/16in ends with nuts & ferrules Ti
CSL2K	Cheminert sample loop 2ml	1/16in ends with nuts & ferrules 316SS
CSL5	Cheminert sample loop 5ul	1/16in ends with nuts & ferrules 316SS
CSL50	Cheminert sample loop 50ul	1/16in ends with nuts & ferrules 316SS
CSL500	Cheminert sample loop 500ul	1/16in ends with nuts & ferrules 316SS
CSL500TI	Cheminert sample loop 500ul	1/16in ends with nuts & ferrules Ti
CSL50TI	Cheminert sample loop 50ul	1/16in ends with nuts & ferrules Ti
CSL5K	Cheminert sample loop 5ml	1/16in ends with nuts & ferrules 316SS
CSLN1K	Cheminert sample loop 1ul (1000nl)	1/32in ends with nuts SS
CSLN2K	Cheminert sample loop 2ul (2000nl)	1/32in ends with nuts SS
CSLN5K	Cheminert sample loop 5ul (5000nl)	1/32in ends with nuts SS
CSS-X1553-200	GC-Column SS ValcoPLOT Molesieve 5A	15m length ID 0.53mm df 20um
CSS-X3053-200	GC-Column SS ValcoPLOT Molesieve 5A	30m length ID 0.53mm df 20um
CST	Cheminert setting tool	for 1/4in -28 flangeless fitting
CTA2KF	Cheminert adapter for tubing 1/8in OD	1.5mm bore CTFE
CTA2PK	Cheminert adapter for tubing 1/8in OD	1.5mm bore PEEK
CTA2S6	Cheminert adapter for tubing 1/8in OD	1.5mm bore 316SS
CTA4KF	Cheminert adapter for tubing 1/4in OD	1.5mm bore CTFE
CTA4PK	Cheminert adapter for tubing 1/4in OD	1.5mm bore PEEK
CTA4S6	Cheminert adapter for tubing 1/4in OD	1.5mm bore 316SS
CTCKF	Cheminert tee 1/4in -28 1/16in OD tubing	.25mm bore CTFE
CTCPK	Cheminert tee 1/4in -28 1/16in OD tubing	.25mm bore PEEK
CTKF	Cheminert tee 1/4in -28 1/16in OD tubing	.5mm bore CTFE
CTLKF	Cheminert tee 1/4in -28 1/8in OD tubing	1.5mm bore CTFE
CTLPK	Cheminert tee 1/4in -28 1/8in OD tubing	1.5mm bore PEEK
CTMKF	Cheminert tee 1/4in -28 1/16in OD tubing	.75mm bore CTFE
CTMPK	Cheminert tee 1/4in -28 1/16in OD tubing	.75mm bore PEEK
CTPK	Cheminert tee 1/4in -28 1/16in OD tubing	.5mm bore PEEK
CU4LKF	Cheminert union 1/4in -28 to 1/2-20	1.5mm bore 1/8in to 1/4in tube CTFE
CU4LPK	Cheminert union 1/4in -28 to 1/2-20	1.6mm bore 1/8in to 1/4in tube PEEK
CUCKF	Cheminert union 1/4in -28 1/16in OD tubing	.25mm bore CTFE
CUCPK	Cheminert union 1/4in -28 1/16in OD tubing	.25mm bore PEEK
CUKF	Cheminert union 1/4in -28 1/16in OD tubing	.5mm bore CTFE
CULKF	Cheminert union 1/4in -28 1/8in OD tubing	1.5mm bore CTFE
CULPK	Cheminert union 1/4in -28 1/8in OD tubing	1.5mm bore PEEK
CUMKF	Cheminert union 1/4in -28 1/16 OD tubing	.75mm bore CTFE
CUMPK	Cheminert union 1/4in -28 1/16in OD tubing	.75mm bore PEEK
CUPK	Cheminert union 1/4in -28 1/16in OD tubing	.5mm bore PEEK
CUTKF	Cheminert union 1/4in -28 1/8in OD tubing	butt connection CTFE
CUTPK	Cheminert union 1/4in -28 OD 1/8in tubing	butt connection PEEK
CUTPP	Cheminert union 1/4in -28 w/o fitting	butt connection Polypropylene 5/pkg
CVA10GS1	Combo needle valve short green knob	10ml/min 40psi He/N2 1/16in int Al/Viton
CVA10GS2	Combo needle valve short green knob	10ml/min 40psi He/N2 1/8in int Al/Viton
CVA150US1	Combo needle valve short blue knob	150ml/min 40psi He/N2 1/16in int Al/Viton
CVA150US2	Combo needle valve short blue knob	150ml/min 40psi He/N2 1/8in int Al/Viton
CVA1KYS1	Combo needle valve short yellow knob	1 liter/min 40psi He/N2 1/16in int Al/Viton
CVA1KYS2	Combo needle valve short yellow knob	1 liter/min 40psi He/N2 1/8in int Al/Viton