

VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]
> CatL#s

> Current System AUD Prices



CZUS6	Cheminert union 1/4in -28 x 1/16in OD tubing	.5mm bore 316SS
D10UW	10 port 2-pos valve replacement	1/8 x .75mm 75C/5000psi liq N60/H
D10UWE	10 port 2-pos valve replacement	1/8 x .75mm 225C/400psi gas N60/E
D10UWT	10 port 2-pos valve replacement	1/8 x .75mm 330C/300psi gas N60/T
D-2-110	Pulsed discharge detector PDECD/HID/PID	48V detector controller HP2 110Vac CE
D-2-220	Pulsed discharge detector PDECD/HID/PID	48V detector controller HP2 220Vac CE
D-2-I-110	Pulsed discharge detector optimized HID	48V detector controller HP2 110Vac CE
D-2-I-220	Pulsed discharge detector optimized HID	48V detector controller HP2 220Vac CE
D-3-I-7890-110	Pulsed discharge detector HID/PID HP7890	pulser HP electrometer HP2-110 HPM-110
D-3-I-7890-220	Pulsed discharge detector HID/PID HP7890	pulser HP electrometer HP2-220 HPM-220
D-3-I-HP-110	Pulsed discharge detector HID/PID HP6890	pulser HP electrometer HP2-110 HPM-110
D-3-I-HP-220	Pulsed discharge detector HID/PID HP6890	pulser HP electrometer HP2-220 HPM-220
D-4-I-110	Pulsed discharge detector HeID/PID	48V detector controller HP2 110Vac CE
D-4-I-220	Pulsed discharge detector HeID/PID	48V detector controller HP2 220Vac CE
D-4-I-HP58-110	Pulsed discharge detector HeID/PID HP5890	48V detector controller HP2 110Vac CE
D-4-I-HP58-220	Pulsed discharge detector HeID/PID HP5890	48V detector controller HP2 220Vac CE
D-4-I-SH14-R-110	Pulsed discharge detector HeID/PID Shimadzu 14	w/o controller HP2-110
D-4-I-SH14-R-220	Pulsed discharge detector HeID/PID Shimadzu 14	w/o controller HP2-220
D-4-I-SH17-R-110	Pulsed discharge detector HeID/PID Shimadzu 17	w/o controller HP2-110 suitable for 2010 & 2014
D-4-I-SH17-R-220	Pulsed discharge detector HeID/PID Shimadzu 17	w/o controller HP2-220 suitable for 2010 & 2014
D-4-I-TQ-R-110	Pulsed discharge detector HeID/PID for Trace GC	pulser HP2-110 ThermoQuest
D-4-I-TQ-R-220	Pulsed discharge detector HeID/PID for Trace GC	pulser HP2-220 ThermoQuest
D-4-I-VA38-R-110	Pulsed discharge detector HeID/PID Varian 3800	w/o controller with HP2-110
D-4-I-VA38-R-220	Pulsed discharge detector HeID/PID Varian 3800	w/o controller with HP2-220
D4UW	4 port 2-pos valve replacement	1/8 x .75mm 75C/5000psi liq N60/H
D4UWE	4 port 2-pos valve replacement	1/8 x .75mm 225C/400psi gas N60/E
D4UWT	4 port 2-pos valve replacement	1/8 x .75mm 330C/300psi gas N60/T
D-5-6890-110	Pulsed discharge detector PDECD mode HP 6890	pulser HP electrometer HP2-110 HPM-110
D-5-6890-220	Pulsed discharge detector PDECD mode HP 6890	pulser HP electrometer HP2-220 HPM-220
D6UW	6 port 2-pos valve replacement	1/8 x .75mm 75C/5000psi liq N60/H
D6UWE	6 port 2-pos valve replacement	1/8 x .75mm 225C/400psi gas N60/E
D6UWT	6 port 2-pos valve replacement	1/8 x .75mm 330C/300psi gas N60/T
D8UW	8 port 2-pos valve replacement	1/8 x .75mm 75C/5000psi liq N60/H
D8UWE	8 port 2-pos valve replacement	1/8 x .75mm 225C/400psi gas N60/E
D8UWT	8 port 2-pos valve replacement	1/8 x .75mm 330C/300psi gas N60/T
DC10UW	10 port 2-pos valve replacement	1/16 x .75mm 75C/5000psi liq N60/H
DC10UWE	10 port 2-pos valve replacement	1/16 x .75mm 225C/400psi gas N60/E
DC10UWT	10 port 2-pos valve replacement	1/16 x .75mm 330C/300psi gas N60/T
DC10W	10 port 2-pos valve replacement	1/16 x .4mm 75C/5000psi liq N60/H
DC10WE	10 port 2-pos valve replacement	1/16 x .4mm 225C/400psi gas N60/E
DC10WT	10 port 2-pos valve replacement	1/16 x .4mm 350C/300psi gas N60/T
DC4UW	4 port 2-pos valve replacement	1/16 x .75mm 75C/5000psi liq N60/H
DC4UWE	4 port 2-pos valve replacement	1/16 x .75mm 225C/400psi gas N60/E
DC4UWT	4 port 2-pos valve replacement	1/16 x .75mm 330C/300psi gas N60/T
DC4W	4 port 2-pos valve replacement	1/16 x .4mm 75C/5000psi liq N60/H
DC4WE	4 port 2-pos valve replacement	1/16 x .4mm 225C/400psi gas N60/E
DC4WT	4 port 2-pos valve replacement	1/16 x .4mm 350C/300psi gas N60/T
DC6UW	6 port 2-pos valve replacement	1/16 x .75mm 75C/5000psi liq N60/H
DC6UWE	6 port 2-pos valve replacement	1/16 x .75mm 225C/400psi gas N60/E
DC6UWT	6 port 2-pos valve replacement	1/16 x .75mm 330C/300psi gas N60/T
DC6W	6 port 2-pos valve K-hole replacement	1/16 x .4mm 75C/5000psi liq N60/H
DC6WE	6 port 2-pos valve replacement	1/16 x .4mm 225C/400psi gas N60/E
DC6WT	6 port 2-pos valve replacement	1/16 x .4mm 350C/300psi gas N60/T
DC8UW	8 port 2-pos valve replacement	1/16 x .75mm 75C/5000psi liq N60/H
DC8UWE	8 port 2-pos valve replacement	1/16 x .75mm 225C/400psi gas N60/E
DC8UWT	8 port 2-pos valve replacement	1/16 x .75mm 330C/300psi gas N60/T
DC8W	8 port 2-pos valve replacement	1/16 x .4mm 75C/5000psi liq N60/H
DC8WE	8 port 2-pos valve replacement	1/16 x .4mm 225C/400psi gas N60/E
DC8WT	8 port 2-pos valve replacement	1/16 x .4mm 350C/300psi gas N60/T
DCI4UW.2	4 port 2-pos int vol valve replacement	1/16 x .75mm 75C/5000psi liq .2ul N60/H
DCI4UW.5	4 port 2-pos int vol valve replacement	1/16 x .75mm 75C/5000psi liq .5ul N60/H