

# VICIValco-Cheminert PRODUCT LIST 2012

(Ctrl F)  
> Cat.#s

> Current System AUD Prices



DSC16MWE	16 mpos common outlet path MW replacement	1/8 x 1mm 200C/200psi gas N60/E
DSC6MWE	6 mpos common outlet path MW replacement	1/8 x 1mm 200C/200psi gas N60/E
DSD10MWE	10 mpos dead-end path MW replacement	1/8 x 1mm 200C/200psi gas N60/E
DSD12MWE	12 mpos dead-end path MW replacement	1/8 x 1mm 200C/200psi gas N60/E
DSD16MWE	16 mpos dead-end path MW replacement	1/8 x 1mm 200C/200psi gas N60/E
DSD4UW	4 mpos dead-end path replacement	1/8 x .75mm 75C/5000psi liq N60/E
DSD6MWE	6 mpos dead-end path MW replacement	1/8 x 1mm 200C/400psi gas N60/E
DSD6UW	6 mpos dead-end path replacement	1/8 x .75mm 75C/5000psi liq N60/E
DSD8UW	8 mpos dead-end path replacement	1/8 x .75mm 75C/5000psi liq N60/E
DSF10MWE	10 mpos flow-through MW replacement	1/8 x 1mm 200C/200psi gas N60/E
DSF12MWE	12 mpos flow-through MW replacement	1/8 x 1mm 200C/200psi gas N60/E
DSF16MWE	16 mpos flow-through MW replacement	1/8 x 1mm 200C/200psi gas N60/E
DSF6MWE	6 mpos flow-through MW replacement	1/8 x 1mm 200C/200psi gas N60/E
DST10MWE	10 mpos trapping path MW replacement	1/8 x 1mm 200C/200psi gas N60/E
DST12MWE	12 mpos trapping path MW replacement	1/8 x 1mm 200C/200psi gas N60/E
DST16MWE	16 mpos trapping path MW replacement	1/8 x 1mm 200C/200psi gas N60/E
DST6MWE	6 mpos trapping path MW replacement	1/8 x 1mm 200C/200psi gas N60/E
DSTF10MWE	10 mpos trap/flow path MW replacement	1/8 x 1mm 200C/200psi gas N60/E
DSTF12MWE	12 mpos trap/flow path MW replacement	1/8 x 1mm 200C/200psi gas N60/E
DSTF16MWE	16 mpos trap/flow path MW replacement	1/8 x 1mm 200C/200psi gas N60/E
DSTF6MWE	6 mpos trap/flow path MW replacement	1/8 x 1mm 200C/200psi gas N60/E
DV12-1110	Mini diaphragm 10 port 2-pos valve	1/32 x .25mm 200C/300psi liq N60/Polyimide
DV12-1114-.5	Mini diaphragm 4 port 2-pos int/vol valve	1/32 x .25mm 50C/750psi liq. N60/Polyimide .5ul
DV12-1114-1	Mini diaphragm 4 port 2-pos int/vol valve	1/32 x .25mm 50C/750psi liq. N60/Polyimide 1ul
DV12-1116	Mini diaphragm 6 port 2-pos valve	1/32 x .25mm 200C/300psi liq N60/Polyimide
DV22-2110	Mini diaphragm 10 port 2-pos valve	1/16 x .4mm 200C/300psi liq N60/Polyimide
DV22-2114-.5	Mini diaphragm 4 port 2-pos int/vol valve	1/16 x .4mm 50C/750psi liq N60/Polyimide .5ul
DV22-2114-1	Mini diaphragm 4 port 2-pos int/vol valve	1/16 x .4mm 50C/750psi liq N60/Polyimide 1ul
DV22-2116	Mini diaphragm 6 port 2-pos valve	1/16 x .4mm 200C/300psi liq N60/Polyimide
DV22-21D	Diaphragm replacement 6/10 port Polyimide	for valve bore 0.25 and 0.40 mm
DV22-22D	Diaphragm replacement 6/10 port Teflon	
DV22-3110	Mini diaphragm 10 port 2-pos valve	1/16 x .75mm 200C/300psi liq N60/Polyimide
DV22-3114-.5	Mini diaphragm 4 port 2-pos int/vol valve	1/16 x .75mm 50C/750psi liq N60/Polyimide .5ul
DV22-3114-1	Mini diaphragm 4 port 2-pos int/vol valve	1/16 x .75mm 50C/750psi liq N60/Polyimide 1ul
DV22-3116	Mini diaphragm 6 port 2-pos valve	1/16 x .75mm 200C/300psi liq N60/Polyimide
DV22-31D	Diaphragm replacement 6/10 port Polyimide	for valve bore 0.75 mm
DV22-PURGE	Purge ring for DV22	
DVI-110	Digital valve interface 110Vac	Non-CE !!!
DVI-220	Digital valve interface 220Vac	Non-CE !!!
DVL4MWE2	4 port 2-pos valve MW replacement	1/4 x 4mm 75C/100psi gas N60/E2
DVL6MWE2	6 port 2-pos valve MW replacement	1/4 x 4mm 75C/100psi gas N60/E2
DVL8MWE2	8 port 2-pos valve MW replacement	1/4 x 4mm 75C/100psi gas N60/E2
DVLSC4MWE2	4 mpos common outlet path MW replacement	1/4 x 4mm 75C/100psi gas N60/E2
DVLSC6MWE2	6 mpos common outlet path MW replacement	1/4 x 4mm 75C/100psi gas N60/E2
DVLSC8MWE2	8 mpos common outlet path MW replacement	1/4 x 4mm 75C/100psi gas N60/E2
DVLSD10MWE2	10 mpos dead-end path MW replacement	1/4 x 4mm 75C/100psi gas N60/E2
DVLSD4MWE2	4 mpos dead-end path MW replacement	1/4 x 4mm 75C/100psi gas N60/E2
DVLSD6MWE2	6 mpos dead-end path MW replacement	1/4 x 4mm 75C/100psi gas N60/E2
DVLSD8MWE2	8 mpos dead-end path MW replacement	1/4 x 4mm 75C/100psi gas N60/E2
DVLSF4MWE2	4 mpos flow-through MW replacement	1/4 x 4mm 75C/100psi gas N60/E2
DVLSF6MWE2	6 mpos flow-through MW replacement	1/4 x 4mm 75C/100psi gas N60/E2
DVLSF8MWE2	8 mpos flow-through MW replacement	1/4 x 4mm 75C/100psi gas N60/E2
DVSP4-220	Digital valve sequence programmer	4 intervals 220Vac Non-CE !!!
E10-110	Electric actuator mpos close mount	10 position 110Vac
E102-110	Electric actuator mpos 2in standoff	10 position 110Vac
E10S-110	Electric actuator mpos for standoff	10 position 110Vac
E10UW	10 port 2-pos valve std-electric	1/8 x .75mm 75C/5000psi liq N60/H
E12-110	Electric actuator mpos close mount	12 position 110Vac
E122-110	Electric actuator mpos 2in standoff	12 position 110 Vac
E12S-110	Electric actuator mpos for standoff	12 position 110Vac
E16-110	Electric actuator mpos close mount	16 position 110Vac