

VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]
> Cat.#s

> Current System AUD Prices



E162-110	Electric actuator mpos 2in standoff	16 position 110Vac
E16S-110	Electric actuator mpos for standoff	16 position 110Vac
E2CI4UWE.2	4 port 2-pos int vol valve std-elect/2in so	1/16 x .75mm 175C/1000psi liq .2ul N60/E
E2CI4UWE.5	4 port 2-pos int vol valve std-elect/2in so	1/16 x .75mm 175C/1000psi liq .5ul N60/E
E2CI4UWE1	4 port 2-pos int vol valve std-elect/2in so	1/16 x .75mm 175C/1000psi liq 1ul N60/E
E2CI4UWE2	4 port 2-pos int vol valve std-elect/2in so	1/16 x .75mm 175C/1000psi liq 2ul N60/E
E2CI4WE.06	4 port 2-pos int vol valve std-elect/2in so	1/16 x .4mm 175C/1000psi liq .06ul N60/E
E2CI4WE.1	4 port 2-pos int vol valve std-elect/2in so	1/16 x .4mm 175C/1000psi liq .1ul N60/E
E2CI4WE.2	4 port 2-pos int vol valve std-elect/2in so	1/16 x .4mm 175C/1000psi liq .2ul N60/E
E2CI4WE.5	4 port 2-pos int vol valve std-elect/2in so	1/16 x .4mm 175C/1000psi liq .5ul N60/E
E2CSC10MWE	10 mpos common outlet path MW std-elect/2in so	1/16 x 1mm 200C/200psi gas N60/E
E2CSC12MWE	12 mpos common outlet path MW std-elect/2in so	1/16 x 1mm 200C/200psi gas N60/E
E2CSC16MWE	16 mpos common outlet path MW std-elect/2in so	1/16 x 1mm 200C/200psi gas N60/E
E2CSC6MWE	6 mpos common outlet path MW std-elect/2in so	1/16 x 1mm 200C/200psi gas N60/E
E2CSD10MWE	10 mpos dead-end path MW std-elect/2in so	1/16 x .75mm 200C/400psi gas N60/E
E2CSD12MWE	12 mpos dead-end path MW std-elect/2in so	1/16 x .75mm 200C/400psi gas N60/E
E2CSD16MWE	16 mpos dead-end path MW std-elect/2in so	1/16 x .75mm 200C/400psi gas N60/E
E2CSD6MWE	6 mpos dead-end path MW std-elect/2in so	1/16 x .75mm 200C/400psi gas N60/E
E2CSF10MWE	10 mpos flow-through MW std-elect/2in so	1/16 x 1mm 200C/200psi gas N60/E
E2CSF12MWE	12 mpos flow-through MW std-elect/2in so	1/16 x 1mm 200C/200psi gas N60/E
E2CSF16MWE	16 mpos flow-through MW std-elect/2in so	1/16 x 1mm 200C/200psi gas N60/E
E2CSF6MWE	6 mpos flow-through MW std-elect/2in so	1/16 x 1mm 200C/200psi gas N60/E
E2CST10MWE	10 mpos trapping path MW std-elect/2in so	1/16 x .75mm 200C/200psi gas N60/E
E2CST12MWE	12 mpos trapping path MW std-elect/2in so	1/16 x .75mm 200C/200psi gas N60/E
E2CST16MWE	16 mpos trapping path MW std-elect/2in so	1/16 x .75mm 200C/200psi gas N60/E
E2CST6MWE	6 mpos trapping path MW std-elect/2in so	1/16 x .75mm 200C/200psi gas N60/E
E2CSTF10MWE	10 mpos trap/flow path MW std-elect/2in so	1/16 x .75mm 200C/200psi gas N60/E
E2CSTF12MWE	12 mpos trap/flow path MW std-elect/2in so	1/16 x .75mm 200C/200psi gas N60/E
E2CSTF16MWE	16 mpos trap/flow path MW std-elect/2in so	1/16 x .75mm 200C/200psi gas N60/E
E2CSTF6MWE	6 mpos trap/flow path MW std-elect/2in so	1/16 x .75mm 200C/200psi gas N60/E
E2I4UWE.2	4 port 2-pos int vol valve std-elect/2in so	1/8 x .75mm 175C/1000psi liq .2ul N60/E
E2I4UWE.5	4 port 2-pos int vol valve std-elect/2in so	1/8 x .75mm 175C/1000psi liq .5ul N60/E
E2I4UWE1	4 port 2-pos int vol valve std-elect/2in so	1/8 x .75mm 175C/1000psi liq 1ul N60/E
E2I4UWE2	4 port 2-pos int vol valve std-elect/2in so	1/8 x .75mm 175C/1000psi liq 2ul N60/E
E2NI4WE.06	4 port 2-pos int vol valve std-elect/2in so	1/32 x .25mm 175C/1000psi liq .06ulN60/E
E2NI4WE.1	4 port 2-pos int vol valve std-elect/2in so	1/32 x .25mm 175C/1000psi liq .1ulN60/E
E2NI4WE.2	4 port 2-pos int vol valve std-elect/2in so	1/32 x .25mm 175C/1000psi liq .2ulN60/E
E2NI4WE.5	4 port 2-pos int vol valve std-elect/2in so	1/32 x .25mm 175C/1000psi liq .5ulN60/E
E2SC10MWE	10 mpos common outlet path MW std-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
E2SC12MWE	12 mpos common outlet path MW std-elect/4in so	1/8 x 1mm 200C/200psi gas N60/E
E2SC16MWE	16 mpos common outlet path MW std-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
E2SC6MWE	6 mpos common outlet path MW std-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
E2SD10MWE	10 mpos dead-end path MW std-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
E2SD12MWE	12 mpos dead-end path MW std-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
E2SD16MWE	16 mpos dead-end path MW std-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
E2SD6MWE	6 mpos dead-end path MW std-elect/2in so	1/8 x 1mm 200C/400psi gas N60/E
E2SF10MWE	10 mpos flow-through MW std-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
E2SF12MWE	12 mpos flow-through MW std-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
E2SF16MWE	16 mpos flow-through MW std-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
E2SF6MWE	6 mpos flow-through MW std-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
E2ST10MWE	10 mpos trapping path MW std-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
E2ST12MWE	12 mpos trapping path MW std-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
E2ST16MWE	16 mpos trapping path MW std-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
E2ST6MWE	6 mpos trapping path MW std-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
E2STF10MWE	10 mpos trap/flow path MW std-elec/2in so	1/8 x 1mm 200C/200psi gas N60/E
E2STF12MWE	12 mpos trap/flow path MW std-elec/2in so	1/8 x 1mm 200C/200psi gas N60/E
E2STF16MWE	16 mpos trap/flow path MW std-elec/2in so	1/8 x 1mm 200C/200psi gas N60/E
E2STF6MWE	6 mpos trap/flow path MW std-elec/2in so	1/8 x 1mm 200C/200psi gas N60/E
E2VLSC4MWE2	4 mpos common outlet path MW std-elect/2in so	1/4 x 4mm 75C/100psi gas N60/E2
E2VLSC6MWE2	6 mpos common outlet path MW std-elect/2in so	1/4 x 4mm 75C/100psi gas N60/E2
E2VLSC8MWE2	8 mpos common outlet path MW std-elect/2in so	1/4 x 4mm 75C/100psi gas N60/E2