

VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]
> Cat.#s

> Current System AUD Prices



E2VLS10MWE2	10 mpos dead-end path MW std-elect/2in so	1/4 x 4mm 75C/100psi gas N60/E2
E2VLS4MWE2	4 mpos dead-end path MW std-elect/2in so	1/4 x 4mm 75C/100psi gas N60/E2
E2VLS6MWE2	6 mpos dead-end path MW std-elect/2in so	1/4 x 4mm 75C/100psi gas N60/E2
E2VLS8MWE2	8 mpos dead-end path MW std-elect/2in so	1/4 x 4mm 75C/100psi gas N60/E2
E2VLSF4MWE2	4 mpos flow-through MW std-elect/2in so	1/4 x 4mm 75C/100psi gas N60/E2
E2VLSF6MWE2	6 mpos flow-through MW std-elect/2in so	1/4 x 4mm 75C/100psi gas N60/E2
E2VLSF8MWE2	8 mpos flow-through MW std-elect/2in so	1/4 x 4mm 75C/100psi gas N60/E2
E30-110	Electric actuator 2-pos close mount	30 deg rotation 110Vac
E302-110	Electric actuator 2-pos 2in standoff	30 deg rotation 110Vac
E302-CE	Electric actuator 2-pos 2in standoff	30 deg rot. 24Vdcw.110/220Vac p.supply
E30-CE	Electric actuator 2-pos close mount	30 deg rot. 24Vdcw.110/220Vac p.supply
E30S-110	Electric actuator 2-pos for standoff	30 deg rotation 110Vac
E30S-CE	Electric actuator 2-pos for standoff	30 deg rot. 24Vdcw.110/220Vac p.supply
E36-110	Electric actuator 2-pos close mount	36 deg rotation 110Vac
E362-110	Electric actuator 2-pos 2in standoff	36 deg rotation 110Vac
E362-CE	Electric actuator 2-pos 2in standoff	36 deg rot. 24Vdcw.110/220Vac p.supply
E36-CE	Electric actuator 2-pos close mount	36 deg rot. 24Vdcw.110/220Vac p.supply
E36S-110	Electric actuator 2-pos for standoff	36 deg rotation 110Vac
E36S-CE	Electric actuator 2-pos for standoff	36 deg rot. 24Vdcw.110/220Vac p.supply
E410UWE	10 port 2-pos valve std-electric/4in so	1/8 x .75mm 225C/400psi gas N60/E
E410UWT	10 port 2-pos valve std-electric/4in so	1/8 x .75mm 330C/300psi gas N60/T
E4-110	Electric actuator mpos close mount	4 position 110Vac
E42-110	Electric actuator mpos 2in standoff	4 position 110Vac
E44UWE	4 port 2-pos valve std-electric/4in so	1/8 x .75mm 225C/400psi gas N60/E
E44UWT	4 port 2-pos valve std-electric/4in so	1/8 x .75mm 330C/300psi gas N60/T
E45-110	Electric actuator 2-pos close mount	45 deg rotation 110Vac
E452-110	Electric actuator 2-pos 2in standoff	45 deg rotation 110Vac
E452-CE	Electric actuator 2-pos 2in standoff	45 deg rot. 24Vdcw.110/220Vac p.supply
E45-CE	Electric actuator 2-pos close mount	45 deg rot.24Vdcw. 110/220Vac p.supply
E45S-110	Electric actuator 2-pos for standoff	45 deg rotation 110Vac
E45S-CE	Electric actuator 2-pos for standoff	45 deg rot. 24Vdcw.110/220Vac p.supply
E46UWE	6 port 2-pos valve std-electric/4in so	1/8 x .75mm 225C/400psi gas N60/E
E46UWT	6 port 2-pos valve std-electric/4in so	1/8 x .75mm 330C/300psi gas N60/T
E48UWE	8 port 2-pos valve std-electric/4in so	1/8 x .75mm 225C/400psi gas N60/E
E48UWT	8 port 2-pos valve std-electric/4in so	1/8 x .75mm 330C/300psi gas N60/T
E4C10UWE	10 port 2-pos valve std-electric/4in so	1/16 x .75mm 225C/400psi gas N60/E
E4C10UWT	10 port 2-pos valve std-electric/4in so	1/16 x .75mm 330C/300psi gas N60/T
E4C10WE	10 port 2-pos valve std-electric/4in so	1/16 x .4mm 225C/400psi gas N60/E
E4C10WT	10 port 2-pos valve std-electric/4in so	1/16 x .4mm 350C/300psi gas N60/T
E4C4UWE	4 port 2-pos valve std-electric/4in so	1/16 x .75mm 225C/400psi gas N60/E
E4C4UWT	4 port 2-pos valve std-electric/4in so	1/16 x .75mm 330C/300psi gas N60/T
E4C4WE	4 port 2-pos valve std-electric/4in so	1/16 x .4mm 225C/400psi gas N60/E
E4C4WT	4 port 2-pos valve std-electric/4in so	1/16 x .4mm 350C/300psi gas N60/T
E4C6UWE	6 port 2-pos valve std-electric/4in so	1/16 x .75mm 225C/400psi gas N60/E
E4C6UWT	6 port 2-pos valve std-electric/4in so	1/16 x .75mm 330C/300psi gas N60/T
E4C6WE	6 port 2-pos valve std-electric/4in so	1/16 x .4mm 225C/400psi gas N60/E
E4C6WT	6 port 2-pos valve std-electric/4in so	1/16 x .4mm 350C/300psi gas N60/T
E4C8UWE	8 port 2-pos valve std-electric/4in so	1/16 x .75mm 225C/400psi gas N60/E
E4C8UWT	8 port 2-pos valve std-electric/4in so	1/16 x .75mm 330C/300psi gas N60/T
E4C8WE	8 port 2-pos valve std-electric/4in so	1/16 x .4mm 225C/400psi gas N60/E
E4C8WT	8 port 2-pos valve std-electric/4in so	1/16 x .4mm 350C/300psi gas N60/T
E4N10WE	10 port 2-pos valve std-electric/4in so	1/32 x .25mm 225C/400psi gas N60/E
E4N10WT	10 port 2-pos valve std-electric/4in so	1/32 x .25mm 350C/300psi gas N60/T
E4N4WE	4 port 2-pos valve std-electric/4in so	1/32 x .25mm 225C/400psi gas N60/E
E4N4WT	4 port 2-pos valve std-electric/4in so	1/32 x .25mm 350C/300psi gas N60/T
E4N6WE	6 port 2-pos valve std-electric/4in so	1/32 x .25mm 225C/400psi gas N60/E
E4N6WT	6 port 2-pos valve std-electric/4in so	1/32 x .25mm 350C/300psi gas N60/T
E4N8WE	8 port 2-pos valve std-electric/4in so	1/32 x .25mm 225C/400psi gas N60/E
E4N8WT	8 port 2-pos valve std-electric/4in so	1/32 x .25mm 350C/300psi gas N60/T
E4S-110	Electric actuator mpos for standoff	4 position 110Vac
E4UW	4 port 2-pos valve std-electric	1/8 x .75mm 75C/5000psi liq N60/H