

VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]
> Cat.#s

> Current System AUD Prices



E4VL4MWE2	4 port 2-pos valve MW std-elect/4in so	1/4 x 4mm 75C/100psi gas N60/E2
E4VL6MWE2	6 port 2-pos valve MW std-elect/4in so	1/4 x 4mm 75C/100psi gas N60/E2
E4VL8MWE2	8 port 2-pos valve MW std-elect/4in so	1/4 x 4mm 75C/100psi gas N60/E
E4X2-110	Electric actuator mpos close mount	4x2 position 110Vac
E4X22-110	Electric actuator mpos 2in standoff	4x2 position 110Vac
E4X2S-110	Electric actuator mpos for standoff	4x2 position 110Vac
E60-110	Electric actuator 2-pos close mount	60 deg rotation 110Vac
E602-110	Electric actuator 2-pos 2in standoff	60 deg rotation 110Vac
E602-CE	Electric actuator 2-pos 2in standoff	60 deg rot. 24Vdcw.110/220Vac p.supply
E60-CE	Electric actuator 2-pos close mount	60 deg rot. 24Vdcw.110/220Vac p.supply
E60S-110	Electric actuator 2-pos for standoff	60 deg rotation 110Vac
E60S-CE	Electric actuator 2-pos for standoff	60 deg rot. 24Vdcw.110/220Vac p.supply
E6-110	Electric actuator mpos close mount	6 position 110Vac
E62-110	Electric actuator mpos 2in standoff	6 position 110Vac
E6S-110	Electric actuator mpos for standoff	6 position 110Vac
E6UW	6 port 2-pos valve std-electric	1/8 x .75mm 75C/5000psi liq N60/H
E6X2-110	Electric actuator mpos close mount	6x2 position 110Vac
E6X22-110	Electric actuator mpos 2in standoff	6x2 position 110Vac
E6X2S-110	Electric actuator mpos for standoff	6x2 position 110Vac
E8-110	Electric actuator mpos close mount	8 position 110Vac
E82-110	Electric actuator mpos 2in standoff	8 position 110Vac
E8S-110	Electric actuator mpos for standoff	8 position 110Vac
E8UW	8 port 2-pos valve std-electric	1/8 x .75mm 75C/5000psi liq N60/H
E90-110	Electric actuator 2-pos close mount	90 deg rotation 110Vac
E902-110	Electric actuator 2-pos 2in standoff	90 deg rotation 110Vac
E902-CE	Electric actuator 2-pos 2in standoff	90 deg rot. 24Vdcw.110/220Vac p.supply
E90-CE	Electric actuator 2-pos close mount	90 deg rot. 24Vdcw.110/220Vac p.supply
E90S-110	Electric actuator 2-pos for standoff	90 deg rotation 110Vac
E90S-CE	Electric actuator 2-pos for standoff	90 deg rot. 24Vdcw.110/220Vac p.supply
EAOR21	External adaptor 1/8in to 10-32 thread	O-ring seal SS
EAOR22	External adaptor 1/8in to 5/16-24 thread	O-ring seal SS
EBRU12L	Bulkhead external red. union 1/8in x 1/16in	1mm bore SS
EBRU12T	Bulkhead external red. union 1/8in x 1/16in	1/16in trough bore SS
EBRU14L	Bulkhead external red. union 1/4in x 1/16in	1mm bore SS
EBRU14T	Bulkhead external red. union 1/4in x 1/16in	1/16in trough bore SS
EBRU24L	Bulkhead external red. union 1/4in x 1/8in	2mm bore SS
EBU2L	Bulkhead external union 1/8in	2mm bore SS
EBU2T	Bulkhead external union 1/8in	1/8in through bore SS
EBU4	Bulkhead external union 1/4in	2mm bore SS
EBU4L	Bulkhead external union 1/4in	4.6mm bore SS
EBU4T	Bulkhead external union 1/4in	1/4in through bore SS
EC10UW	10 port 2-pos valve std-electric	1/16 x .75mm 75C/5000psi liq N60/H
EC10W	10 port 2-pos valve std-electric	1/16 x .4mm 75C/5000psi liq N60/H
EC4UW	4 port 2-pos valve std-electric	1/16 x .75mm 75C/5000psi liq N60/H
EC4W	4 port 2-pos valve std-electric	1/16 x .4mm 75C/5000psi liq N60/H
EC6UW	6 port 2-pos valve std-electric	1/16 x .75mm 75C/5000psi liq N60/H
EC6W	6 port 2-pos valve std-electric	1/16 x .4mm 75C/5000psi liq N60/H
EC8UW	8 port 2-pos valve std-electric	1/16 x .75mm 75C/5000psi liq N60/H
EC8W	8 port 2-pos valve std-electric	1/16 x .4mm 75C/5000psi liq N60/H
ECEF111.0	External column end fitting 1/16in	.25mm bore 1mm cone without frit 316SS
ECEF111.0F	External column end fitting 1/16in	.25mm bore 1mm cone removable 2um frit 316SS
ECEF1K1	External column end fitting 1in x 1/16in	.75mm bore 20mm cone without frit 316SS
ECEF1K1F	External column end fitting 1in x 1/16in	.75mm bore 20mm cone removable 2um frit 316SS
ECEF211.0	External column end fitting 1/8in x 1/16in	.25mm bore 1mm cone without frit 316SS
ECEF211.0F	External column end fitting 1/8in x 1/16in	.25mm bore 1mm cone removable 2um frit 316SS
ECEF412.1	External column end fitting 1/4in x 1/16in	.4mm bore 2.1mm conewithout frit 316SS
ECEF412.1F	External column end fitting 1/4in x 1/16in	.4mm bore 2.1mm coneremovable 2um frit 316SS
ECEF413.0	External column end fitting 1/4in x 1/16in	.4mm bore 3mm cone without frit 316SS
ECEF413.0F	External column end fitting 1/4in x 1/16in	.4mm bore 3mm cone removable 2um frit 316SS
ECEF414.0	External column end fitting 1/4in x 1/16in	.4mm bore 4mm cone without frit 316SS
ECEF414.0F	External column end fitting 1/4in x 1/16in	.4mm bore 4mm cone removable 2um frit 316SS