

VICI Valco-Cheminert PRODUCT LIST 2012

[Ctrl F]
> Cat.#s

> Current System AUD Prices



ECEF414.6	External column end fitting 1/4in x 1/16in	.4mm bore 4.6mm conewithout frit 316SS
ECEF414.6F	External column end fitting 1/4in x 1/16in	.4mm bore 4.6mm coneremovable 2um frit 316SS
ECEF616.0	External column end fitting 3/8in x 1/16in	.35mm bore 6mm cone without frit 316SS
ECEF616.0F	External column end fitting 3/8in x 1/16in	.35mm bore 6mm cone removable 2um frit 316SS
ECEF617.0	External column end fitting 3/8in x 1/16in	.4mm bore 7mm cone without frit 316SS
ECEF617.0F	External column end fitting 3/8in x 1/16in	.4mm bore 7mm cone removable 2um frit 316SS
ECEF8110.0	External column end fitting 1/2in x 1/16in	.75mm bore 10mm cone without frit 316SS
ECEF8110.0F	External column end fitting 1/2in x 1/16in	.75mm bore 10mm cone removable 2um frit 316SS
ECEF819.0	External column end fitting 1/2in x 1/16in	.75mm bore 9mm cone without frit 316SS
ECEF819.0F	External column end fitting 1/2in x 1/16in	.75mm bore 9mm cone removable 2um frit 316SS
ECI4UW.2	4 port 2-pos int vol valve std-electric	1/16 x .75mm 75C/5000psi liq .2ul N60/H
ECI4UW.5	4 port 2-pos int vol valve std-electric	1/16 x .75mm 75C/5000psi liq .5ul N60/H
ECI4UW1	4 port 2-pos int vol valve std-electric	1/16 x .75mm 75C/5000psi liq 1ul N60/H
ECI4UW2	4 port 2-pos int vol valve std-electric	1/16 x .75mm 75C/5000psi liq 2ul N60/H
ECI4W.06	4 port 2-pos int vol valve std-electric	1/16 x .4mm 75C/5000psi liq .06ul N60/H
ECI4W.1	4 port 2-pos int vol valve std-electric	1/16 x .4mm 75C/5000psi liq .1ul N60/H
ECI4W.2	4 port 2-pos int vol valve std-electric	1/16 x .4mm 75C/5000psi liq .2ul N60/H
ECI4W.5	4 port 2-pos int vol valve std-electric	1/16 x .4mm 75C/5000psi liq .5ul N60/H
ECMH	OBSOLETE! Please ask for alternatives!	
ECMH2	OBSOLETE! Please ask for alternatives!	
ECMH2-CE	OBSOLETE! Please ask for alternatives!	
ECMH-CE	OBSOLETE! Please ask for alternatives!	
ECMHS	OBSOLETE! Please ask for alternatives!	
ECMHS-CE	OBSOLETE! Please ask for alternatives!	
ECMT	OBSOLETE! Please ask for alternatives!	
ECMT2	OBSOLETE! Please ask for alternatives!	
ECMT2-CE	OBSOLETE! Please ask for alternatives!	
ECMT-CE	OBSOLETE! Please ask for alternatives!	
ECMTS	OBSOLETE! Please ask for alternatives!	
ECMTS-CE	OBSOLETE! Please ask for alternatives!	
ECSD10UW	10 mpos dead-end path std-electric	1/16 x .4mm 75C/5000psi liq N60/E
ECSD4UW	4 mpos dead-end path std-electric	1/16 x .4mm 75C/5000psi liq N60/E
ECSD6UW	6 mpos dead-end path std-electric	1/16 x .4mm 75C/5000psi liq N60/E
ECST4UW	4 mpos trapping path std-electric	1/16 x .4mm 75C/5000psi liq N60/E
ECST6UW	6 mpos trapping path std-electric	1/16 x .4mm 75C/5000psi liq N60/E
ED	Micro electric actuator 2-pos closemount	medium torque 24Vdc w.110/220Vac p-supply
ED10UW	10 port 2-pos valve m-electric	1/8 x .75mm 75C/5000psi liq N60/H
ED2	Micro electric actuator 2-pos/2in so	high torque 24Vdc w.110/220Vac p-supply
ED2CI4UWE.2	4 port 2-pos int vol valve m-elect/2in so	1/16 x .75mm 175C/1000psi liq .2ul N60/E
ED2CI4UWE.5	4 port 2-pos int vol valve m-elect/2in so	1/16 x .75mm 175C/1000psi liq .5ul N60/E
ED2CI4UWE1	4 port 2-pos int vol valve m-elect/2in so	1/16 x .75mm 175C/1000psi liq 1ul N60/E
ED2CI4UWE2	4 port 2-pos int vol valve m-elect/2in so	1/16 x .75mm 175C/1000psi liq 2ul N60/E
ED2I4UWE.2	4 port 2-pos int vol valve m-elect/2in so	1/8 x .75mm 175C/1000psi liq .2ul N60/E
ED2I4UWE.5	4 port 2-pos int vol valve m-elect/2in so	1/8 x .75mm 175C/1000psi liq .5ul N60/E
ED2I4UWE1	4 port 2-pos int vol valve m-elect/2in so	1/8 x .75mm 175C/1000psi liq 1ul N60/E
ED2I4UWE2	4 port 2-pos int vol valve m-elect/2in so	1/8 x .75mm 175C/1000psi liq 2ul N60/E
ED410UWE	10 port 2-pos valve m-electric/4in so	1/8 x .75mm 225C/400psi gas N60/E
ED410UWT	10 port 2-pos valve m-electric/4in so	1/8 x .75mm 330C/300psi gas N60/T
ED44UWE	4 port 2-pos valve m-electric/4in so	1/8 x .75mm 225C/400psi gas N60/E
ED44UWT	4 port 2-pos valve m-electric/4in so	1/8 x .75mm 330C/300psi gas N60/T
ED46UWE	6 port 2-pos valve m-electric/4in so	1/8 x .75mm 225C/400psi gas N60/E
ED46UWT	6 port 2-pos valve m-electric/4in so	1/8 x .75mm 330C/300psi gas N60/T
ED48UWE	8 port 2-pos valve m-electric/4in so	1/8 x .75mm 225C/400psi gas N60/E
ED48UWT	8 port 2-pos valve m-electric/4in so	1/8 x .75mm 330C/300psi gas N60/T
ED4C10UWE	10 port 2-pos valve m-electric/4in so	1/16 x .75mm 225C/400psi gas N60/E
ED4C10UWT	10 port 2-pos valve m-electric/4in so	1/16 x .75mm 330C/300psi gas N60/T
ED4C4UWE	4 port 2-pos valve m-electric/4in so	1/16 x .75mm 225C/400psi gas N60/E
ED4C4UWT	4 port 2-pos valve m-electric/4in so	1/16 x .75mm 330C/300psi gas N60/T
ED4C6UWE	6 port 2-pos valve m-electric/4in so	1/16 x .75mm 225C/400psi gas N60/E
ED4C6UWT	6 port 2-pos valve m-electric/4in so	1/16 x .75mm 330C/300psi gas N60/T
ED4C8UWE	8 port 2-pos valve m-electric/4in so	1/16 x .75mm 225C/400psi gas N60/E