

# VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]  
> Cat.#s

> Current System AUD Prices



ED4C8UWT	8 port 2-pos valve m-electric/4in so	1/16 x .75mm 330C/300psi gas N60/T
ED4UW	4 port 2-pos valve m-electric	1/8 x .75mm 75C/5000psi liq N60/H
ED6UW	6 port 2-pos valve m-electric	1/8 x .75mm 75C/5000psi liq N60/H
ED8UW	8 port 2-pos valve m-electric	1/8 x .75mm 75C/5000psi liq N60/H
EDC10UW	10 port 2-pos valve m-electric	1/16 x .75mm 75C/5000psi liq N60/H
EDC4UW	4 port 2-pos valve m-electric	1/16 x .75mm 75C/5000psi liq N60/H
EDC6UW	6 port 2-pos valve m-electric	1/16 x .75mm 75C/5000psi liq N60/H
EDC8UW	8 port 2-pos valve m-electric	1/16 x .75mm 75C/5000psi liq N60/H
EDCI4UW.2	4 port 2-pos int vol valve m-electric	1/16 x .75mm 75C/5000psi liq .2ul N60/H
EDCI4UW.5	4 port 2-pos int vol valve m-electric	1/16 x .75mm 75C/5000psi liq .5ul N60/H
EDCI4UW1	4 port 2-pos int vol valve m-electric	1/16 x .75mm 75C/5000psi liq 1ul N60/H
EDCI4UW2	4 port 2-pos int vol valve m-electric	1/16 x .75mm 75C/5000psi liq 2ul N60/H
EDL10UW	10 port 2-pos valve m-electric	1/8 x 1.0mm 75C/5000psi liq N60/H
EDL4UW	4 port 2-pos valve m-electric	1/8 x 1.7mm 75C/5000psi liq N60/H
EDL6UW	6 port 2-pos valve m-electric	1/8 x 1.7mm 75C/5000psi liq N60/H
EDL8UW	8 port 2-pos valve m-electric	1/8 x 1.3mm 75C/5000psi liq N60/H
EDS	Micro electric actuator 2-pos for so	high torque 24Vdc w.110/220Vac p-supply
EH	Micro electric actuator 2-pos closmount	high speed 24Vdc w.110/220Vac p-supply
EH2	Micro electric actuator 2-pos/2in so	high speed 24Vdc w.110/220Vac p-supply
EH4C10WE	10 port 2-pos valve m-electric/4in so	1/16 x .4mm 225C/400psi gas N60/E
EH4C10WT	10 port 2-pos valve m-electric/4in so	1/16 x .4mm 350C/300psi gas N60/T
EH4C4WE	4 port 2-pos valve m-electric/4in so	1/16 x .4mm 225C/400psi gas N60/E
EH4C4WT	4 port 2-pos valve m-electric/4in so	1/16 x .4mm 350C/300psi gas N60/T
EH4C6WE	6 port 2-pos valve m-electric/4in so	1/16 x .4mm 225C/400psi gas N60/E
EH4C6WT	6 port 2-pos valve m-electric/4in so	1/16 x .4mm 350C/300psi gas N60/T
EH4C8WE	8 port 2-pos valve m-electric/4in so	1/16 x .4mm 225C/400psi gas N60/E
EH4C8WT	8 port 2-pos valve m-electric/4in so	1/16 x .4mm 350C/300psi gas N60/T
EH4N10WE	10 port 2-pos valve m-electric act/4in so	1/32 x .25mm 225C/400psi gas N60/E
EH4N10WT	10 port 2-pos valve m-electric/4in so	1/32 x .25mm 350C/300psi gas N60/T
EH4N4WE	4 port 2-pos valve m-electric/4in so	1/32 x .25mm 225C/400psi gas N60/E
EH4N4WT	4 port 2-pos valve m-electric/4in so	1/32 x .25mm 350C/300psi gas N60/T
EH4N6WE	6 port 2-pos valve m-electric/4in so	1/32 x .25mm 225C/400psi gas N60/E
EH4N6WT	6 port 2-pos valve m-electric/4in so	1/32 x .25mm 350C/300psi gas N60/T
EH4N8WE	8 port 2-pos valve m-electric/4in so	1/32 x .25mm 225C/400psi gas N60/E
EH4N8WT	8 port 2-pos valve m-electric/4in so	1/32 x .25mm 350C/300psi gas N60/T
EHS	Micro electric actuator 2-pos for so	high speed 24Vdc w.110/220Vac p-supply
EL10UW	10 port 2-pos valve std-electric	1/8 x 1.0mm 75C/5000psi liq N60/H
EL4UW	4 port 2-pos valve std-electric	1/8 x 1.7mm 75C/5000psi liq N60/H
EL6UW	6 port 2-pos valve std-electric	1/8 x 1.7mm 75C/5000psi liq N60/H
EL8UW	8 port 2-pos valve std-electric	1/8 x 1.3mm 75C/5000psi liq N60/H
EMH	!!!RECOMMENDED EMH-CE	
EMH2	!!!RECOMMENDED EMH2-CE	
EMH2-CE	Micro electric actuator mpos 2in so	high speed 24Vdc w. 110/220Vac p-supply
EMH-CE	Micro electric actuator mpos closmount	high speed 24Vdc w. 110/220Vac p-supply
EMHS	!!!RECOMMENDED EMHS-CE	
EMHS-CE	Micro electric actuator mpos for so	high speed 24Vdc w. 110/220Vac p-supply
EMT	!!!RECOMMENDED EMT-CE	
EMT2	!!!RECOMMENDED EMT2-CE	
EMT2-CE	Micro electric actuator mpos 2in so	high torque 24Vdc w.110/220Vac p-supply
EMT2CSC10MWE	10 mpos common outlet path MW m-elect/2in so	1/16 x 1mm 200C/200psi gas N60/E
EMT2CSC12MWE	12 mpos common outlet path MW m-elect/2in so	1/16 x 1mm 200C/200psi gas N60/E
EMT2CSC16MWE	16 mpos common outlet path MW m-elect/2in so	1/16 x 1mm 200C/200psi gas N60/E
EMT2CSC6MWE	6 mpos common outlet path MW m-elect/2in so	1/16 x 1mm 200C/200psi gas N60/E
EMT2CSD10MWE	10 mpos dead-end path MW m-elect/2in so	1/16 x .75mm 200C/400psi gas N60/E
EMT2CSD12MWE	12 mpos dead-end path MW m-elect/2in so	1/16 x .75mm 200C/400psi gas N60/E
EMT2CSD16MWE	16 mpos dead-end path MW m-elect/2in so	1/16 x .75mm 200C/400psi gas N60/E
EMT2CSD6MWE	6 mpos dead-end path MW m-elect/2in so	1/16 x .75mm 200C/400psi gas N60/E
EMT2CSF10MWE	10 mpos flow-through MW m-elect/2in so	1/16 x 1mm 200C/200psi gas N60/E
EMT2CSF12MWE	12 mpos flow-through MW m-elect/2in so	1/16 x 1mm 200C/200psi gas N60/E
EMT2CSF16MWE	16 mpos flow-through MW m-elect/2in so	1/16 x 1mm 200C/200psi gas N60/E
EMT2CSF6MWE	6 mpos flow-through MW m-elect/2in so	1/16 x 1mm 200C/200psi gas N60/E