

VICIValco-Cheminert PRODUCT LIST 2012

(Ctrl F)
> CatL#s

> Current System AUD Prices



EMT2CST10MWE	10 mpos trapping path MW m-elect/2in so	1/16 x .75mm 200C/200psi gas N60/E
EMT2CST12MWE	12 mpos trapping path MW m-elect/2in so	1/16 x .75mm 200C/200psi gas N60/E
EMT2CST16MWE	16 mpos trapping path MW m-elect/2in so	1/16 x .75mm 200C/200psi gas N60/E
EMT2CST6MWE	6 mpos trapping path MW m-elect/2in so	1/16 x .75mm 200C/200psi gas N60/E
EMT2CSTF10MWE	10 mpos trap/flow path MW m-elect/2in so	1/16 x .75mm 200C/200psi gas N60/E
EMT2CSTF12MWE	12 mpos trap/flow path MW m-elect/2in so	1/16 x .75mm 200C/200psi gas N60/E
EMT2CSTF16MWE	16 mpos trap/flow path MW m-elect/2in so	1/16 x .75mm 200C/200psi gas N60/E
EMT2CSTF6MWE	6 mpos trap/flow path MW m-elect/2in so	1/16 x .75mm 200C/200psi gas N60/E
EMT2SC10MWE	10 mpos common outlet path MW m-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
EMT2SC12MWE	12 mpos common outlet path MWm-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
EMT2SC16MWE	16 mpos common outlet path MW m-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
EMT2SC6MWE	6 mpos common outlet path MW m-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
EMT2SD10MWE	10 mpos dead-end path MW m-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
EMT2SD12MWE	12 mpos dead-end path MW m-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
EMT2SD16MWE	16 mpos dead-end path MW m-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
EMT2SD6MWE	6 mpos dead-end path MW m-elect/2in so	1/8 x 1mm 200C/400psi gas N60/E
EMT2SF10MWE	10 mpos flow-through MW m-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
EMT2SF12MWE	12 mpos flow-through MW m-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
EMT2SF16MWE	16 mpos flow-through MW m-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
EMT2SF6MWE	6 mpos flow-through MW m-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
EMT2ST10MWE	10 mpos trapping path MW m-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
EMT2ST12MWE	12 mpos trapping path MW m-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
EMT2ST16MWE	16 mpos trapping path MW m-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
EMT2ST6MWE	6 mpos trapping path MW m-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
EMT2STF10MWE	10 mpos trap/flow path MW m-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
EMT2STF12MWE	12 mpos trap/flow path MW m-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
EMT2STF16MWE	16 mpos trap/flow path MW m-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
EMT2STF6MWE	6 mpos trap/flow path MW m-elect/2in so	1/8 x 1mm 200C/200psi gas N60/E
EMT2VLS4MWE2	4 mpos common outlet path MW m-elect/2in so	1/4 x 4mm 75C/100psi gas N60/E2
EMT2VLS6MWE2	6 mpos common outlet path MW m-elect/2in s	1/4 x 4mm 75C/100psi gas N60/E2
EMT2VLS8MWE2	8 mpos common outlet path MW m-elect/2in so	1/4 x 4mm 75C/100psi gas N60/E2
EMT2VLS10MWE2	10 mpos dead-end path MW m-elect/2in so	1/4 x 4mm 75C/100psi gas N60/E2
EMT2VLS4MWE2	4 mpos dead-end path MW m-elect/2in so	1/4 x 4mm 75C/100psi gas N60/E2
EMT2VLS6MWE2	6 mpos dead-end path MW m-elect/2in so	1/4 x 4mm 75C/100psi gas N60/E2
EMT2VLS8MWE2	8 mpos dead-end path MW m-elect/2in so	1/4 x 4mm 75C/100psi gas N60/E2
EMT2VLSF4MWE2	4 mpos flow-through MW m-elect/2in so	1/4 x 4mm 75C/100psi gas N60/E2
EMT2VLSF6MWE2	6 mpos flow-through MW m-elect/2in so	1/4 x 4mm 75C/100psi gas N60/E2
EMT2VLSF8MWE2	8 mpos flow-through MW m-elect/2in so	1/4 x 4mm 75C/100psi gas N60/E2
EMT-CE	Micro electric actuator mpos closemount	high torque 24Vdc w.110/220Vac p-supply
EMTCS10UW	10 mpos dead-end path m-electric	1/16 x .4mm 75C/5000psi liq N60/E
EMTCS4UW	4 mpos dead-end path m-electric	1/16 x .4mm 75C/5000psi liq N60/E
EMTCS6UW	6 mpos dead-end path m-electric	1/16 x .4mm 75C/5000psi liq N60/E
EMTCS4UW	4 mpos trapping path m-electric	1/16 x .4mm 75C/5000psi liq N60/E
EMTCS6UW	6 mpos trapping path m-electric	1/16 x .4mm 75C/5000psi liq N60/E
EMTS	RECOMMENDED EMTS-CE	
EMTS-CE	Micro electric actuator mpos for so	high torque 24Vdc w.110/220Vac p-supply
EMTSD4UW	4 mpos dead-end path m-electric	1/8 x .75mm 75C/5000psi liq N60/E
EMTSD6UW	6 mpos dead-end path m-electric	1/8 x .75mm 75C/5000psi liq N60/E
EMTSD8UW	8 mpos dead-end path m-electric	1/8 x .75mm 75C/5000psi liq N60/E
EN.5	External nut 1/32in hex	SS
EN.5KN	External nut 1/32in knurled	SS
EN1	External nut 1/16in hex	SS
EN1K	External nut 1in hex	SS
EN2	External nut 1/8in hex	SS
EN2SI	Septum injector nut 1/8in connection	with polyimide support and 1/4in septum
EN4	External nut 1/4in hex	SS
EN6	External nut 3/8in hex	SS
EN8	External nut 1/2in hex	SS
EP	Micro electric actuator 2-pos closemount	medium torque 24Vdc w.110/220Vac p-supply
EP2	Micro electric actuator 2-pos/2in so	medium torque 24Vdc w.110/220Vac p-supply
EP2CI4WE.06	4 port 2-pos int vol valve m-elect/2in so	1/16 x .4mm 175C/1000psi liq .06ul N60/E