

VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]
> Cat.#s

> Current System AUD Prices



EP2CI4WE.1	4 port 2-pos int vol valve m-elect/2in so	1/16 x .4mm 175C/1000psi liq .1ul N60/E
EP2CI4WE.2	4 port 2-pos int vol valve m-elect/2in so	1/16 x .4mm 175C/1000psi liq .2ul N60/E
EP2CI4WE.5	4 port 2-pos int vol valve m-elect/2in so	1/16 x .4mm 175C/1000psi liq .5ul N60/E
EP2NI4WE.06	4 port 2-pos int vol valve m-elect/2in so	1/32 x .25mm 175C/1000psi liq .06ulN60/E
EP2NI4WE.1	4 port 2-pos int vol valve m-elect/2in so	1/32 x .25mm 175C/1000psi liq .1ulN60/E
EP2NI4WE.2	4 port 2-pos int vol valve m-elect/2in so	1/32 x .25mm 175C/1000psi liq .2ulN60/E
EP2NI4WE.5	4 port 2-pos int vol valve m-elect/2in so	1/32 x .25mm 175C/1000psi liq .5ulN60/E
EPC10W	10 port 2-pos valve m-electric hi-psi	1/16 x .4mm 75C/5000psi liq N60/H
EPC4W	4 port 2-pos valve m-electric hi-psi	1/16 x .4mm 75C/5000psi liq N60/H
EPC6W	6 port 2-pos valve m-electric hi-psi	1/16 x .4mm 75C/5000psi liq N60/H
EPC8W	8 port 2-pos valve m-electric hi-psi	1/16 x .4mm 75C/5000psi liq N60/H
EPCI4W.06	4 port 2-pos int vol valve m-elect hi-psi	1/16 x .4mm 75C/5000psi liq .06ul N60/H
EPCI4W.1	4 port 2-pos int vol valve m-elect hi-psi	1/16 x .4mm 75C/5000psi liq .1ul N60/H
EPCI4W.2	4 port 2-pos int vol valve m-elect hi-psi	1/16 x .4mm 75C/5000psi liq .2ul N60/H
EPCI4W.5	4 port 2-pos int vol valve m-elect hi-psi	1/16 x .4mm 75C/5000psi liq .5ul N60/H
EPS	Micro electric actuator 2-pos for so	medium torque 24Vdc w.110/220Vac p-supply
EQ	Micro electric actuator 2-pos closemount	highest speed 24Vdc w.110/220Vac p-supply
EQ2	Micro electric actuator 2-pos/2in so	highest speed 24Vdc w.110/220Vac p-supply
EQS	Micro electric actuator 2-pos for so	highest speed 24Vdc w.110/220Vac p-supply
ERU21	External reducing union 1/8in x 1/16in	.75mm bore SS
ERU21L	External reducing union 1/8in x 1/16in	1mm bore SS
ERU21T	External reducing union 1/8in x 1/16in	1/16in through bore SS
ERU41	External reducing union 1/4in x 1/16in	.75mm bore SS
ERU41T	External reducing union 1/4in x 1/16in	1/16in through bore SS
ERU42	External reducing union 1/4in x 1/8in	0.75mm bore SS
ERU42L	External reducing union 1/4in x 1/8in	2mm bore SS
ERU42T	External reducing union 1/4in x 1/8in	1/8in through bore SS
ESD4UW	4 mpos dead-end path std-electric	1/8 x .75mm 75C/5000psi liq N60/E
ESD6UW	6 mpos dead-end path std-electric	1/8 x .75mm 75C/5000psi liq N60/E
ESD8UW	8 mpos dead-end path std-electric	1/8 x .75mm 75C/5000psi liq N60/E
ET	Micro electric actuator 2-pos closemount	highest torque 24Vdc w.110/220Vac p-supply
ET2	Micro electric actuator 2-pos/2in so	highest torque 24Vdc w.110/220Vac p-supply
ET4VL4MWE2	4 port 2-pos valve MW m-electric/4in so	1/4 x 4mm 75C/100psi gas N60/E2
ET4VL6MWE2	6 port 2-pos valve MW m-electric/4in so	1/4 x 4mm 75C/100psi gas N60/E2
ET4VL8MWE2	8 port 2-pos valve MW m-electric/4in so	1/4 x 4mm 75C/100psi gas N60/E2
ETS	Micro electric actuator 2-pos for so	highest torque 24Vdc w.110/220Vac p-supply
EU.5	External union 1/32in	.25mm bore SS
EU.5L	External union 1/32in	.50mm bore SS
EU.5T	External union 1/32in	1/32in through bore SS
EU2	External union 1/8in	1mm bore SS
EU2L	External union 1/8in	2mm bore SS
EU2T	External union 1/8in	1/8in through bore SS
EU4	External union 1/4in	2mm bore SS
EU4L	External union 1/4in	4.6mm bore SS
EU4T	External union 1/4in	1/4in through bore SS
EUD	Universal actuator no interface no clamp ring	medium torque 24Vdc w.110/220Vac p-supply
EUDA	Universal actuator RS-232/485 no clamp ring	medium torque 24Vdc w.110/220Vac p-supply
EUDB	Universal actuator USB no clamp ring	medium torque 24Vdc w.110/220Vac p-supply
EUDC	Universal actuator BCD no clamp ring	medium torque 24Vdc w.110/220Vac p-supply
EUH	Universal actuator no interface no clamp ring	high speed 24Vdc w.110/220Vac p-supply
EUHA	Universal actuator RS-232/485 no clamp ring	high speed 24Vdc w.110/220Vac p-supply
EUHB	Universal actuator USB no clamp ring	high speed 24Vdc w.110/220Vac p-supply
EUHC	Universal actuator BCD no clamp ring	high speed 24Vdc w.110/220Vac p-supply
EUT	Universal actuator no interface no clamp ring	high torque 24Vdc w.110/220Vac p-supply
EUTA	Universal actuator RS-232/485 no clamp ring	high torque 24Vdc w.110/220Vac p-supply
EUTB	Universal actuator USB no clamp ring	high torque 24Vdc w.110/220Vac p-supply
EUTC	Universal actuator BCD no clamp ring	high torque 24Vdc w.110/220Vac p-supply
EZA1	Ext./int. adapter 1/16in x 1/16in SS	
EZA2	Ext./int. adapter 1/8in x 1/8in SS	
EZBRU.51	Bulkhead ext/int red. union 1/16in x 1/32in	.25mm bore SS
EZBRU.51L	Bulkhead ext/int red. union 1/16in x 1/32in	.5mm bore SS