

VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]
> Cat.#s

> Current System AUD Prices



EZRU41C	Ext./Int. reducing unions 1/4in x 1/16in	.25mm bore SS
EZRU41T	Ext./Int. reducing unions 1/4in x 1/16in	1/16in through bore SS
EZRU42	Ext./int. reducing union 1/4in x 1/8in	1mm bore SS
EZRU42L	Ext./int. reducing union 1/4in x 1/8in	2mm bore SS
EZRU42T	Ext./int. reducing union 1/4in x 1/8in	1/8in through bore SS
EZU.5	Ext./int union 1/32in	.25mm bore SS
EZU.5L	Ext./int union 1/32in	.5mm bore SS
EZU1	Ext./int union 1/16in	.75mm bore SS
EZU1C	Ext./int union 1/16in	.25mm bore SS
EZU1M	Ext./int union 1/16in	.5mm bore SS
EZU1T	Ext./int union 1/16in	1/16in through bore SS
EZU2	Ext./int. union 1/8in	1mm bore SS
EZU2L	Ext./int. union 1/8in	2mm bore SS
EZU2T	Ext./int. union 1/8in	1/8in through bore SS
FC10AS1K	Flow controller M100 standard knob	1/8in ext 150ml N2 40psi Aluminum/SS
FC10AS1S3	Flow controller M100 Spectrol 3-dial	1/8in ext 150ml N2 40psi Aluminum/SS
FC10AS1S4	Flow controller M100 Spectrol 4-dial	1/8in ext 150ml N2 40psi Aluminum/SS
FC10AS2K	Flow controller M100 standard knob	1/8in ext 250ml N2 40psi Aluminum/SS
FC10AS2S3	Flow controller M100 Spectrol 3-dial	1/8in ext 250ml N2 40psi Aluminum/SS
FC10AS2S4	Flow controller M100 Spectrol 4-dial	1/8in ext 250ml N2 40psi Aluminum/SS
FC10AS3K	Flow controller M100 standard knob	1/8in ext 850ml N2 40psi Aluminum/SS
FC10AS3S3	Flow controller M100 Spectrol 3-dial	1/8in ext 850ml N2 40psi Aluminum/SS
FC10AS3S4	Flow controller M100 Spectrol 4-dial	1/8in ext 850ml N2 40psi Aluminum/SS
FC10AS4K	Flow controller M100 standard knob	1/8in ext 1.2l N2 40psi Aluminum/SS
FC10AS4S3	Flow controller M100 Spectrol 3-dial	1/8in ext 1.2l N2 40psi Aluminum/SS
FC10AS4S4	Flow controller M100 Spectrol 4-dial	1/8in ext 1.2l N2 40psi Aluminum/SS
FC10AS5K	Flow controller M100 standard knob	1/8in ext 4.5l N2 40psi Aluminum/SS
FC10AS5S3	Flow controller M100 Spectrol 3-dial	1/8in ext 4.5l N2 40psi Aluminum/SS
FC10AS5S4	Flow controller M100 Spectrol 4-dial	1/8in ext 4.5l N2 40psi Aluminum/SS
FC10AS6K	Flow controller M100 standard knob	1/8in ext 10.0l N2 40psi Aluminum/SS
FC10AS6S3	Flow controller M100 Spectrol 3-dial	1/8in ext 10.0l N2 40psi Aluminum/SS
FC10AS6S4	Flow controller M100 Spectrol 4-dial	1/8in ext 10.0l N2 40psi Aluminum/SS
FC10AV1K	Flow controller M100 standard knob	1/8in ext 150ml N2 40psi Aluminum/Viton
FC10AV1S3	Flow controller M100 Spectrol 3-dial	1/8in ext 150ml N2 40psi Aluminum/Viton
FC10AV1S4	Flow controller M100 Spectrol 4-dial	1/8in ext 150ml N2 40psi Aluminum/Viton
FC10AV2K	Flow controller M100 standard knob	1/8in ext 250ml N2 40psi Aluminum/Viton
FC10AV2S3	Flow controller M100 Spectrol 3-dial	1/8in ext 250ml N2 40psi Aluminum/Viton
FC10AV2S4	Flow controller M100 Spectrol 4-dial	1/8in ext 250ml N2 40psi Aluminum/Viton
FC10AV3K	Flow controller M100 standard knob	1/8in ext 850ml N2 40psi Aluminum/Viton
FC10AV3S3	Flow controller M100 Spectrol 3-dial	1/8in ext 850ml N2 40psi Aluminum/Viton
FC10AV3S4	Flow controller M100 Spectrol 4-dial	1/8in ext 850ml N2 40psi Aluminum/Viton
FC10AV4K	Flow controller M100 standard knob	1/8in ext 1.2l N2 40psi Aluminum/Viton
FC10AV4S3	Flow controller M100 Spectrol 3-dial	1/8in ext 1.2l N2 40psi Aluminum/Viton
FC10AV4S4	Flow controller M100 Spectrol 4-dial	1/8in ext 1.2l N2 40psi Aluminum/Viton
FC10AV5K	Flow controller M100 standard knob	1/8in ext 4.5l N2 40psi Aluminum/Viton
FC10AV5S3	Flow controller M100 Spectrol 3-dial	1/8in ext 4.5l N2 40psi Aluminum/Viton
FC10AV5S4	Flow controller M100 Spectrol 4-dial	1/8in ext 4.5l N2 40psi Aluminum/Viton
FC10AV6K	Flow controller M100 standard knob	1/8in ext 10.0l N2 40psi Aluminum/Viton
FC10AV6S3	Flow controller M100 Spectrol 3-dial	1/8in ext 10.0l N2 40psi Aluminum/Viton
FC10AV6S4	Flow controller M100 Spectrol 4-dial	1/8in ext 10.0l N2 40psi Aluminum/Viton
FC10SS1K	Flow controller M100 standard knob	1/8in ext 150ml N2 40psi SS/SS
FC10SS1S3	Flow controller M100 Spectrol 3-dial	1/8in ext 150ml N2 40psi SS/SS
FC10SS1S4	Flow controller M100 Spectrol 4-dial	1/8in ext 150ml N2 40psi SS/SS
FC10SS2K	Flow controller M100 standard knob	1/8in ext 250ml N2 40psi SS/SS
FC10SS2S3	Flow controller M100 Spectrol 3-dial	1/8in ext 250ml N2 40psi SS/SS
FC10SS2S4	Flow controller M100 Spectrol 4-dial	1/8in ext 250ml N2 40psi SS/SS
FC10SS3K	Flow controller M100 standard knob	1/8in ext 850ml N2 40psi SS/SS
FC10SS3S3	Flow controller M100 Spectrol 3-dial	1/8in ext 850ml N2 40psi SS/SS
FC10SS3S4	Flow controller M100 Spectrol 4-dial	1/8in ext 850ml N2 40psi SS/SS
FC10SS4K	Flow controller M100 standard knob	1/8in ext 1.2l N2 40psi SS/SS
FC10SS4S3	Flow controller M100 Spectrol 3-dial	1/8in ext 1.2l N2 40psi SS/SS