

VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]
> CatL#s

> Current System AUD Prices



FC10SS4S4	Flow controller M100 Spectrol 4-dial	1/8in ext 1.2l N2 40psi SS/SS
FC10SS5K	Flow controller M100 standard knob	1/8in ext 4.5l N2 40psi SS/SS
FC10SS5S3	Flow controller M100 Spectrol 3-dial	1/8in ext 4.5l N2 40psi SS/SS
FC10SS5S4	Flow controller M100 Spectrol 4-dial	1/8in ext 4.5l N2 40psi SS/SS
FC10SS6K	Flow controller M100 standard knob	1/8in ext 10.0l N2 40psi SS/SS
FC10SS6S3	Flow controller M100 Spectrol 3-dial	1/8in ext 10.0l N2 40psi SS/SS
FC10SS6S4	Flow controller M100 Spectrol 4-dial	1/8in ext 10.0l N2 40psi SS/SS
FC10SV1K	Flow controller M100 standard knob	1/8in ext 150ml N2 40psi SS/Viton
FC10SV1S3	Flow controller M100 Spectrol 3-dial	1/8in ext 150ml N2 40psi SS/Viton
FC10SV1S4	Flow controller M100 Spectrol 4-dial	1/8in ext 150ml N2 40psi SS/Viton
FC10SV2K	Flow controller M100 standard knob	1/8in ext 250ml N2 40psi SS/Viton
FC10SV2S3	Flow controller M100 Spectrol 3-dial	1/8in ext 250ml N2 40psi SS/Viton
FC10SV2S4	Flow controller M100 Spectrol 4-dial	1/8in ext 250ml N2 40psi SS/Viton
FC10SV3K	Flow controller M100 standard knob	1/8in ext 850ml N2 40psi SS/Viton
FC10SV3S3	Flow controller M100 Spectrol 3-dial	1/8in ext 850ml N2 40psi SS/Viton
FC10SV3S4	Flow controller M100 Spectrol 4-dial	1/8in ext 850ml N2 40psi SS/Viton
FC10SV4K	Flow controller M100 standard knob	1/8in ext 1.2l N2 40psi SS/Viton
FC10SV4S3	Flow controller M100 Spectrol 3-dial	1/8in ext 1.2l N2 40psi SS/Viton
FC10SV4S4	Flow controller M100 Spectrol 4-dial	1/8in ext 1.2l N2 40psi SS/Viton
FC10SV5K	Flow controller M100 standard knob	1/8in ext 4.5l N2 40psi SS/Viton
FC10SV5S3	Flow controller M100 Spectrol 3-dial	1/8in ext 4.5l N2 40psi SS/Viton
FC10SV5S4	Flow controller M100 Spectrol 4-dial	1/8in ext 4.5l N2 40psi SS/Viton
FC10SV6K	Flow controller M100 standard knob	1/8in ext 10.0l N2 40psi SS/Viton
FC10SV6S3	Flow controller M100 Spectrol 3-dial	1/8in ext 10.0l N2 40psi SS/Viton
FC10SV6S4	Flow controller M100 Spectrol 4-dial	1/8in ext 10.0l N2 40psi SS/Viton
FC22AS1K	Flow controller M202 standard knob	1/8in NPT adjustable span Aluminum/SS
FC22AS1S3	Flow controller M202 Spectrol 3-dial	1/8in NPT adjustable span Aluminum/SS
FC22AS1S4	Flow controller M202 Spectrol 4-dial	1/8in NPT adjustable span Aluminum/SS
FC22AV1K	Flow controller M202 standard knob	1/8in NPT adjustable span Aluminum/Viton
FC22AV1S3	Flow controller M202 Spectrol 3-dial	1/8in NPT adjustable span Aluminum/Viton
FC22AV1S4	Flow controller M202 Spectrol 4-dial	1/8in NPT adjustable span Aluminum/Viton
FC22SS1K	Flow controller M202 standard knob	1/8in NPT adjustable span SS/SS
FC22SS1S3	Flow controller M202 Spectrol 3-dial	1/8in NPT adjustable span SS/SS
FC22SS1S4	Flow controller M202 Spectrol 4-dial	1/8in NPT adjustable span SS/SS
FC22SV1K	Flow controller M202 standard knob	1/8in NPT adjustable span SS/Viton
FC22SV1S3	Flow controller M202 Spectrol 3-dial	1/8in NPT adjustable span SS/Viton
FC22SV1S4	Flow controller M202 Spectrol 4-dial	1/8in NPT adjustable span SS/Viton
FC30AS1K	Flow controller M300 standard knob	1/8in ext 200ml N2 40psi Aluminum/SS
FC30AS1S3	Flow controller M300 Spectrol 3-dial	1/8in ext 200ml N2 40psi Aluminum/SS
FC30AS1S4	Flow controller M300 Spectrol 4-dial	1/8in ext 200ml N2 40psi Aluminum/SS
FC30AS2K	Flow controller M300 standard knob	1/8in ext 300ml N2 40psi Aluminum/SS
FC30AS2S3	Flow controller M300 Spectrol 3-dial	1/8in ext 300ml N2 40psi Aluminum/SS
FC30AS2S4	Flow controller M300 Spectrol 4-dial	1/8in ext 300ml N2 40psi Aluminum/SS
FC30AS3K	Flow controller M300 standard knob	1/8in ext 800ml N2 40psi Aluminum/SS
FC30AS3S3	Flow controller M300 Spectrol 3-dial	1/8in ext 800ml N2 40psi Aluminum/SS
FC30AS3S4	Flow controller M300 Spectrol 4-dial	1/8in ext 800ml N2 40psi Aluminum/SS
FC30AS4K	Flow controller M300 standard knob	1/8in ext 1.6l N2 40psi Aluminum/SS
FC30AS4S3	Flow controller M300 Spectrol 3-dial	1/8in ext 1.6l N2 40psi Aluminum/SS
FC30AS4S4	Flow controller M300 Spectrol 4-dial	1/8in ext 1.6l N2 40psi Aluminum/SS
FC30AV1K	Flow controller M300 standard knob	1/8in ext 200ml N2 40psi Aluminum/Viton
FC30AV1S3	Flow controller M300 Spectrol 3-dial	1/8in ext 200ml N2 40psi Aluminum/Viton
FC30AV1S4	Flow controller M300 Spectrol 4-dial	1/8in ext 200ml N2 40psi Aluminum/Viton
FC30AV2K	Flow controller M300 standard knob	1/8in ext 300ml N2 40psi Aluminum/Viton
FC30AV2S3	Flow controller M300 Spectrol 3-dial	1/8in ext 300ml N2 40psi Aluminum/Viton
FC30AV2S4	Flow controller M300 Spectrol 4-dial	1/8in ext 300ml N2 40psi Aluminum/Viton
FC30AV3K	Flow controller M300 standard knob	1/8in ext 800ml N2 40psi Aluminum/Viton
FC30AV3S3	Flow controller M300 Spectrol 3-dial	1/8in ext 800ml N2 40psi Aluminum/Viton
FC30AV3S4	Flow controller M300 Spectrol 4-dial	1/8in ext 800ml N2 40psi Aluminum/Viton
FC30AV4K	Flow controller M300 standard knob	1/8in ext 1.6l N2 40psi Aluminum/Viton
FC30AV4S3	Flow controller M300 Spectrol 3-dial	1/8in ext 1.6l N2 40psi Aluminum/Viton
FC30AV4S4	Flow controller M300 Spectrol 4-dial	1/8in ext 1.6l N2 40psi Aluminum/Viton