

# VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]  
> Cat.#s

> Current System AUD Prices



FC30SS1K	Flow controller M300 standard knob	1/8in ext 200ml N2 40psi SS/SS
FC30SS1S3	Flow controller M300 Spectrol 3-dial	1/8in ext 200ml N2 40psi SS/SS
FC30SS1S4	Flow controller M300 Spectrol 4-dial	1/8in ext 200ml N2 40psi SS/SS
FC30SS2K	Flow controller M300 standard knob	1/8in ext 300ml N2 40psi SS/SS
FC30SS2S3	Flow controller M300 Spectrol 3-dial	1/8in ext 300ml N2 40psi SS/SS
FC30SS2S4	Flow controller M300 Spectrol 4-dial	1/8in ext 300ml N2 40psi SS/SS
FC30SS3K	Flow controller M300 standard knob	1/8in ext 800ml N2 40psi SS/SS
FC30SS3S3	Flow controller M300 Spectrol 3-dial	1/8in ext 800ml N2 40psi SS/SS
FC30SS3S4	Flow controller M300 Spectrol 4-dial	1/8in ext 800ml N2 40psi SS/SS
FC30SS4K	Flow controller M300 standard knob	1/8in ext 1.6l N2 40psi SS/SS
FC30SS4S3	Flow controller M300 Spectrol 3-dial	1/8in ext 1.6l N2 40psi SS/SS
FC30SS4S4	Flow controller M300 Spectrol 4-dial	1/8in ext 1.6l N2 40psi SS/SS
FC30SV1K	Flow controller M300 standard knob	1/8in ext 200ml N2 40psi SS/Viton
FC30SV1S3	Flow controller M300 Spectrol 3-dial	1/8in ext 200ml N2 40psi SS/Viton
FC30SV1S4	Flow controller M300 Spectrol 4-dial	1/8in ext 200ml N2 40psi SS/Viton
FC30SV2K	Flow controller M300 standard knob	1/8in ext 300ml N2 40psi SS/Viton
FC30SV2S3	Flow controller M300 Spectrol 3-dial	1/8in ext 300ml N2 40psi SS/Viton
FC30SV2S4	Flow controller M300 Spectrol 4-dial	1/8in ext 300ml N2 40psi SS/Viton
FC30SV3K	Flow controller M300 standard knob	1/8in ext 800ml N2 40psi SS/Viton
FC30SV3S3	Flow controller M300 Spectrol 3-dial	1/8in ext 800ml N2 40psi SS/Viton
FC30SV3S4	Flow controller M300 Spectrol 4-dial	1/8in ext 800ml N2 40psi SS/Viton
FC30SV4K	Flow controller M300 standard knob	1/8in ext 1.6l N2 40psi SS/Viton
FC30SV4S3	Flow controller M300 Spectrol 3-dial	1/8in ext 1.6l N2 40psi SS/Viton
FC30SV4S4	Flow controller M300 Spectrol 4-dial	1/8in ext 1.6l N2 40psi SS/Viton
FC31AV1	Flow controller M300 screwdriver adjustment	1/8in ext 750ml N2 40psi Aluminium/Viton
FP1Z3M21	Manifold pipe adaptor	one 1/8in F-NPT/three 1/16in 1mm bore SS
FP1Z3M22	Manifold pipe adaptor	one 1/8in F-NPT/three 1/8in 2mm bore SS
FP1Z3M24	Manifold pipe adaptor	one 1/8in F-NPT/three 1/4in 4.6mm bore SS
FP1Z3M41	Manifold pipe adaptor	one 1/4in F-NPT/three 1/16in 1mm bore SS
FP1Z3M42	Manifold pipe adaptor	one 1/4in F-NPT/three 1/8in 2mm bore SS
FP1Z3M44	Manifold pipe adaptor	one 1/4in F-NPT/three 1/4in 4.6mm bore SS
FP2Z3M21	Manifold pipe adaptor	two 1/8in F-NPT/three 1/16in 1mm bore SS
FP2Z3M22	Manifold pipe adaptor	two 1/8in F-NPT/three 1/8in 2mm bore SS
FP2Z3M24	Manifold pipe adaptor	two 1/8in F-NPT/three 1/4in 4.6mm bore SS
FP2Z3M41	Manifold pipe adaptor	two 1/4in F-NPT/three 1/16in 1mm bore SS
FP2Z3M42	Manifold pipe adaptor	two 1/4in F-NPT/three 1/8in 2mm bore SS
FP2Z3M44	Manifold pipe adaptor	two 1/4in F-NPT/three 1/4in 4.6mm bore SS
FPEA22	Female pipe adaptor 1/8in F-NPT x 1/8in ext	2mm bore SS
FPEA24	Female pipe adaptor 1/8in F-NPT x 1/4in ext	4.6mm bore SS
FPEA42	Female pipe adaptor 1/4in F-NPT x 1/8in ext	2mm bore SS
FPEA44	Female pipe adaptor 1/4in F-NPT x 1/4in ext	4.6mm bore SS
FPEA82	Female pipe adaptor 1/2in F-NPT x 1/8in ext	2mm bore SS
FPEA84	Female pipe adaptor 1/2in F-NPT x 1/4in ext	4.6mm bore SS
FPZA21	Female pipe adaptor 1/8in F-NPT x 1/16in int	1mm bore SS
FPZA22	Female pipe adaptor 1/8in F-NPT x 1/8in int	1mm bore SS
FPZA22L	Female pipe adaptor 1/8in F-NPT x 1/8in int	2mm bore SS
FPZA41	Female pipe adaptor 1/4in F-NPT x 1/16in int	1mm bore SS
FPZA42	Female pipe adaptor 1/4in F-NPT x 1/8in int	1mm bore SS
FPZA42L	Female pipe adaptor 1/4in F-NPT x 1/8in int	2mm bore SS
FPZA44L	Female pipe adaptor 1/4in F-NPT x 1/4in int	4.6mm bore SS
FPZA81	Female pipe adaptor 1/2in F-NPT x 1/16in int	1mm bore SS
FPZA82	Female pipe adaptor 1/2in F-NPT x 1/8in int	1mm bore SS
FPZA82L	Female pipe adaptor 1/2in F-NPT x 1/8in int	2mm bore SS
FPZA84L	Female pipe adaptor 1/2in F-NPT x 1/4in int	4.6mm bore SS
FRK1	Ferrule removal kit	
FS.25-5	Fused silica adaptor 1/32in	for tubing .25mm OD Valcon T 5/pkg
FS.25PK-5	Fused silica adaptor 1/32in	for tubing .25mm OD PEEK 5/pkg
FS.25V1-5	Fused silica adaptor 1/32in	for tubing .25mm OD Polyimide Virgin 5/pkg
FS.4-5	Fused silica adaptor 1/32in	for tubing .4mm OD Valcon T 5/pkg
FS.4PK-5	Fused silica adaptor 1/32in	for tubing .4mm OD PEEK 5/pkg
FS.4V1-5	Fused silica adaptor 1/32in	for tubing .4mm OD Polyimide Virgin 5/pkg