

# VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]  
> Cat.#s

> Current System AUD Prices



FSR.25-5	Fused silica adaptor 1/32in	for tubing .25mm OD Polyimide Valcon 5/pkg
FSR.3-5	Fused silica adaptor 1/32in removable	for tubing .3mm OD PolyimideValcon 5/pkg
FSR.4-5	Fused silica adaptor 1/32in	for tubing .4mm OD Polyimide Valcon 5/pkg
FSR.5-5	Fused silica adaptor 1/32in	for tubing .5mm OD Polyimide Valcon 5/pkg
FSZA-HP	Nut self compensating for HP5890/6890	with split/splitless seal disk
FSZN1	Replacement nut for fused silica union	self compensating SS
FSZNA-HP	Nut self compensating for HP5890/6890	SS
F-TCF	Tube connector for air actuator	compressed fitting 1/8 ftg to 10-32 thread
GH-LNR-CIS4-B-5	Reduced breakdown liner Gerstel CIS-4/PTV	Baffled 5/pkg
GH-LNR-DGS4-5	Reduced breakdown liner Agilent/Finnigan	4mm double gooseneck 5/pkg
GH-LNR-GS2-5	Reduced breakdown liner Agilent/Finnigan/Varian CP-1177	2mm gooseneck 5/pkg
GH-LNR-GS4-5	Reduced breakdown liner Agilent/Finnigan/Varian CP-1177	4mm gooseneck 5/pkg
GH-LNR-HP2-5	Reduced breakdown liner Agilent/Finnigan	2mm straight splitless 5/pkg
GH-LNR-HP4-5	Reduced breakdown liner Agilent/Finnigan	4mm straight splitless 5/pkg
GH-LNR-VAR2-5	replaced by GH-LNR-GS2-5	
GH-LNR-VAR3.4-5	Reduced breakdown liner Varian 1078/9	3.4mm gooseneck 5/pkg
GH-LNR-VAR4-5	replaced by GH-LNR-GS4-5	
GH-LNR-VARGS2-5	Reduced breakdown liner Varian 1078/9	2mm gooseneck 5/pkg
HA1-110	Heater assembly for single valve	65W/110Vac
HA1-220	Heater assembly for single valve	65W/220Vac
HA1T-110	Heater assembly for single valve	100W/110Vac
HA1T-220	Heater assembly for single valve	100W/220Vac
HA2-110	Heater assembly for two valves	125W/110Vac
HA2-220	Heater assembly for two valves	125W/220Vac
HA3-110	Heater assembly for three valves	150W/110Vac
HA3-220	Heater assembly for three valves	150W/220Vac
HA6-110	Heater assembly for six valves	300W/110Vac
HA6-220	Heater assembly for six valves	300W/220Vac
HB	Heater block standard for single valve	w/o heater cartridge
HB1N	Heater block for single NW type valve	w/o heater cartridge
HBS	Heater block low mass for single valve	w/o heater cartridge
HCE1-110	Heated column enclosure 1 col. mandrel	4in x4.25in x3.63in d 65W/110Vac
HCE1-220	Heated column enclosure 1 col. mandrel	4in x4.25in x3.63in d 65W/220Vac
HCE2-110	Heated column enclosure 1 col. mandrel	8in x5.25in x4in d 65W/110Vac
HCE2-220	Heated column enclosure 1 col. mandrel	8in x5.25in x4in d 65W/220Vac
HCEB-110	Heated column enclosure 1 col. mandrel	4.25in x5.13in x3.63in d 65W/110Vac
HCEB-220	Heated column enclosure 1 col. mandrel	4.25in x5.13in x3.63in d 65W/220Vac
HCEC-110	Heated column enclosure 1 col. mandrel	8in x8in x6in d 65W/110Vac
HCEC-220	Heated column enclosure 1 col. mandrel	8in x8in x6in d 65W/220Vac
HKS	Hex key set	
HP2-110	Helium purifier Model 2	24VDC input 110/230Vac US power cable
HP2-220	Helium purifier Model 2	24VDC input 110/230Vac EUR power cable
HPM-110	Helium purifier Mini version	24VDC input 110/230Vac US power cable
HPM-220	Helium purifier Mini version	24VDC input 110/230Vac EUR power cable
HSSA	High speed switching assembly for DVI	
HVE2-110	Heated valve enclosure for 2 valves	8in x5.25in x4in 125W/110Vac; Non-CE !!!
HVE2-220	Heated valve enclosure for 2 valves	8in x5.25in x4in 125W/220Vac; Non-CE !!!
HVE3-110	Heated valve enclosure for 3 valves	13.5in x5.75in x4in 150W/110Vac; Non-CE !!!
HVE3-220	Heated valve enclosure for 3 valves	13.5in x5.75in x4in 150W/220Vac; Non-CE !!!
HVE6-110	Heated valve enclosure for 6 valves	13.75in x8in x6in 300W/110Vac; Non-CE !!!
HVE6-220	Heated valve enclosure for 6 valves	13.75in x8in x6in 300W/220Vac; Non-CE !!!
HVEA-110	Heated valve enclosure for 1 valve	4in x4.25in x3.63in 65W/110Vac; Non-CE !!!
HVEA-220	Heated valve enclosure for 1 valve	4in x4.25in x3.63in 65W/220Vac; Non-CE !!!
HVEAN-110	Heated valve enclosure for NW valve	4in x4.25in x3.63in 65W/110Vac Non-CE !!!
HVEAN-220	Heated valve enclosure for NW valve	4in x4.25in x3.63in 65W/220Vac; Non-CE !!!
HVEB-110	Heated valve enclosure for 1 valve	4.25in x5.13in x3.63in 65W/110Vac; Non-CE !!!
HVEB-220	Heated valve enclosure for 1 valve	4.25in x5.13in x3.63in 65W/220Vac; Non-CE !!!
HVEBN-110	Heated valve enclosure for NW valve	4.25in x5.13in x3.63in 65W/110Vac Non-CE !!!
HVEBN-220	Heated valve enclosure for NW valve	4.25in x5.13in x3.63in 65W/220Vac; Non-CE !!!
HVEC-110	Heated valve enclosure for 1 valve	8in x8in x6in 100W/110Vac; Non-CE !!!
HVEC-220	Heated valve enclosure for 1 valve	8in x8in x6in 100W/220Vac; Non-CE !!!