



# VICIValco-Cheminert PRODUCT LIST 2012

HWSC-SC8-6	Screw 8-32 x 3/8in long	counter sunk SS
HWSC-SC8-8B	Screw 8-32 x 1/2in long	counter sunk black oxide SS.
HWSC-SC8-8TDH	Screw 8-32 x 1/2in long	counter sunk turned down head SS
I-21014-01	Thermocouple wire assy	ITC typ in Kin
I-21208-05	Heater cartridge repl. for HVEC	100W/110Vac
I-21208-06	Heater cartridge repl. for HVEC	100W/220Vac
I-21208-32	Heater cartridge for HVEA/HVEB	65W/120Vac
I-21208-33	Heater cartridge repl. for HVEA/HVEB	65W/220Vac
I-22239	Interface cable DVI/SVI	
I-22697	Interface cable RS-232 6 feet	for 2-pos/mpos micro electric actuator
I-22897-02	Interface cable RS-232 2 output	for 2-pos/mpos micro electric actuator
I-22897-03	Interface cable RS-232 3 output	for 2-pos/mpos micro electric actuator
I-22897-04	Interface cable RS-232 4 output	for 2-pos/mpos micro electric actuator
I-22897-05	Interface cable RS-232 5 output	for 2-pos/mpos micro electric actuator
I-22897-06	Interface cable RS-232 6 output	for 2-pos/mpos micro electric actuator
I-22897-08	Interface cable RS-232 8 output	for 2-pos/mpos micro electric actuator
I-23572HP2	Getter assembly replacement for HP2	helium purifier
I-23572NP2	Getter assembly replacement for NP2	nitrogen purifier
I4UWE.2	4 port 2-pos int vol valve manual	1/8 x .75mm 175C/1000psi liq .2ul N60/E
I4UWE.5	4 port 2-pos int vol valve manual	1/8 x .75mm 175C/1000psi liq .5ul N60/E
I4UWE1	4 port 2-pos int vol valve manual	1/8 x .75mm 175C/1000psi liq 1ul N60/E
I4UWE2	4 port 2-pos int vol valve manual	1/8 x .75mm 175C/1000psi liq 2ul N60/E
ITC10399-110	Instrumentation temperature controller	0-399 deg. C 10A/110Vac
ITC10399-220	Instrumentation temperature controller	0-399 deg. C 10A/220Vac
IZERA1.5	Int./Ext. reducer/adaptor 1/16in x 1/32in	1mm bore SS
IZERA1.5C	Int./Ext. reducer/adaptor 1/16in x 1/32in	.25mm bore SS
IZERA1.5M	Int./Ext. reducer/adaptor 1/16in x 1/32in	.5mm bore SS
IZR1.5	Internal reducer 1/16in x 1/32in	.25mm bore SS
IZR1.5F	Internal reducer 1/16in x 1/32in	.25mm bore 2 um frit SS
IZR1.5L	Internal reducer 1/16in x 1/32in	.50mm bore SS
IZR1.5LF	Internal reducer 1/16in x 1/32in	.50mm bore 2 um frit SS
IZR1.5T	Internal reducer 1/16in x 1/32in	1/32in through bore SS
IZR21	Internal reducer 1/8in x 1/16in	.50mm bore SS
IZR21C	Internal reducer 1/8in x 1/16in	.25mm bore SS
IZR21CF	Internal reducer 1/8in x 1/16in	.25mm bore 2 um frit SS
IZR21F	Internal reducer 1/8in x 1/16in	.50mm bore 2 um frit SS
IZR21L	Internal reducer 1/8in x 1/16in	1mm bore SS
IZR21LF	Internal reducer 1/8in x 1/16in	1mm bore 2 um frit SS
IZR21T	Internal reducer 1/8in x 1/16in	1/16 trough bore SS
IZR41	Internal reducer 1/4in x 1/16in	1mm bore SS
IZR41F	Internal reducer 1/4in x 1/16in	1mm bore 2 um frit SS
IZR42	Internal reducer 1/4in x 1/8in	1mm bore SS
IZR42F	Internal reducer 1/4in x 1/8in	1mm bore 2 um frit SS
IZR42L	Internal reducer 1/4in x 1/8in	2mm bore SS
IZR42LF	Internal reducer 1/4in x 1/8in	2mm bore 2 um frit SS
JR-201540	Easy-Flange kit in plastic case	
JR-26501	Coupler PEEK universal 0.13 mm ID red	
JR-26502	Coupler PEEK universal 0.17 mm ID yellow	
JR-26503	Coupler PEEK universal 0.25 mm ID blue	
JR-26504	Coupler PEEK universal 0.50 mm ID orange	
JR-32178	Filter PE mobile phase No-Met 20 um 1/8"	
JR-32179	Filter PE mobile phase replacement No-Met 20 um	
JR-357090-5	Tubing Elbow 90° 5/pkg	
JR-357180-5	Tubing Elbow 180° 5/pkg	
JR-35P	PEEK Starter Kit	
JR-367008-10	Filter SS mobile phase 10 um	fittings for 1/8" tubing
JR-367008-2	Filter SS mobile phase 2 um	fittings for 1/8" tubing
JR-367008-20	Filter SS mobile phase 20 um	fittings for 1/8" tubing
JR-367016-10	Filter SS mobile phase 10 um	fittings for 1/16" tubing
JR-367016-2	Filter SS mobile phase 2 um	fittings for 1/16" tubing
JR-367016-20	Filter SS mobile phase 20 um	fittings for 1/16" tubing