

VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]
> Cat.#s

> Current System AUD Prices



JR-TD-6007-M25	Tubing Dual Layer PEEK 1/16" x 0.13 mm ID	solid red outside natural inside 25m/pkg
JR-TD-6007-M3	Tubing Dual Layer PEEK 1/16" x 0.13 mm ID	solid red outside natural inside 3m/pkg
JR-TD-6008-M10	Tubing Dual Layer PEEK 1/16" x 0.18 mm ID	solid yellow outside natural inside 10m/pkg
JR-TD-6008-M25	Tubing Dual Layer PEEK 1/16" x 0.18 mm ID	solid yellow outside natural inside 25m/pkg
JR-TD-6008-M3	Tubing Dual Layer PEEK 1/16" x 0.18 mm ID	solid yellow outside natural inside 3m/pkg
JR-TD-6009-M10	Tubing Dual Layer PEEK 1/16" x 0.25 mm ID	solid blue outside natural inside 10m/pkg
JR-TD-6009-M25	Tubing Dual Layer PEEK 1/16" x 0.25 mm ID	solid blue outside natural inside 25m/pkg
JR-TD-6009-M3	Tubing Dual Layer PEEK 1/16" x 0.25 mm ID	solid blue outside natural inside 3m/pkg
JR-TD-6010-M10	Tubing Dual Layer PEEK 1/16" x 0.50 mm ID	solid orange outside natural inside 10m/pkg
JR-TD-6010-M25	Tubing Dual Layer PEEK 1/16" x 0.50 mm ID	solid orange outside natural inside 25m/pkg
JR-TD-6010-M3	Tubing Dual Layer PEEK 1/16" x 0.50 mm ID	solid orange outside natural inside 3m/pkg
JR-TD-6011-M10	Tubing Dual Layer PEEK 1/16" x 0.75 mm ID	solid green outside natural inside 10m/pkg
JR-TD-6011-M25	Tubing Dual Layer PEEK 1/16" x 0.75 mm ID	solid green outside natural inside 25m/pkg
JR-TD-6011-M3	Tubing Dual Layer PEEK 1/16" x 0.75 mm ID	solid green outside natural inside 3m/pkg
L4UW	!!! RECOMMEND 2L4UW	SUPPLIED WITH LARGER HANDLE
L6UW	!!! RECOMMEND 2L6UW	SUPPLIED WITH LARGER HANDLE
L8UW	!!! RECOMMEND 2L8UW	SUPPLIED WITH LARGER HANDLE
LZCN1-10	Counter bored nut 1/16in long	SS 10/pkg
LZN.5-10	Nut 1/32in 11mm long SS 10/pkg	
LZN.5FPK-10	Nut 1/32in fingertight 13.7mm long	PEEK 10/pkg
LZN1-10	Nut 1/16in 19mm long SS 10/pkg	
LZN1PK-10	Nut 1/16in hex 22mm long	PEEK 10/pkg
LZN2-10	Nut 1/8in 21mm long SS 10/pkg	
LZN4-10	Nut 1/4in 28mm long SS 10/pkg	
LZNF1KF-5	Nut 1/16in No Twist hex long PEEK	with CTFE ferrule 5/pkg
LZNF1PK-5	Nut 1/16in No Twist hex long PEEK	with PEEK ferrule 5/pkg
LZNF1PKG-5	Nut 1/16in No Twist hex long PEEK	with glass-filled PEEK ferrule 5/pkg
LZP.5FPK	Plug 1/32in fingertight PEEK	
LZP1	Plug 1/16in 19mm long	SS
LZP1H	Plug 1/16in 19mm long high pressure	SS
LZP1PK	Plug 1/16in long hex PEEK	
LZP2	Plug 1/8in 21mm long	SS
LZP2H	Plug 1/8in 21mm long high pressure	SS
MRX.5PK	Micro volume replacement ring 1/32in	for union tee cross PEEK
MRX.5S6	Micro volume replacement ring 1/32in	for union tee cross 316SS
MRX1PK	Micro volume replacement ring 1/16in	for union tee cross PEEK
MRX1S6	Micro volume replacement ring 1/16in	for union tee cross 316SS
MRY.5PK	Micro volume replacement ring 1/32in	for Y PEEK
MRY.5S6	Micro volume replacement ring 1/32in	for Y 316SS
MRY1PK	Micro volume replacement ring 1/16in	for Y PEEK
MRY1S6	Micro volume replacement ring 1/16in	for Y 316SS
MS-P100-1	Helium Purifier	1/8in brass caps
MS-P100-2	Helium Purifier	1/4in brass caps
MS-P200-1	Hydrogen Purifier	1/8in brass caps
MS-P200-2	Hydrogen Purifier	1/4in brass caps
MS-P300-1	Nitrogen Purifier	1/8in brass caps
MS-P300-2	Nitrogen Purifier	1/4in brass caps
MS-P310-1	Nitrogen Purifier for LC/MS applications	1/8in brass caps
MS-P310-2	Nitrogen Purifier for LC/MS applications	1/4in brass caps
MS-P350-1	Nitrogen Purifier for nitrogen generators	1/8in brass caps
MS-P350-2	Nitrogen Purifier for nitrogen generators	1/4in brass caps
MS-P400-1	Air Purifier	1/8in brass caps
MS-P400-2	Air Purifier	1/4in brass caps
MS-P500-1	Methane Purifier/CI	1/8in brass caps
MS-P500-2	Methane Purifier/CI	1/4in brass caps
MS-P600-1	Carbon dioxide	1/8in brass caps
MS-P600-2	Carbon dioxide	1/4in brass caps
MS-P700-1	CO2 Purifier	1/8in brass caps
MS-P700-2	CO2 Purifier	1/4in brass caps
MS-T100-1	Moisture Trap	1/8in brass caps
MS-T100-2	Moisture Trap	1/4in brass caps