

VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]
> Cat.#s

> Current System AUD Prices



| | | |
|------------|---|--|
| MX.5XCKF | Micro volume cross-assy 1/32in | .15mm bore CTFE |
| MX.5XCPK | Micro volume cross-assy 1/32in | .15mm bore PEEK |
| MX.5XCS6 | Micro volume cross-assy 1/32in | .15mm bore 316SS |
| MX.5XCTI | Micro volume cross-assy 1/32in | .15mm bore Titanium |
| MX1CHC | Micro volume cross-assy 1/16in | .25mm bore HC |
| MX1CKF | Micro volume cross-assy 1/16in | .25mm bore CTFE |
| MX1CPK | Micro volume cross-assy 1/16in | .25mm bore PEEK |
| MX1CS6 | Micro volume cross-assy 1/16in | .25mm bore 316SS |
| MX1CTI | Micro volume cross-assy 1/16in | .25mm bore Titanium |
| MX1XCHC | Micro volume cross-assy 1/16in | .15mm bore HC |
| MX1XCKF | Micro volume cross-assy 1/16in | .15mm bore CTFE |
| MX1XCPK | Micro volume cross-assy 1/16in | .15mm bore PEEK |
| MX1XCS6 | Micro volume cross-assy 1/16in | .15mm bore 316SS |
| MX1XCTI | Micro volume cross-assy 1/16in | .15mm bore Titanium |
| MY.5CHC | Micro volume Y-assy 1/32in | .25mm bore HC |
| MY.5CKF | Micro volume Y-assy 1/32in | .25mm bore CTFE |
| MY.5CPK | Micro volume Y-assy 1/32in | .25mm bore PEEK |
| MY.5CS6 | Micro volume Y-assy 1/32in | .25mm bore 316SS |
| MY.5CTI | Micro volume Y-assy 1/32in | .25mm bore Titanium |
| MY.5XCHC | Micro volume Y-assy 1/32in | .15mm bore HC |
| MY.5XCKF | Micro volume Y-assy 1/32in | .15mm bore CTFE |
| MY.5XCPK | Micro volume Y-assy 1/32in | .15mm bore PEEK |
| MY.5XCS6 | Micro volume Y-assy 1/32in | .15mm bore 316SS |
| MY.5XCTI | Micro volume Y-assy 1/32in | .15mm bore Titanium |
| MY1CHC | Micro volume Y-assy 1/16in | .25mm bore HC |
| MY1CKF | Micro volume Y-assy 1/16in | .25mm bore CTFE |
| MY1CPK | Micro volume Y-assy 1/16in | .25mm bore PEEK |
| MY1CS6 | Micro volume Y-assy 1/16in | .25mm bore 316SS |
| MY1CTI | Micro volume Y-assy 1/16in | .25mm bore Titanium |
| MY1XCHC | Micro volume Y-assy 1/16in | .15mm bore HC |
| MY1XCKF | Micro volume Y-assy 1/16in | .15mm bore CTFE |
| MY1XCPK | Micro volume Y-assy 1/16in | .15mm bore PEEK |
| MY1XCS6 | Micro volume Y-assy 1/16in | .15mm bore 316SS |
| MY1XCTI | Micro volume Y-assy 1/16in | .15mm bore Titanium |
| MZN1-10 | Nut 1/16in 13mm long SS 10/pkg | |
| MZN1PK-10 | Nut 1/16in hex 15.7mm long | PEEK 10/pkg |
| MZNF1KF-5 | Nut 1/16in No Twist hex medium PEEK | with CTFE ferrule 5/pkg |
| MZNF1PK-5 | Nut 1/16in No Twist hex medium PEEK | with PEEK ferrule 5/pkg |
| MZNF1PKG-5 | Nut 1/16in No Twist hex medium PEEK | with glass-filled PEEK ferrule 5/pkg |
| MZP1PK | Plug 1/16in hex PEEK | |
| NP2-110 | Nitrogen purifier Model 2 | 24VDC input 110/230Vac US power cable |
| NP2-220 | Nitrogen purifier Model 2 | 24VDC input 110/230Vac EUR power cable |
| NPM-110 | Nitrogen purifier Mini version | 24VDC input 110/230Vac US power cable |
| NPM-220 | Nitrogen purifier Mini version | 24VDC input 110/230Vac EUR power cable |
| OEW-1 | Open end wrench 3/16in x1/4in | for 1/32in and 1/16in fittings |
| OEW-2 | Open end wrench 3/8in x7/16in | for 1/8in fittings |
| OEW-3 | Open end wrench 1/2in x9/16in | for 1/4in fittings |
| OR | O-ring set incl. lubricant | standard 2-pos air actuator |
| ORMP | O-ring set incl. lubricant | standard mpos air actuator |
| ORT | O-ring set incl. lubricant | high temperature 2-pos air actuator |
| ORTMP | O-ring set incl. lubricant | high temperature mpos air actuator |
| PCL412 | Precolumn 1/4in x 2cm 4.6mm ID | incl. insert nut and ferrule 2um frit SS |
| PCL415 | Precolumn 1/4in x 5cm 4.6mm ID | incl. insert nut and ferrule 2um frit SS |
| PCS412F | Precolumn system 1/4in x 2cm | incl. insert body and 2um frit SS |
| PCS415F | Precolumn system 1/4in x 5cm | incl. insert body and 2um frit SS |
| PEA22 | Male pipe adaptor 1/8in M-NPT x 1/8in ext | 2mm bore SS |
| PEA24 | Male pipe adaptor 1/8in M-NPT x 1/4in ext | 4.6mm bore SS |
| PEA42 | Male pipe adaptor 1/4in M-NPT x 1/8in ext | 2mm bore SS |
| PEA44 | Male pipe adaptor 1/4in M-NPT x 1/4in ext | 4.6mm bore SS |
| PEA82 | Male pipe adaptor 1/2in M-NPT x 1/8in ext | 2mm bore SS |
| PEA84 | Male pipe adaptor 1/2in M-NPT x 1/4in ext | 4.6mm bore SS |