

# VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]  
> Cat.#s

> Current System AUD Prices



PFAF	Position feedback adapter	for air actuator
PFC2	Position feedback	Cheminert C2 and C3 series 6/10 port
PFC4	Position feedback	to flat plate valve C4
PFW36	Position feedback for 2-pos manual valve	W type 8 and 10 port 36 deg
PFW60	Position feedback for 2-pos manual valve	W type 6 port and int. 4 port 60 deg
PFW90	Position feedback for 2-pos manual valve	W type 4 port 90 deg
PM	Pencil magnet	for W and UW rotor seals
PR50A15E2	Combo pressure regulator 0-15psi	1/8in ext Aluminum/SS
PR50A15Z1	Combo pressure regulator 0-15psi	1/16in int Aluminum/SS
PR50A15Z2	Combo pressure regulator 0-15psi	1/8in int Aluminum/SS
PR50A30E2	Combo pressure regulator 0-30psi	1/8in ext Aluminum/SS
PR50A30Z1	Combo pressure regulator 0-30psi	1/16in int Aluminum/SS
PR50A30Z2	Combo pressure regulator 0-30psi	1/8in int Aluminium/SS
PR50A60E2	Combo pressure regulator 0-60psi	1/8in ext Aluminum/SS
PR50A60Z1	Combo pressure regulator 0-60psi	1/16in int Aluminum/SS
PR50A60Z2	Combo pressure regulator 0-60psi	1/8in int Aluminium/SS
PS-050023	Gas syringe A-2 25 ul	RN .028in x.005in x2in bevel open end
PS-050024	Gas syringe A-2 50 ul	RN .029in x.005in x2in bevel open end
PS-050025	Gas syringe A-2 100 ul	RN .028in x.005in x2in bevel open end
PS-050031	Gas syringe A-2 250 ul	RN .029in x.012in x2in bevel open end
PS-050032	Gas syringe A-2 500 ul	RN .029in x.012in x2in bevel open end
PS-050033	Gas syringe A-2 1 ml	RN .029in x.012in x2in bevel open end
PS-050034	Gas syringe A-2 2 ml	RN .029in x.012in x2in bevel open end
PS-050035	Gas syringe A-2 5 ml	RN .029in x.012in x2in bevel open end
PS-050036	Gas syringe A-2 10 ml	RN .029in x.012in x2in bevel open end
PS-050043	Gas syringe A-2 25 ul	RN .028in x.005in x2in bevel open end Luer
PS-050044	Gas syringe A-2 50 ul	RN .028in x.005in x2in bevel open end Luer
PS-050045	Gas syringe A-2 100 ul	RN .028in x.005in x2in bevel open end Luer
PS-050051	Gas syringe A-2 250 ul	RN .029in x.012in x2in bevel open end Luer
PS-050052	Gas syringe A-2 500 ul	RN .029in x.012in x2in bevel open end Luer
PS-050053	Gas syringe A-2 1 ml	RN .029in x.012in x2in bevel open end Luer
PS-050054	Gas syringe A-2 2 ml	RN .029in x.012in x2in bevel open end Luer
PS-050055	Gas syringe A-2 5 ml	RN .029in x.012in x2in bevel open end Luer
PS-050056	Gas syringe A-2 10 ml	RN .029in x.012in x2in bevel open end Luer
PS-123050	Needles removable C-160 CG-130	.019in x.005in x2.25in bevel open end 3/pkg
PS-123050R	Needles removable C-160	22GAx2in blunt tip open end V/C/Rh 3/pkg
PS-160021	Liquid syringe C-160 5 ul	FN .019in x.005in x2in bevel open end
PS-160021R	Liquid syringe C-160 5 ul	FN 22GAx2in blunt tip open end V/C/Rh
PS-160022	Liquid syringe C-160 10 ul	FN .019in x.005in x2in bevel open end
PS-160022R	Liquid syringe C-160 10 ul	FN 22GAx2in blunt tip open end V/C/Rh
PS-160023	Liquid syringe C-160 25 ul	FN .019in x.005in x2in bevel open end
PS-160023R	Liquid syringe C-160 25 ul	FN 22GAx2in blunt tip open end V/C/Rh
PS-160024	Liquid syringe C-160 50 ul	FN .019in x.005in x2in bevel open end
PS-160024R	Liquid syringe C-160 50 ul	FN 22GAx2in blunt tip open end V/C/Rh
PS-160025	Liquid syringe C-160 100 ul	FN 019in x.005in x2in bevel open end
PS-160025R	Liquid syringe C-160 100 ul	FN 22GAx2in blunt tip open end V/C/Rh
PS-160221	Liquid syringe C-160 5 ul	RN .019in x.005in x2.25in bevel open end
PS-160221R	Liquid syringe C-160 5 ul	RN 22GAx2in blunt tip open end V/C/Rh
PS-160222	Liquid syringe C-160 10 ul	RN .019in x.005in x2.25in bevel open end
PS-160222R	Liquid syringe C-160 10 ul	RN 22GAx2in blunt tip open end V/C/Rh
PS-160223	Liquid syringe C-160 25 ul	RN .019in x.005in x2.25in bevel open end
PS-160223R	Liquid syringe C-160 25 ul	RN 22GAx2in blunt tip open end V/C/Rh
PS-160224	Liquid syringe C-160 50 ul	RN .019in x.005in x2.25in bevel open end
PS-160224R	Liquid syringe C-160 50 ul	RN 22GAx2in blunt tip open end V/C/Rh
PS-160225	Liquid syringe C-160 100 ul	RN .019in x.005in x2.25in bevel open end
PS-160225R	Liquid syringe C-160 100 ul	RN 22GAx2in blunt tip open end V/C/Rh
PS-614158	Mininert valve 13mm-425 12/pkg	
PS-614160	Mininert valve 15mm-425 12/pkg	
PS-614161	Mininert valve 18mm-400 12/pkg	
PS-614163	Mininert valve 24mm-400 12/pkg	
PS-614170	Mininert valve 20mm-400 12/pkg	