



# VICIValco-Cheminert PRODUCT LIST 2012

PS-614250	Mininert valve crimp-top 12/pkg	for 13 mm ID glassware
PS-631201	Mininert valve termination	1/4in -28 male to Mininert
PS-631202	Mininert valve termination	1/8in male NPT to Mininert
PS-631203	Mininert valve termination	1/4in -28 female to Mininert
PS-631204	Mininert valve termination	1/8in female NPT to Mininert
PS-631205	Mininert valve in-line	1/4in -28 male to 1/4in -28 male
PS-644350	Mininert needle seal septa 50/pkg	
PS-644850	Septum installation tool	
PS-654050	Mininert syringe valve	for C or D syringe
PS-654051	Mininert syringe valve	for luer-tip
PS-660100	Valve 3-port manual T-flow w/o nutsferrules	200psi .06" bore 1/4-28 fitting detail
PS-660110	Valve 4-port manual T-flow w/o nutsferrules	200psi .06" bore 1/4-28 fitting detail
PS-660200	Valve 2-port manual 180-flow w/o nutsferrules	200psi .06" bore 1/4-28 fitting detail
PS-660210	Valve 4-port manual 180-flow w/o nutsferrules	200psi .06" bore 1/4-28 fitting detail
PS-660300	Valve 2-port manual 90-flow w/o nutsferrules	200psi .06" bore 1/4-28 fitting detail
PS-660310	Valve 3-port manual 90-flow w/o nutsferrules	200psi .06" bore 1/4-28 fitting detail
PS-660320	Valve 4-port manual 90-flow w/o nutsferrules	200psi .06" bore 1/4-28 fitting detail
PS-943050	Needles RN p-lok A-2 C	.028in x.005in x2in bevel open end 3/pkg
PS-943051	Needles RN p-lok A-2 C D	.029in x.012in x2in bevel open end 3/pkg
PS-943052	Needles RN p-lok A-2 C D	.029in x.012in x2in side-port taper 3/pkg
PS-943060	Needles RN luer A-2 C Magnum	.028in x.006in x2in bevel open end 3/pkg
PS-943061	Needles RN luer A-2 D	.028in x.012in x2in bevel open end 3/pkg
PS-943062	Needles RN luer A-2 C D Magnum	.028in x.012in x2in side port taper 3/pkg
PV	Pin vise and drill index .34-1mm	
PZA21	Male pipe adaptor 1/8in M-NPT x 1/16in int	1mm bore SS
PZA21T	Male pipe adaptor 1/8in M-NPT x 1/16in int	1/16in trough bore SS
PZA22	Male pipe adaptor 1/8in M-NPT x 1/8in int	1mm bore SS
PZA41	Male pipe adaptor 1/4in M-NPT x 1/16in int	1mm bore SS
PZA42	Male pipe adaptor 1/4in M-NPT x 1/8in int	1mm bore SS
PZA42L	Male pipe adaptor 1/4in M-NPT x 1/8in int	2mm bore SS
PZA44L	Male pipe adaptor 1/4in M-NPT x 1/4in int	4.6mm bore SS
PZA81	Male pipe adaptor 1/2in M-NPT x 1/16in int	1mm bore SS
PZA82	Male pipe adaptor 1/2in M-NPT x 1/8in int	1mm bore SS
PZA82L	Male pipe adaptor 1/2in M-NPT x 1/8in int	2mm bore SS
PZA84L	Male pipe adaptor 1/2in M-NPT x 1/4in int	4.6mm bore SS
RAD	Right angle drive close mount	
RF1.5KF-5	Standard reducing ferrule 1/16in x 1/32in	CTFE 5/pkg
RF1.5PK-5	Standard reducing ferrule 1/16in x 1/32in	PEEK 5/pkg
RF1.5TFG-5	Standard reducing ferrule 1/16in x 1/32in	PTFE Glass-filled 25% 5/pkg
RF1.5V-5	Standard reducing ferrule 1/16in x 1/32in	Polyimide Valcon 5/pkg
RF2.5KF-5	Standard reducing ferrule 1/8in x 1/32in	CTFE 5/pkg
RF2.5PK-5	Standard reducing ferrule 1/8in x 1/32in	PEEK 5/pkg
RF2.5TFG-5	Standard reducing ferrule 1/8in x 1/32in	PTFE Glass-filled 25% 5/pkg
RF2.5V-5	Standard reducing ferrule 1/8in x 1/32in	Polyimide Valcon 5/pkg
RF21KF-5	Standard reducing ferrule 1/8in x 1/16in	CTFE 5/pkg
RF21PK-5	Standard reducing ferrule 1/8in x 1/16in	PEEK 5/pkg
RF21TFG-5	Standard reducing ferrule 1/8in x 1/16in	PTFE Glass-filled 25% 5/pkg
RF21V-5	Standard reducing ferrule 1/8in x 1/16in	Polyimide Valcon 5/pkg
RF41KF-5	Standard reducing ferrule 1/4in x 1/16in	CTFE 5/pkg
RF41PK-5	Standard reducing ferrule 1/4in x 1/16in	PEEK 5/pkg
RF41TFG-5	Standard reducing ferrule 1/4in x 1/16in	PTFE Glass-filled 25% 5/pkg
RF41V-5	Standard reducing ferrule 1/4in x 1/16in	Polyimide Valcon 5/pkg
RF42KF-5	Standard reducing ferrule 1/4in x 1/8in	CTFE 5/pkg
RF42PK-5	Standard reducing ferrule 1/4in x 1/8in	PEEK 5/pkg
RF42TFG-5	Standard reducing ferrule 1/4in x 1/8in	PTFE Glass-filled 25% 5/pkg
RF42V-5	Standard reducing ferrule 1/4in x 1/8in	Polyimide Valcon 5/pkg
SD4UW	4 mpos dead-end path manual	1/8 x .75mm 75C/5000psi liq N60/E
SD6UW	6 mpos dead-end path manual	1/8 x .75mm 75C/5000psi liq N60/E
SD8UW	8 mpos dead-end path manual	1/8 x .75mm 75C/5000psi liq N60/E
SEAL1-HP	Seal disk split/splitless for HP5890	SS
SFV	Prime/Purge valve manual	3 x 1/16in .50 mm bore 100C/10'000psi SS