

VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]
> Cat.#s

> Current System AUD Prices



SFVL	Prime/Purge valve manual	3 x 1/16in .75 mm bore 100C/10'000psi SS
SFVO	On/Off valve manual	2 x 1/16in .50 mm bore 100C/10'000psi SS
SFVOHT	On/Off valve manual high temperature/pressure	2 x 1/16in .50 mm bore 300C/6000psi SS
SFVOHT4	On/Off valve manual high temp/pressure/4in so	2 x 1/16in .50 mm bore 100C/10'000psi SS
SFVOL	On/Off valve manual	2 x 1/16in .75 mm bore 100C/10'000psi SS
SI4G	Replacement septa for septum injector 350C	1/4in OD low bleed 10/pkg
SL100CSTP	Sample loop 100ul mpos ST/MW P-type valve	1/16in ends with nuts & ferrules 316SS
SL100CSTUW	Sample loop 100ul mpos ST UW-type valve	1/16in ends with nuts & ferrules 316SS
SL100CUW	Sample loop 100ul UW type valve	1/16in ends with nuts & ferrules 316SS
SL100CW	Sample loop 100ul W type valve	1/16in ends with nuts & ferrules SS
SL100NW	Sample loop 100ul W type valve	1/32in ends with nuts & ferrules 316SS
SL100STP	Sample loop 100ul mpos ST/MW P-type valve	1/8in ends with nuts & ferrules 316SS
SL100UW	Sample loop 100ul UW type valve	1/8in ends with nuts & ferrules 316SS
SL10CSTUW	Sample loop 10ul mpos ST UW-type valve	1/16in ends with nuts & ferrules 316SS
SL10CUW	Sample loop 10ul UW type valve	1/16in ends with nuts & ferrules 316SS
SL10CW	Sample loop 10ul W type valve	1/16in ends with nuts & ferrules 316SS
SL10KCSTP	Sample loop 10ml mpos ST/MW P-type valve	1/16in ends with nuts & ferrules 316SS
SL10KCSTUW	Sample loop 10ml mpos ST UW-type valve	1/16in ends with nuts & ferrules 316SS
SL10KCUW	Sample loop 10ml UW type valve	1/16in ends with nuts & ferrules 316SS
SL10KCW	Sample loop 10ml W type valve	1/16in ends with nuts & ferrules 316SS
SL10KSTP	Sample loop 10ml mpos ST/MW P-type valve	1/8in ends with nuts & ferrules 316SS
SL10KUW	Sample loop 10ml UW type valve	1/8in ends with nuts & ferrules 316SS
SL10NW	Sample loop 10ul W type valve	1/32in ends with nuts & ferrules 316SS
SL10UW	Sample loop 10ul UW type valve	1/8in ends with nuts & ferrules 316SS
SL15CSTUW	Sample loop 15ul mpos ST UW-type valve	1/16in ends with nuts & ferrules 316SS
SL15CUW	Sample loop 15ul UW type valve	1/16in ends with nuts & ferrules 316SS
SL15CW	Sample loop 15ul W type valve	1/16in ends with nuts & ferrules 316SS
SL15NW	Sample loop 15ul W type valve	1/32in ends with nuts & ferrules 316SS
SL15UW	Sample loop 15ul UW type valve	1/8in ends with nuts & ferrules 316SS
SL1KCSTP	Sample loop 1ml mpos ST/MT P-type valve	1/16in ends with nuts & ferrules 316SS
SL1KCSTUW	Sample loop 1ml mpos ST UW-type valve	1/16in ends with nuts & ferrules 316SS
SL1KCUW	Sample loop 1ml UW type valve	1/16in ends with nuts & ferrules 316SS
SL1KCW	Sample loop 1ml W type valve	1/16in ends with nuts & ferrules 316SS
SL1KSTP	Sample loop 1ml mpos ST/MW P-type valve	1/8in ends with nuts & ferrules 316SS
SL1KUW	Sample loop 1ml UW type valve	1/8in ends with nuts & ferrules 316SS
SL20CSTUW	Sample loop 20ul mpos ST UW-type valve	1/16in ends with nuts & ferrules 316SS
SL20CUW	Sample loop 20ul UW type valve	1/16in ends with nuts & ferrules 316SS
SL20CW	Sample loop 20ul W type valve	1/16in ends with nuts & ferrules 316SS
SL20KUW	Sample loop 20 ml UW type valve	1/8in ends with nuts & ferrules 316SS
SL20NW	Sample loop 20ul W type valve	1/32in ends with nuts & ferrules 316SS
SL20UW	Sample loop 20ul UW type valve	1/8in ends with nuts & ferrules 316SS
SL250CSTP	Sample loop 250ul mpos ST/MW P-type valve	1/16in ends with nuts & ferrules 316SS
SL250CSTUW	Sample loop 250ul mpos ST UW-type valve	1/16in ends with nuts & ferrules 316SS
SL250CUW	Sample loop 250ul UW type valve	1/16in ends with nuts & ferrules 316SS
SL250CW	Sample loop 250ul W type valve	1/16in ends with nuts & ferrules 316SS
SL250NW	Sample loop 250ul W type valve	1/32in ends with nuts & ferrules 316SS
SL250STP	Sample loop 250ul mpos ST/MW P-type valve	1/8in ends with nuts & ferrules 316SS
SL250UW	Sample loop 250ul UW type valve	1/8in ends with nuts & ferrules 316SS
SL25CSTUW	Sample loop 25ul mpos ST UW-type valve	1/16in ends with nuts & ferrules 316SS
SL25CUW	Sample loop 25ul UW type valve	1/16in ends with nuts & ferrules 316SS
SL25CW	Sample loop 25ul W type valve	1/16in ends with nuts & ferrules 316SS
SL25NW	Sample loop 25ul W type valve	1/32in ends with nuts & ferrules 316SS
SL25UW	Sample loop 25ul UW type valve	1/8in ends with nuts & ferrules 316SS
SL2CW	Sample loop 2ul W type valve	1/16in ends with nuts & ferrules 316SS
SL2KCSTP	Sample loop 2ml mpos ST/MW P-type valve	1/16in ends with nuts & ferrules 316SS
SL2KCSTUW	Sample loop 2ml mpos ST UW-type valve	1/16in ends with nuts & ferrules 316SS
SL2KCUW	Sample loop 2ml UW type valve	1/16in ends with nuts & ferrules 316SS
SL2KCW	Sample loop 2ml W type valve	1/16in ends with nuts & ferrules 316SS
SL2KSTP	Sample loop 2ml mpos ST/MW P-type valve	1/8in ends with nuts & ferrules 316SS
SL2KUW	Sample loop 2ml UW type valve	1/8in ends with nuts & ferrules 316SS
SL2NW	Sample loop 2ul W type valve	1/32in ends with nuts & ferrules 316SS