

# VICI Valco-Cheminert PRODUCT LIST 2012

[Ctrl F]  
> Cat.#s

> Current System AUD Prices



|            |   |  |
|------------|---|--|
| SL3CUW     | Sample loop 3ul UW type valve             | 1/16in ends with nuts & ferrules 316SS |
| SL500CSTP  | Sample loop 500ul mpos ST/MW P-type valve | 1/16in ends with nuts & ferrules 316SS |
| SL500CSTUW | Sample loop 500ul mpos ST UW-type valve   | 1/16in ends with nuts & ferrules 316SS |
| SL500CUW   | Sample loop 500ul UW type valve           | 1/16in ends with nuts & ferrules 316SS |
| SL500CW    | Sample loop 500ul W type valve            | 1/16in ends with nuts & ferrules 316SS |
| SL500NW    | Sample loop 500ul W type valve            | 1/32in ends with nuts & ferrules 316SS |
| SL500STP   | Sample loop 500ul mpos ST/MW P-type valve | 1/8in ends with nuts & ferrules 316SS  |
| SL500UW    | Sample loop 500ul UW type valve           | 1/8in ends with nuts & ferrules 316SS  |
| SL50CSTP   | Sample loop 50ul mpos ST/MW P-type valve  | 1/16in ends with nuts & ferrules 316SS |
| SL50CSTUW  | Sample loop 50ul mpos ST UW-type valve    | 1/16in ends with nuts & ferrules 316SS |
| SL50CUW    | Sample loop 50ul UW type valve            | 1/16in ends with nuts & ferrules 316SS |
| SL50CW     | Sample loop 50ul W type valve             | 1/16in ends with nuts & ferrules 316SS |
| SL50NW     | Sample loop 50ul W type valve             | 1/32in ends with nuts & ferrules 316SS |
| SL50UW     | Sample loop 50ul UW type valve            | 1/8in ends with nuts & ferrules 316SS  |
| SL5CUW     | Sample loop 5ul UW type valve             | 1/16in ends with nuts & ferrules 316SS |
| SL5CW      | Sample loop 5ul W type valve              | 1/16in ends with nuts & ferrules 316SS |
| SL5KCSTP   | Sample loop 5ml mpos ST/MW P-type valve   | 1/16in ends with nuts & ferrules 316SS |
| SL5KCSTUW  | Sample loop 5ml mpos ST UW-type valve     | 1/16in ends with nuts & ferrules 316SS |
| SL5KCUW    | Sample loop 5ml UW type valve             | 1/16in ends with nuts & ferrules 316SS |
| SL5KCW     | Sample loop 5ml W type valve              | 1/16in ends with nuts & ferrules 316SS |
| SL5KSTP    | Sample loop 5ml mpos ST/MW P-type valve   | 1/8in ends with nuts & ferrules 316SS  |
| SL5KUW     | Sample loop 5ml UW type valve             | 1/8in ends with nuts & ferrules 316SS  |
| SL5NW      | Sample loop 5ul W type valve              | 1/32in ends with nuts & ferrules 316SS |
| SOMAP      | Manual adaptor for standoff               | incl. MHA and SVH                      |
| SOMAPPF    | Manual adaptor with Position feedback     | for standoff incl. MHA and SVH         |
| SOMAW      | Manual adaptor for standoff               | incl. MHA and WK                       |
| SOUTH      | Handle for use with standoff              | 2-pos. UW-type valve                   |
| SPSS40     | Ultra High Pressure Injection System      | 40K psi liq                            |
| SSA10UW    | Rotor seal 10 port 2-pos UW-valve         | 1/8 x .75mm 75C/5000psi liq H          |
| SSA10UWE   | Rotor seal 10 port 2-pos UW-valve         | 1/8 x .75mm 225C/400psi gas E          |
| SSA10UWT   | Rotor seal 10 port 2-pos UW-valve         | 1/8 x .75mm 330C/300psi gas T          |
| SSA4UW     | Rotor seal 4 port 2-pos UW-valve          | 1/8 x .75mm 75C/5000psi liq H          |
| SSA4UWE    | Rotor seal 4 port 2-pos UW-valve          | 1/8 x .75mm 225C/400psi gas E          |
| SSA4UWT    | Rotor seal 4 port 2-pos UW-valve          | 1/8 x .75mm 330C/300psi gas T          |
| SSA6UW     | Rotor seal 6 port 2-pos UW-valve          | 1/8 x .75mm 75C/5000psi liq H          |
| SSA6UWE    | Rotor seal 6 port 2-pos UW-valve          | 1/8 x .75mm 225C/400psi gas E          |
| SSA6UWT    | Rotor seal 6 port 2-pos UW-valve          | 1/8 x .75mm 330C/300psi gas T          |
| SSA8UW     | Rotor seal 8 port 2-pos UW-valve          | 1/8 x .75mm 75C/5000psi liq H          |
| SSA8UWE    | Rotor seal 8 port 2-pos UW-valve          | 1/8 x .75mm 225C/400psi gas E          |
| SSA8UWT    | Rotor seal 8 port 2-pos UW-valve          | 1/8 x .75mm 330C/300psi gas T          |
| SSAC10UW   | Rotor seal 10 port 2-pos UW-valve         | 1/16 x .75mm 75C/5000psi liq H         |
| SSAC10UWE  | Rotor seal 10 port 2-pos UW-valve         | 1/16 x .75mm 200C/400psi gas E         |
| SSAC10UWT  | Rotor seal 10 port 2-pos UW-valve         | 1/16 x .75mm 330C/300psi gas T         |
| SSAC10W    | Rotor seal 10 port 2-pos W-valve          | 1/16 x .4mm 75C/5000psi liq H          |
| SSAC10WE   | Rotor seal 10 port 2-pos W-valve          | 1/16 x .4mm 225C/400psi gas E          |
| SSAC10WT   | Rotor seal 10 port 2-pos W-valve          | 1/16 x .4mm 350C/300psi gas T          |
| SSAC4UW    | Rotor seal 4 port 2-pos UW-valve          | 1/16 x .75mm 75C/5000psi liq H         |
| SSAC4UWE   | Rotor seal 4 port 2-pos UW-valve          | 1/16 x .75mm 225C/400psi gas E         |
| SSAC4UWT   | Rotor seal 4 port 2-pos UW-valve          | 1/16 x .75mm 330C/300psi gas T         |
| SSAC4W     | Rotor seal 4 port 2-pos W-valve           | 1/16 x .4mm 75C/5000psi liq H          |
| SSAC4WE    | Rotor seal 4 port 2-pos W-valve           | 1/16 x .4mm 225C/400psi gas E          |
| SSAC4WT    | Rotor seal 4 port 2-pos W-valve           | 1/16 x .4mm 350C/300psi gas T          |
| SSAC6UW    | Rotor seal 6 port 2-pos UW-valve          | 1/16 x .75mm 75C/5000psi liq H         |
| SSAC6UWE   | Rotor seal 6 port 2-pos UW-valve          | 1/16 x .75mm 225C/400psi gas E         |
| SSAC6UWT   | Rotor seal 6 port 2-pos UW-valve          | 1/16 x .75mm 330C/300psi gas T         |
| SSAC6W     | Rotor seal 6 port 2-pos W-valve           | 1/16 x .4mm 75C/5000psi liq H          |
| SSAC6WE    | Rotor seal 6 port 2-pos W-valve           | 1/16 x .4mm 225C/400psi gas E          |
| SSAC6WT    | Rotor seal 6 port 2-pos W-valve           | 1/16 x .4mm 350C/300psi gas T          |
| SSAC8UW    | Rotor seal 8 port 2-pos UW-valve          | 1/16 x .75mm 75C/5000psi liq H         |
| SSAC8UWE   | Rotor seal 8 port 2-pos UW-valve          | 1/16 x .75mm 225C/400psi gas E         |
| SSAC8UWT   | Rotor seal 8 port 2-pos UW-valve          | 1/16 x .75mm 330C/300psi gas T         |